



# Planar SLP55-T

4K LCD Display

The Planar® Simplicity™ P Series SLP55-T is an 55" 4K LCD display for landscape or portrait digital signage that affordably incorporates media playback, cybersecurity mitigation, 4K @ 60Hz support, ENERGY STAR® efficiency and commercial functionality. Its elegant design with a narrow, logo-free bezel and slim profile provide the ideal display for digital signage in retail stores, restaurants, medical offices, corporate meeting areas and hospitality.



SPECIFICATION	DETAIL
Product Name	SLP55-T
Planar Part Number	998-3933-00
Protective Glass	2mm with AG coating
Touch Technology	Projected Capacitive: 20 points
OS Compatibility	Windows 10, 11, Mac OSX and Linux
Display Resolution	Ultra HD (3840 x 2160)
Screen Size	55 in. (diagonal)
Aspect Ratio	16:9
Display Technology	Direct-lit LED LCD
Display Active Area	47.7" x 26.7" (1211.6mm x 682.4mm)
Viewing Angle (typ)	178°
Backlight	LED
Backlight life (1/2 brightness)	30,000 hrs (min)
Brightness (w/protective glass)	400 nits
Response Time (typ)	8 ms

<b>Frame Rate</b>	60Hz
<b>Contrast Ratio (typ)</b>	1200:1
<b>Pixel Pitch</b>	0.315mm x 0.315mm
<b>Color Gamut</b>	72% NTSC
<b>Display Color</b>	>1 billion colors. Full 10 bit data path
<b>External Connections</b>	HDMI® x 2 (HDCP 2.2), USB-C x 1 (also used for touch interface), VGA x 1, USB 3.0 x1, USB 2.0 x1, MicroSD, USB-B (for touch interface)
<b>Modes</b>	3840x2160 @ 24/25/30/60Hz; 480p, 576p, 720p @ 50/60 Hz; 1080p @ 50/60Hz; 1080i @ 50/60 Hz
<b>Display Control</b>	IR, RS-232, LAN, HDMI-CEC, Keypad
<b>Cabinet Dimensions (W x H x D)</b>	49.4" x 28.6" x 2.5" (1254.4mm x 725.2mm x 62.8mm)
<b>Cabinet Dimensions with Handles (W x H x D)</b>	Not Applicable
<b>Orientation</b>	Landscape/Portrait
<b>Bezel Width</b>	0.8" (19.5mm)
<b>Display Edge to Active Area</b>	1.1" (26.7mm)
<b>Weight</b>	46.3 lbs (21.0 kg)
<b>Weight (Shipping)</b>	62.8 lbs (28.5 kg)
<b>Audio Input</b>	PC Line In
<b>Audio Output</b>	PC Line Out, S/PDIF
<b>Speakers</b>	10W x 2 built-in
<b>Enclosure</b>	Plastic rear enclosure
<b>Mounting</b>	VESA: 300mm x 300mm
<b>Fanless</b>	Yes
<b>Line Voltage</b>	100-240V; 50/60Hz
<b>Power Consumption (typ)</b>	145W (standby: <0.5W)
<b>Operating Temperature</b>	0° to +40°C (32° to 104°F) up to 3000m
<b>Humidity</b>	20 - 85% RH (non-condensing)

<b>Options / Features</b>	Media file playback via USB, MicroSD, internal storage, web page and embedded cloud-based content app (requires subscription). Logo-free bezel, logo-free bezel, lockable rear keypad.
<b>Operating System</b>	Proprietary OS based on Android 10.0. Google Play and installation of third-party apps are not supported by Planar.
<b>Storage</b>	32GB (10.5GB available)
<b>Approvals</b>	FCC Class A, cTUVus, CE, RoHS, EN 303 645
<b>ENERGY STAR® Certified</b>	Yes
<b>Cyber Security</b>	EN 303 645 certified
<b>Security</b>	No WiFi, Secure Shell (SSH) protocol, EN 303 645 certified
<b>Warranty</b>	3 years Advance Exchange
<b>Recommended Usage</b>	Up to 24x7
<b>In the Box</b>	SLP55-T display, C14 connector US power cord - 1.8m, C14 connector EU power cord - 1.8m, HDMI cable - 1.8m, USB-C cable 1.8m, RS-232 cable, IR cable, USB A to B cable, remote control, cable clamps, 3mm tip passive stylus x1, Quick Start Guide
<b>UPC</b>	8 10069 81158 1
<b>HDMI®</b>	Planar utilizes HDMI® standards in this product. The terms HDMI, HDMI High-Definition Multimedia Interface, HDMI Trade dress and the HDMI Logos are trademarks or registered trademarks of HDMI Licensing Administrator, Inc.

For more information, please visit [www.planar.com](http://www.planar.com)

*Specifications are subject to change without notice.*

*Specification Report Date: 10/28/2024*

*© Copyright 2024 Planar Systems, Inc. All rights reserved*