

Satellite Pro™ C40-K

PSY25U-08501V

DYNAMIC CAPABILITY, PORTABILITY AND VALUE

Boost workforce productivity with the sleek, budget-friendly Satellite Pro™ C40-K by Dynabook. Featuring Intel® Core™ processors, Windows 11 Pro, Wi-Fi 6E, 14-inch display, large battery and a variety of ports, it conquers tasks with confidence, no matter where the workday leads.



UNCOMPROMISED POWER AND EFFICIENCY

Equipped with the latest Intel® Core™ processors (Series 1), And Wi-Fi 6E, these laptops offer accelerated performance and wireless connections for effortless task management and browsing.



SECURITY TAKEN SERIOUSLY

Built to withstand a variety of threats, Satellite Pro™ laptops incorporate firmware TPM (fTPM) 2.0 technology and a security lock slot, providing peace of mind against unauthorized access and data breaches.



MAINTAINS A CLEANER WORK SURFACE

With an EPA-approved IONPURE IPL coating, Satellite Pro™ laptop chassis inhibits microbial growth, ensuring a cleaner work environment for users, whether in classrooms, offices, or shared workspaces.



PORTS FOR VERSATILE CONNECTIVITY

Designed with a comprehensive selection of ports, including HDMI, Gigabit LAN, USB-C, USB-A, and a microSD card slot for seamless, clutter-free connections with peripherals and accessories.



COLLABORATION COMES NATURALLY

Featuring a privacy shutter webcam, dual microphones, and stereo speakers, Satellite Pro™ laptops enhance collaboration, enabling users to engage in clear and productive video conferences and virtual meetings.



PROVEN RELIABILITY

Satellite Pro™ laptops are backed by proven reliability and come standard with Dynabook's +Care Service® Warranty with On-site.



PLATFORM SPECIFICATIONS AND CONFIGURABLE OPTIONS

Operating System*

- Windows 11 Pro

Processor*

- Intel® Core™ 5 Processors (Series 1) 120U

Memory*

- 16 GB DDR4 3200 SODIMM

Display*

- 14" FHD (1920 x 1080)

Storage*

- 512 GB M.2 PCIe NVMe SSD

Communications

- Gigabit Ethernet LAN
- Intel® Wi-Fi 6E AX211, 802.11ax
- Bluetooth™

Camera*

- Webcam with privacy shutter

Audio

- Stereo Speakers with DTS® Audio Processing
- Dual-Array Microphones

Ports

- HDMI®
- One (1) USB-C® 3.2. Gen 2 (supports Thunderbolt 4)
- Three (3) USB 3.2 Gen 1 Type-A Ports
 - One (1) with USB Sleep & Charge Support
- RJ-45 Ethernet LAN Port
- Headset Jack (Combo Port)
- microSD™ Card Slot

Security*

- Trusted Platform Module 2.0
- Security Lock Slot

Input Devices

- Premium Raised-tile, Spill-resistant 10-key Keyboard
- ClickPad Pointing Device

Battery

- 53 Wh Battery

Physical Description

- 323.9 x 211.8 x 18.75 Millimeters
- 12.75 x 8.33 x 0.74 Inches
- 1.38 Kilograms / 3.04 Pounds

Regulatory / Environmental Specifications

- EPEAT® Rated
- ENERGY STAR® Qualified
- RoHS Compatible

Warranty*

- 1 Year Standard Limited Warranty

Optional Accessories

- PS0120UA1PRP – Dynabook Thunderbolt™ 4 Dock
- PA5356U-1PRP – Dynabook USB-C® Dock
- PS0001UA1PRP – USB-C® to HDMI® / VGA / LAN / USB 3.0 Adapter with Power Delivery (PD) Charging
- PS0089UA1PRP – USB-C® to VGA / LAN Adapter with Power Delivery (PD) Charging
- PA5270U-1PRP – USB-C® to VGA Adapter with Power Delivery (PD) Charging
- PA5352U-1ACA – 65W USB-C® AC Adapter (5V / 9V / 15V / 20V)



+Care Service® Warranty with On-Site

For even greater peace of mind, Dynabook's industry-leading +Care Service® Warranty with On-site can be added for worry-free reliability with up to four years of coverage. With comprehensive warranty coverage and access to a vast service and support network, Dynabook helps businesses minimize downtime, reduce IT costs, and ensure uninterrupted productivity.



*Based on Configuration

** Visit <http://us.dynabook.com/info> for a complete list of all product legal footnotes

© 2024 Dynabook Americas, Inc. While Dynabook has made every effort at the time of publication to ensure the accuracy of the information provided herein, product specifications, configurations, prices, system/component/options availability are all subject to change without notice. Dynabook, the Dynabook logo and +Care Service are trademarks or service marks of Dynabook Americas, Inc. and/or Dynabook, Inc. All other products and names are the property of their respective owners. All rights reserved.