

## Business Essential

### ***Satellite Pro C40-K / C50-K***

# Striking a balance between performance and portability

Unlock a new era of seamless work performance with the ultraportable Satellite Pro C40/C50 series, equipped with fully loaded features including the latest USB Type-C™ port to provide a one-click connection to your most-used peripherals, making multitasking easier than before. Coated with a special anti-bacterial dark blue finish to inhibit bacterial growth, this ultra-slim, narrow-bezel laptop is ready to take on any business task you throw its way so you can work in style.



#### ***Satellite Pro C40-K***

Thin & Sleek  
**18.75mm**

From  
**1.35kg\***

#### ***Satellite Pro C50-K***

Thin & Sleek  
**18.95mm**

From  
**1.52kg\***



Powered by the latest 12<sup>th</sup> Gen Intel® Core™ processors



Choice of HD and FHD Anti-glare displays with narrow bezels for a comfortable viewing experience



HD webcam with camera shutter and AI-enhanced audio capabilities



Fingerprint reader for boosted security



Full ports connectivity with 4 USB ports, HDMI, and built-in LAN for collaboration anywhere





Anti-Bacterial coating to keep you safe



Lay-flat 180° hinge

 Windows 11



Intel® Core™ i7 processor

# Product Highlights



## No-compromise Style, Productivity, and Value

Meet your company's technology goals with a stylish device carefully engineered for business mobility, without breaking the IT budget. Equipped with the latest 12th Gen Intel® Core™ processors up to 32GB of DDR4 RAM in two configurable slots, and PCIe SSD storage of up to 1TB, the new Satellite Pro C40/C50 series feature a special anti-bacterial paint coating which inhibits the growth of microorganisms by up to 99.9%.

## Designed to look the part

Weighing just 1.35kg\* (Satellite Pro C40-K) and 1.52kg\* (Satellite Pro C50-K), the sleek and stylish Satellite Pro C40/C50 series are less than 19mm in thickness and are coated in modern dark blue. Its non-reflective matte surface, paired with an aesthetically pleasing ergonomic keyboard and a large ClickPad for accurate control, complements any kind of work environment and makes work a joy thanks to its long battery life of up to 8 hours\*\*.

## Make Any Environment Your Workspace

The Satellite Pro C40/C50 series may be sleek and compact, but they are fully loaded with connectivity. Besides having three USB 3.2 Type-A ports, built-in Bluetooth® 5.2, and a microSD card reader, the Satellite Pro C40/C50 series also feature a HDMI 1.4b port for plug-and-play connection to external screens, USB 3.2 Type-C ports for charging, external display, and data transfer, as well as and reliable Gigabit LAN and 802.11ac Wi-Fi for effortless network access.

## Made for Hybrid Working

Enjoy a seamless remote experience with premium audio-visual tools and conferencing buttons on the ergonomic keyboard, to easily engage with work or study colleagues. Powered by the latest AI technology, all audio-visual integration provides crystal clear conferencing regardless of the surroundings or the clarity of the audio stream of others on the call.

## Security You Can Trust

The Satellite Pro C40/C50 series come with enterprise-ready security features such as firmware-based Trusted Platform Module (TPM) 2.0 so information is encrypted on the device. To enhance protection for security, the Satellite Pro series offers optional robust fingerprint biometric authentication, optional face authentication camera, and an integrated webcam privacy shutter with a security cable lock slot for greater piece of mind.





# Specifications

	Satellite Pro C40-K	Satellite Pro C50-K
PROCESSOR	Intel® Core™ i3-1215U Processor (1.2GHz, upto 4.4GHz, 6 Cores (2P+4E), 10MB Cache) Intel® Core™ i5-1235U Processor (1.3GHz, upto 4.4GHz, 10 Cores (2P+8E), 12MB Cache) Intel® Core™ i7-1255U Processor (1.7GHz, upto 4.7GHz, 10 Cores (2P+8E), 12MB Cache)	
OPERATING SYSTEM	Windows 11 Pro	
GRAPHICS	Up to Intel® Iris® Xe Graphics	
SYSTEM MEMORY	Choice of 8GB / 16GB DDR4 (3,200 MHz) up to a maximum of 32GB (two fully configurable slots)	
DISPLAY	14" HD Anti-Glare display, resolution 1,366 x 768  14" Full HD Anti-Glare (250NIT) IPS display, resolution 1,920 x 1,080	15.6" HD Anti-Glare display, resolution 1,366 x 768  15.6" Full HD Anti-Glare (250NIT) IPS display, resolution 1,920 x 1,080
HARD DISK*	Choice of 256GB, 512GB Gen 3 PCIe NVMe Solid State Drive or 1TB Gen 4 PCIe NVMe Solid State Drive	
INPUT DEVICES	ClickPad with antibacterial coating	
COMMUNICATIONS	Intel® Wi-Fi 6 Dual Band Wireless LAN (802.11ax), Bluetooth® 5.2	
BUILT-IN CAMERA / MICROPHONE	HD webcam with shutter slider and LED indicator. Infrared camera with Face Authentication (optional). Dual Mic supports beam forming and AI-powered noise reduction technology	
SOUND SYSTEM	Stereo speakers	
KEYBOARD	Frameless matt black tiled keyboard with antibacterial coating. Dedicated conference call function keys	Frameless matt black tiled keyboard with numeric keypad, antibacterial coating. Dedicated conference call function keys
INTERFACES	3x USB 3.2 Type-A, 1x USB 3.2 Type-C™ Gen 2 (supporting power delivery, data transfer and display), HDMI-out, RJ-45, headphone/microphone combo, MicroSD card reader	
BATTERY TYPE	3-cell, 45Whr Lithium-Ion Polymer (not user replaceable). Quick charge technology (30 minutes charge = 4 hours of battery). Battery management eco utility for conservation of the battery lifespan	
POWER RATING	45W 100-240V/50-60Hz Universal AC Adaptor	
SECURITY FEATURES	Firmware Trusted Platform Module (fTPM) 2.0, Fingerprint Reader (optional), Infrared (IR) camera for Face Authentication (optional), Camera shutter slider, Security lock slot	
PROTECTION FEATURES	180-degree hinge, Antibacterial paint coating (chassis, keyboard and Clickpad), Slim bezels (83% screen-to-body ratio)	
PHYSICAL DIMENSIONS	323.9 x 211.8 x 18.75mm	358.9 x 230.5 x 18.95mm
WEIGHT	Starting from 1.35kg	Starting from 1.52kg
WARRANTY*	1-year Local limited warranty (carry-in), 1-year battery	

\* Actual product features and specifications depend on model and local availability. For more information, please visit <http://asia.dynabook.com>  
+ Dynabook's standard limited warranty terms and limitations apply. For more details, please visit <https://asia.dynabook.com/warrantylaptop/>



## Recommended Accessories



Additional dynabook Universal 45W AC Adaptor (PS0131EA1ACA)



Dynabook USB-C Dock (PA5356L-2PRP)



Dynabook Backpack (OA1207-CWTBP)



Dynabook Blue LED USB Optical Mouse U60 (PA5346L-1ETE)