



SPECIFICATIONS

PANEL SIZE	27"
PANEL RESOLUTION	1920 x 1080 (FHD)
REFRESH RATE	120Hz
RESPONSE TIME	1ms (MPRT) / 4ms (GTG)
PANEL TYPE	IPS
BRIGHTNESS (NITS)	300 cd/m2
VIEWING ANGLE	178°(H) / 178°(V)
ASPECT RATIO	16:9
CONTRAST RATIO	1500:1
sRGB	116%
ACTIVE DISPLAY AREA (MM)	597.888(H) x 336.312(V)
PIXEL PITCH (H X V)	0.3114 (H) x 0.3114 (V)
SURFACE TREATMENT	Anti-glare
DISPLAY COLORS	16.7M
COLOR BIT	8 bits (6 bits + FRC)
HDR SUPPORT	HDR Ready
VIDEO PORTS	1x HDMI™ 2.0 (FHD@120Hz) 1x DisplayPort (1.2a) 1x D-Sub (VGA)
AUDIO PORTS	1x Headphone-out 1x Line-in
KENSINGTON LOCK	Yes
SPEAKER	2x 2W
VESA MOUNTING	100 x 100 mm
POWER TYPE	Internal Power Board
POWER INPUT	100~240V, 50~60Hz
DYNAMIC REFRESH RATE TECHNOLOGY	Adaptive-Sync
ADJUSTMENT (TILT)	-5° ~ 20°
DIMENSION (W X H X D)	611.9 x 447.7 x 206.8 mm (24.09 x 17.63 x 8.14 inch)
CARTON DIMENSION (W X H X D)	688 x 505 x 128 mm (27.09 x 19.89 x 5.04 inch)
WEIGHT (NW / GW)	3.66 kg (8.07 lbs) / 6.54 kg (14.42 lbs)
CERTIFICATES	CB/CE Energy Star

FEATURES



IPS Panel with Wide Viewing Angle

Instantly optimize the screen colors and brightness to ensure that you enjoy every detail at its best.



Perfect Edge

Set-up multi-display immensely with the 4-side edgeless design and enjoy the wider and more immersive view.



120Hz High Refresh Rate

Enjoy the high-quality entertainment with a smoother and flicker-free images.



EyesErgo

An eye care solution designed with ergonomics in mind.



Eye-Q Check

Help have self-check eyes & remind to take a rest while using the monitor for a long time.



Accessory Slot Design

Enjoy a clean table with the accessory slot design where you can put MSI Pen or Smartphone, and you will not miss important messages anymore.



Built-In Speaker

Built-in speakers allow you to listen clearly without connecting external speakers.



VESA Mountable

To be mounted on the wall of your office & home with a VESA standard design which can make it completely invisible on a desk.

VIDEO INPUT COMPATIBILITY

PC, Mac, PS5™, PS4™, Xbox, Mobile, Notebook

* All trademarks and the registered trademarks are the property of their respective owners.

Note

HDMI™: 1920 x 1080 (Up to 120Hz)

DisplayPort: 1920 x 1080 (Up to 120Hz)

D-Sub (VGA): 1920 x 1080 (Up to 60Hz)

HDMI™ CEC Support

*sRGB follow CIE1976 Standard

CONNECTIONS



1. 1x DisplayPort 1.2a
2. 1x HDMI™ 2.0 (FHD@120Hz)
3. 1x D-Sub (VGA)
4. 1x Line-in
5. 1x Headphone-out
6. 1x AC-in
7. 1x Kensington Lock
8. 1x 5-way Navigator