



## SPECIFICATIONS

Panel Size	24.5" (62.23 cm)
Active Display Area (mm)	543.744(H) x 302.616(V)
Curvature	Flat
Panel Type	Rapid IPS
Panel Resolution	1920x1080 (FHD)
Pixel Pitch (H x V)	0.2832 (H) x 0.2802 (V)
Aspect Ratio	16:9
Brightness (nits)	250 Nits (Typ.)
Contrast Ratio	1000:1
DCR	100000000:1
Signal Frequency	53.28~333KHz (H) / 48~300Hz (V)
ACTIVATED RANGE	48 to 300Hz
Refresh Rate	300Hz
Response time	0.5ms (GtG, Min.)
DYNAMIC REFRESH RATE TECHNOLOGY	Adaptive-Sync
HDR Support	HDR Ready
Video ports	1 x DisplayPort 1.4a 2 x HDMI™ 2.0b (FHD@240Hz)
USB ports	N/A
Audio ports	1 x Headphone-out
Viewing Angle	178°(H) / 178°(V)
Adobe RGB / DCI-P3 / sRGB	87% / 90% / 120%
Surface Treatment	Anti-glare
Display Colors	1.07B, (8 bits + FRC)
Frameless Design	Yes
PIP / PBP Function	N/A
Power Type	Internal Power Board
Power Input	100~240V, 50/60Hz
Adjustment (Tilt)	-5° ~ 20°
Kensington Lock	Yes
VESA Mounting	100 x 100 mm
Weight (NW / GW)	3.24kg / 5.13kg
Dimension (W x D x H)	557.1 x 220.1 x 418.5mm 557.1 x 66.4 x 326.9mm (without stand)
Carton Dimension (W X D X H)	630 x 125 x 411mm

## FEATURES



### Rapid IPS

Make sure the intensity and purity of colors when gaming.



### 300Hz High Refresh Rate

Experience smooth gaming with a blazing fast 300Hz refresh rate that gives you the upper hand in fast moving games.



### 0.5ms (GtG, Min.) Response Time

Eliminate screen tearing and choppy frame rates with 0.5ms (GtG, Min.) Response Time.



### Console Mode

Perfectly support 120Hz at QHD 2K resolution with next-gen console like PS5 and Xbox series X/S.



### Frameless Design

With the narrow bezel, you will not even notice the monitor at all in the heat of the moment.



### AI Vision

Smart black tuner to brighten your day by bringing out the fine details in dark areas.

**Note**

Display Port: 1920 x 1080 (Up to 300Hz)  
HDMI™: 1920 x 1080 (Up to 240Hz)  
Adobe RGB, DCI-P3 and sRGB follow CIE1976 Standard

## CONNECTIONS



1. 5-way Joystick Navigator
2. AC-in
3. 2x HDMI™ 2.0b(FHD@240Hz)
4. Display Port 1.2a
5. Earphone out
6. Kensington Lock