



## SPECIFICATIONS

|  |   |
|--|---|
| <b>PANEL SIZE</b>                      | 27"   |
| <b>PANEL RESOLUTION</b>                | 1920 x 1080 (FHD)   |
| <b>REFRESH RATE</b>                    | 120Hz   |
| <b>RESPONSE TIME</b>                   | 1ms (MPRT) / 4ms (GtG)  |
| <b>PANEL TYPE</b>                      | IPS   |
| <b>BRIGHTNESS (NITS)</b>               | 300 cd/m <sup>2</sup>   |
| <b>VIEWING ANGLE</b>                   | 178°(H) / 178°(V)   |
| <b>ASPECT RATIO</b>                    | 16:9  |
| <b>CONTRAST RATIO</b>                  | 1500:1  |
| <b>sRGB</b>                            | 116%  |
| <b>ACTIVE DISPLAY AREA (MM)</b>        | 597.888 (H) x 336.312 (V)   |
| <b>PIXEL PITCH (H X V)</b>             | 0.3114 (H) x 0.3114 (V)   |
| <b>SURFACE TREATMENT</b>               | Anti-glare  |
| <b>DISPLAY COLORS</b>                  | 16.7M   |
| <b>COLOR BIT</b>                       | 8 bits (6 bits + FRC)   |
| <b>HDR SUPPORT</b>                     | HDR Ready   |
| <b>VIDEO PORTS</b>                     | 1x HDMI™ 2.0 (FHD@120Hz)<br>1x DisplayPort 1.2a<br>1x D-Sub (VGA) |
| <b>AUDIO PORTS</b>                     | 1x Headphone-out<br>1x Line-in                                    |
| <b>KENSINGTON LOCK</b>                 | Yes   |
| <b>SPEAKER</b>                         | 2x 2W   |
| <b>VESA MOUNTING</b>                   | 100 x 100 mm  |
| <b>POWER TYPE</b>                      | Internal Power Board  |
| <b>POWER INPUT</b>                     | 100~240V, 50~60Hz   |
| <b>DYNAMIC REFRESH RATE TECHNOLOGY</b> | Adaptive-Sync   |
| <b>ADJUSTMENT (TILT)</b>               | -5° ~ 20°   |
| <b>DIMENSION (W X H X D)</b>           | 611.9 x 447.7 x 206.8 mm<br>(24.09 x 17.63 x 8.14 inch)           |
| <b>CARTON DIMENSION (W X H X D)</b>    | 688 x 505 x 128 mm<br>(27.09 x 19.89 x 5.04 inch)                 |
| <b>WEIGHT (NW / GW)</b>                | 3.66 kg (8.07 lbs) / 6.54 kg (14.42 lbs)                          |
| <b>CERTIFICATES</b>                    | CB/CE<br>Energy Star  |

## FEATURES



### IPS Panel with Wide Viewing Angle

Instantly optimize the screen colors and brightness to ensure that you enjoy every detail at its best.



### Perfect Edge

Set-up multi-display immensely with the 4-side edgeless design and enjoy the wider and more immersive view.



### 120Hz High Refresh Rate

Enjoy the high-quality entertainment with a smoother and flicker-free images.



### EyesErgo

An eye care solution designed with ergonomics in mind.



### Eye-Q Check

Help have self-check eyes & remind to take a rest while using the monitor for a long time.



### Accessory Slot Design

Enjoy a clean table with the accessory slot design where you can put MSI Pen or Smartphone, and you will not miss important messages anymore.



### Built-In Speaker

Built-in speakers allow you to listen clearly without connecting external speakers.



### VESA Mountable

To be mounted on the wall of your office & home with a VESA standard design which can make it completely invisible on a desk.

### VIDEO INPUT COMPATIBILITY

PC, Mac, PS5™, PS4™, Xbox, Mobile, Notebook

\*All trademarks and the registered trademarks are the property of their respective owners.

### Note

HDMI™: 1920 x 1080 (Up to 120Hz)

DisplayPort: 1920 x 1080 (Up to 120Hz)

D-Sub (VGA): 1920 x 1080 (Up to 60Hz)

HDMI™ CEC Support

\*sRGB follow CIE1976 Standard

## CONNECTIONS



1. 1x DisplayPort 1.2a
2. 1x HDMI™ 2.0 (FHD@120Hz)
3. 1x D-Sub (VGA)
4. 1x Line-in
5. 1x Headphone-out
6. 1x AC-in
7. 1x Kensington Lock
8. 1x 5-Way Navigator