



## SPECIFICATIONS

|                                 |  |
|---------------------------------|--|
| Panel Size                      | 27" (68.58 cm)   |
| Active Display Area (mm)        | 596.736 (H) x 335.664 (V)                                |
| Curvature                       | Curve 1500R  |
| Panel Type                      | Rapid VA   |
| Panel Resolution                | 2560x1440 (WQHD)   |
| Pixel Pitch (H x V)             | 0.2331(H) x 0.2331(V)                                    |
| Aspect Ratio                    | 16:9   |
| Brightness (nits)               | 300 (Typ.)   |
| Contrast Ratio                  | 5000:1 (Typ.)  |
| DCR                             | 10000000:1   |
| Signal Frequency                | 71.04~266.4KHz (H) / 48~180Hz(V)                         |
| ACTIVATED RANGE                 | 48~180Hz   |
| Refresh Rate                    | 180Hz  |
| Response time                   | 0.5ms (GtG, Min.)  |
| DYNAMIC REFRESH RATE TECHNOLOGY | Adaptive-Sync  |
| HDR Support                     | HDR Ready  |
| Video ports                     | 1 x DisplayPort 1.4a<br>2 x HDMI™ 2.0b (WQHD@144Hz)      |
| USB ports                       | N/A  |
| Audio ports                     | 1 x Headphone-out  |
| Viewing Angle                   | 178°(H) / 178°(V)  |
| Adobe RGB / DCI-P3 / sRGB       | 89% / 93% / 128%   |
| Surface Treatment               | Anti-glare   |
| Display Colors                  | 1.07B , 10 bits (8 bits + FRC)                           |
| Power Type                      | External Adaptor 20V 2.25A                               |
| Power Input                     | 100~240V, 50/60Hz  |
| Adjustment (Tilt)               | -5° ~ 20°  |
| Adjustment (Swivel)             | N/A  |
| Adjustment (Pivot)              | N/A  |
| Adjustment (Height)             | N/A  |
| Kensington Lock                 | Yes  |
| Dimension (W x D x H)           | 614 x 250 x 438mm<br>614 x 77 x 364mm (without stand)    |
| Carton Dimension (W X D X H)    | WW carton: 750 x 150 x 488mm<br>Outer: 765 x 165 x 515mm |
| Frameless Design                | Yes  |
| PIP / PBP Function              | Yes  |

## FEATURES



### Curved 1500R

Bring an immersive & comfortable viewing experience to eliminate distortion and cover a wider field of view



### Rapid VA Panel

Make sure the intensity and purity of colors when gaming.



### 180Hz High Refresh Rate

Experience smooth gaming with a blazing fast 180Hz refresh rate, that gives you the upperhand in fast moving games.



### 0.5ms (GtG, Min.) Response Time

Eliminate screen tearing and choppy frame rates with 0.5ms (GtG, Min.) Response Time.



### HDR Ready

Provide eye-catching detail through contrast and shadows adjustment.



### Console Mode

Perfectly support 120Hz at QHD 2K resolution with next-gen console like PS5 and Xbox series X/S.

|                         |   |
|-------------------------|---|
| <b>VESA Mounting</b>    | 100 x 100 mm  |
| <b>Weight (NW / GW)</b> | 3.4kg / 6.1kg<br>3kg (without stand)  |
| <b>Note</b>             | Display Port: 2560 x 1440 (Up to 180Hz)<br>HDMI 2.0b: 2560 x 1440 (Up to 144Hz)<br>Adobe RGB, DCI-P3 and sRGB follow CIE1976 Standard |

## CONNECTIONS



1. 5-way Joystick Navigator
2. DC-in
3. Display Port 1.4a
4. 2x HDMI™  
2.0b(WQHD@144Hz)
5. Earphone out
6. Kensington Lock