



TG2460HIII

60mm ticket / receipt printer

- Metal frame (galvanized/aluminium alloy)
- High print quality (200 DPI)
- Paper width: 60mm
- Paper thickness: from 60 to 80 μ m
- Printing > 140 mm/sec
- RS232 and USB interfaces
- Barcodes: UPC-A, UPC-E, EAN13, EAN8, CODE39, ITF, CODABAR, CODE93, CODE128, CODE32, QR CODE
- Characters: European, International, Thai, Portuguese, Nordic, Arabic, Chinese and Russian
- Highly reliable cutter: over 1,000,000 cuts or Tear-Off system
- Sensors: head temperature, paper presence, anti paper jamming, ticket collection, paper end and near paper end
- LED bezel



CHARACTERISTICS

- Patented Anti Jamming System
- Suitable for tough environments, down to -20°C up to +70°C
- Available version with ejector
- Illuminated paper bezel
- Multi-position paper roll
- Large paper roll: Ø 100 mm
- Metal structure that provides increased rigidity for the printing mechanism and facilitates motor heat dissipation, resulting in improved stability and reliability over time
- Improved distribution of the head-roller pressure, resulting in improved printing quality


APPLICATIONS

- Self-service kiosks
 - Banking machines
 - Gaming machines
 - Parking meters
 - Queue management systems
 - Vending machines
-

TECHNICAL SHEET

Printing Method	Thermal with fixed head
Number of dots	8 dots/mm
Columns	32 - 42 - 56
Resolution	203 DPI
Printing (mm/sec)	140mm/sec
Character set	PC437, PC850, PC860, PC863, PC865, PC858, PC866, GB2312
Printing Format	Normal, height and width from 1 to 4, bold, negative, underlined, script, italic
Printing Direction	Straight, 180°
Paper width	60 mm
Paper weight	from 55 to 70 g/m ²
Paper thickness	from 60 to 80 μ m
Roll Dimension	100 mm
Sensors	Head temperature, paper jamming, paper presence, notch presence, optional: almost external paper end
Emulation	Custom/POS, TGH
Interfaces	RS232 + USB
Data Buffer	2 kB
Flash Memory	1 MB
Graphic Memory	2 logos of 448x584 dots
Drivers	Windows® (32/64 bit) – only on request WHQL and silent installation; Linux (32/64 bit); Virtual COM (Linux or Windows 32/64 bit); Android™
Software Tools	Status Monitor, PrinterSet, CustomPowerTool, Custom Windows API
Power supply	24V +/- 10%
Medium consumption	0.62A (12.5% dots turned on)
MTBF	420,000 hours (electronic board)
Head Life	50Km/100M pulses
Operating temperature	-20°C + 70°C
Dimensions	PRINTER TG2460HIII USB RS232 CUTTER: 135 (L) x 114 (W) x 81 (H) mm PRINTER TG2460HIII USB RS232 CUT HC STD: 126 (L) x 114 (W) x 81 (H) mm PRINTER TG2460HIII USB TEAR OFF TRASP. BEZ: 126 (L) x 114 (W) x 81 (h) mm PRINTER TG2460HIII USB RS232 CUTTER EJECTOR: 129 (L) x 114 (W) x 81 (H) mm
Weight	0.6 Kg

MODELS



915CG060100300
PRINTER TG2460HIII USB RS232
CUTTER



915CG050141300
PRINTER TG2460HIII USB TEAR
OFF TRASP. BEZ



915CG060200300
PRINTER TG2460HIII USB RS232
CUT HC STD



915CG060300300
PRINTER TG2460HIII USB RS232
CUTTER EJECTOR

Via Berettine, 2 - 43010 Fontevivo PR - VAT: IT02498250345 - TEL: +39 0521 680111 - FAX: +39 0521 610701 - UNIQUE CODE: 8RQN7AZ

The technical data on this website are not binding and may be changed without advanced notice.

Last update: 15 October 2024