



SPECIFICATIONS

Panel Size	27" (68.58 cm)
Active Display Area (mm)	597.888 (H) x 336.312 (V)
Curvature	Curve 1500R
Panel Type	Rapid VA
Panel Resolution	1920x1080 (FHD)
Pixel Pitch (H x V)	0.3114 (H) x 0.3114 (V)
Aspect Ratio	16:9
Brightness (nits)	300 (Typ.)
Contrast Ratio	4000:1 (Typ.)
DCR	100000000:1
Signal Frequency	53.04~1434.72KHz (H) / 48-280Hz (V)
ACTIVATED RANGE	48 to 280Hz
Refresh Rate	280Hz
Response time	0.5ms (GtG, Min.)
DYNAMIC REFRESH RATE TECHNOLOGY	Adaptive-Sync
HDR Support	HDR Ready
Video ports	1 x DisplayPort 1.4a 2 x HDMI™ 2.0b (FHD@240Hz)
USB ports	N/A
Audio ports	1 x Headphone-out
Viewing Angle	178° (H) / 178° (V)
Adobe RGB / DCI-P3 / sRGB	80% / 78% / 102%
Surface Treatment	Anti-glare
Display Colors	1.07B, 10 bits (8 bits + FRC)
Power Type	Power Cable
Power Input	100~240V, 50~60Hz
Adjustment (Tilt)	-5° ~ 20°
Kensington Lock	Yes
Dimension (W x D x H)	610.5 x 249.8 x 451.6mm 610.5 x 90.4 x 362.5mm (without stand)
Carton Dimension (W x D x H)	WW carton: 684 x 158 x 475mm Outer: 704 x 178 x 508mm
Frameless Design	Yes
PIP / PBP Function	N/A
VESA Mounting	100 x 100 mm
Weight (NW / GW)	3.95kg / 6.51kg 3.56kg (without stand)

FEATURES

- HDR Ready**
 Provide eye-catching detail through contrast and shadows adjustment.
- Curved 1500R**
 Bring an immersive & comfortable viewing experience to eliminate distortion and cover a wider field of view.
- Rapid VA Panel**
 Make sure the intensity and purity of colors when gaming.
- Console Mode**
 Perfectly support 120Hz at QHD 2K resolution with next-gen console like PS5 and Xbox series X/S.
- 0.5ms (GtG, Min.) Response Time**
 Eliminate screen tearing and choppy frame rates with 0.5ms (GtG, Min.) Response Time.
- 280Hz High Refresh Rate**
 Experience smooth gaming with a blazing fast refresh rate, that gives you the upper hand in fast-moving games.

Note

Display Port: 1920 x 1080 (Up to 280Hz)
HDMI 2.0b: 1920 x 1080 (Up to 240Hz)
Adobe RGB, DCI-P3 and sRGB follow
CIE1976 Standard

CONNECTIONS



1. 5-way Joystick Navigator
2. AC-in
3. 2x HDMI™ 2.0b(FHD@240Hz)
4. Display Port 1.4a
5. Earphone out
6. Kensington Lock