

PRO MP252 E2

SLIM, SLEEK, SMOOTH





SPECIFICATIONS

PANEL SIZE	24.5"
PANEL RESOLUTION	1920 x 1080 (FHD)
REFRESH RATE	120Hz
RESPONSE TIME	1ms (MPRT) / 4ms (GTG)
PANEL TYPE	IPS
BRIGHTNESS (NITS)	300 cd/m2
VIEWING ANGLE	178°(H) / 178°(V)
ASPECT RATIO	16:9
CONTRAST RATIO	1500:1
sRGB	99%
ACTIVE DISPLAY AREA (MM)	543.744(H) x 302.616(V)
PIXEL PITCH (H X V)	0.2832(H) x 0.2802(V)
SURFACE TREATMENT	Anti-glare
DISPLAY COLORS	16.7M
COLOR BIT	8 bits (6 bits + FRC)
HDR SUPPORT	HDR Ready
VIDEO PORTS	1x HDMI™ 1.4 (FHD@120Hz) 1x DisplayPort (1.2a)
AUDIO PORTS	1x Headphone-out
KENSINGTON LOCK	Yes
SPEAKER	2x 2W
VESA MOUNTING	100 x 100 mm
POWER TYPE	Internal Power Board
POWER INPUT	100~240V, 50~60Hz
DYNAMIC REFRESH RATE TECHNOLOGY	Adaptive-Sync
ADJUSTMENT (TILT)	-5° ~ 20°
DIMENSION (W X H X D)	558 x 416.5 x 188 mm (21.97 x 16.4 x 7.4 inch)
CARTON DIMENSION (W X H X D)	630 x 410 x 125 mm (23.62 x 16.14 x 4.92 inch)
WEIGHT (NW / GW)	3.2 kg (7.1 lbs) / 4.9 kg (10.8 lbs)
CERTIFICATES	CB/CE Energy Star
VIDEO INPUT COMPATIBILITY	PC, Mac, PS5™, PS4™, Xbox, Mobile, Notebook * All trademarks and the registered trademarks are the property of their respective owners.

FEATURES



Perfect Edge

Set-up multi-display immensely with the 4-side edgeless design and enjoy the wider and more immersive view.





120 Hz Enjoy the high-quality entertainment with a smoother and flickerfree images.



IPS Grade Panel

Instantly optimize the screen colors and brightness to ensure that you enjoy every detail at its best while creating your own on-line video



Broadened Display

View your applications, spreadsheets and more with a perfect screen size for work desk that aligns with the visual's comfort



Eye-Q Check

Help have self-check eyes & remind to take a rest while using the monitor for a long time.



EyesErgo

EyesErgo An eye care solution designed with ergonomics in mind.



Built-In Speaker

Built-in speakers allow you to listen clearly without connecting external speakers.



VESA Mountable

To be mounted on the wall of your office & home with a VESA standard design which can make it completely invisible on a desk.



BUSINESS PRODUCTIVITY MONITORS

PRO MP252 E2

SLIM, SLEEK, SMOOTH

Note

HDMI™: 1920 x 1080 (Up to 120Hz) DisplayPort: 1920 x 1080 (Up to 120Hz) D-Sub (VGA): 1920 x 1080 (Up to 60Hz) HDMI™ CEC Support *sRGB follow CIE1976 Standard

CONNECTIONS



- 1. 1x AC-in
- 2. 1x DisplayPort 1.2a
- 3. 1x HDMI™ (FHD@120Hz)
- 4. 1x D-Sub (VGA)
- 5. 1x Headphone-out
- 6. 1x Kensington Lock
- 7. 1x 5-way navigator