



L A P T O P S

Raider A18 HX

RAIDER A18 HX A7VHG-023US

Specification

Manufacturer Part #	RAIDERA18HXA7023
OS	Windows 11 Home
CPU	Ryzen 9 7945HX3D
CPU Speed	2.3 - 5.4GHz
Chipset	-
Color	Core Black
Screen Size	18" 16:10 QHD+(2560 x 1600) 240Hz 100% DCI-P3 IPS-Level Panel
Resolution	(2560x1600) 16:10
GPU	NVIDIA® GeForce RTX™ 4080 Laptop GPU
Video Memory	12G GDDR6
Keyboard	SteelSeries per-Key RGB with Anti-Ghost key (99 Key)
Speaker	Sound by Dynaudio, 4x2W Speakers 2W x2W Woofer
Memory	32GB (16GB*2) DDR5 5600MHz
HDD Capacity	1TB NVMe SSD Gen4x4
HDD Interface	NVMe
TPM	fTPM 2.0
LAN	GB LAN (Up to 2.5G)
WLAN	Qualcomm WiFi7
Bluetooth	BT 5.4
Card Reader	SD7.0
Webcam	IR FHD w/shutter
USB	1x USB 3.2 Gen 2 2x USB 3.2 Gen 1
Type-C Port	1x USB 3.2 Gen 2/DP; 1x USB 3.2 Gen 2/DP&PD 3.1
Video Port	v2.1,
Audio Port	1 Audio Combo (1/8")
AC Power Adaptor	330W
Battery Pack	4 cell (99.9Whr) Li-Ion
Dimension	15.91"x 12.09"x 1.26"
Weight	7.94 lbs
Manufacturer Warranty	*Copilot key feature availability varies by market, see aka.ms/Keysupport
Accessories	1 year Limited warranty (Include 1 Year Global)