
## Key **Features**

- Simplify multi-monitor setups with USB-C daisy chain technology
- Integrated USB-C docking station with Ethernet and up to 100W power delivery
- Gen 2 USB 3.2 hub with USB-C upstream, USB-A\*3 and USB-C\*2 downstream ports, HDMI, and DisplayPort inputs for easy connectivity
- 100Hz refresh rate delivers fluid visuals
- Compact design using sustainable materials, with eco-friendly packaging



## Product **Description**

The VG2758-2K is a 27" QHD (2560 x 1440) USB-C docking monitor designed for business and home use. It features HDMI, DisplayPort, USB-C, USB-C out, Ethernet, and USB Type-A inputs, making connectivity simple. With USB-C daisy chain technology, you can connect additional monitors while transferring audiovisual, data, and up to 100W of power through a single cable. Display Stream Compression (DSC) compatibility ensures full USB 3.2 Gen 2 speeds when daisy-chaining to another QHD monitor. The monitor offers a 100Hz refresh rate, Eye ProTech+ eye care technology, and various ViewMode presets for enhanced performance and comfortable viewing. Effortlessly personalize your workspace with a VESA-compatible mount, allowing easy adjustments for ergonomic multitasking. Reflecting ViewSonic's commitment to sustainability, this monitor is designed for energy efficiency and features a compact build with a laser-textured finish, made from sustainable materials. It also comes in FSC-certified, 100% recyclable packaging that minimizes single-use materials.



## Visit Us

5. Power In

6. HDMI

www.viewsonic.com

13. Ethernet (RJ45)

12. USB Type A 3.2 DownStream

DISPLAY	
Display Size (in.):	27
Viewable Area (in.):	27
Panel Type:	IPS Technology
Resolution:	2560 x 1440
Resolution Type:	QHD (Quad HD)
Static Contrast Ratio:	1,500:1 (typ)
Dynamic Contrast Ratio:	80M:1
Light Source:	LED
Brightness:	350 cd/m² (typ)
Colors:	16.7M
Color Space Support:	8 bit true
Aspect Ratio:	16:9
Response Time (Typical GTG):	5ms
Response Time (GTG w/OD):	5ms
Viewing Angles:	178º horizontal, 178º vertical
Backlight Life (Hours):	30000 Hrs (Min)
Curvature:	Flat
Refresh Rate (Hz):	100
Low Blue Light:	Hardware solution
Flicker-Free:	Yes
Color Gamut:	NTSC: 76% size (Typ) sRGB: 108% size / 99% coverage (Typ)
Pixel Size:	0.233 mm (H) x 0.233 mm (V)
Surface Treatment:	Anti-Glare, Hard Coating (3H)
OMPATIBILITY	
PC Resolution (max):	2560x1440
Mac® Resolution (max):	2560x1440
PC Operating System:	Windows 10/11 certified; macOS tested
Mac® Resolution (min):	2560x1440
ONNECTOR	
USB 3.2 Type A Down Stream:	3
USB 3.2 Type C Down stream:	2 (15W power charger)
USB 3.2 Type C Down Stream; DisplayPort Alt mode: USB 3.2 Type C Up Stream;	1
DisplayPort Alt mode :	1 (98W power charger)
3.5mm Audio Out:	1
HDMI 2.0:	1
DisplayPort:	1
Power in:	3-pin Socket (IEC C14 / CEE22)
Ethernet LAN (RJ45):	1
AUDIO	
Internal Speakers:	2Watts x2
POWER	
Eco Mode (Conserve):	19.6W
Eco Mode (optimized):	23.9W
Consumption (typical):	29.3W
Consumption (max):	42W
Voltage:	AC 100-240V
Stand-by:	0.5W
Power Supply:	Internal Power Supply
DDITIONAL HARDWARE	
Kensington Lock Slot:	1
Cable Organization:	Yes
CONTROLS	
Physical Controls:	Joystick key: Up, Right, Down, Left, Center; Power
On Screen Display:	Input Select, Audio Adjust, ViewMode, Color Adjust, Manual Image Adjust, Setup Menu
OPERATING CONDITIONS	
Temperature:	32°F to 104°F (0°C to 40°C)
Humidity (non-condensing):	20% to 90%
WALL MOUNT	

VESA Compatible:

100 x 100 mm

INPUT SIGNAL		
Frequency Horizontal:	30 ~ 151KHz	
Frequency Vertical:	50 ~ 100Hz	
VIDEO INPUT		
Digital Sync:	TMDS - HDMI (v2.0), PCI-E - DisplayPort (v1.4), Micro-Packet - Type C	
ERGONOMICS		
Height Adjust (mm):	150	
Swivel:	90°	
Tilt (Forward/Back):	-5° / 30°	
Pivot (Right/Left):	90° / 90°	
WEIGHT (IMPERIAL)		
Net (lbs):	16.4	
Net Without Stand (lbs):	11	
Gross (lbs):	22.4	
WEIGHT (METRIC)		
Net (kg):	7.4	
Net Without Stand (kg):	5	
Gross (kg):	10.2	
DIMENSIONS (IMPERIAL) (WXHXD)		
Packaging (in.):	27.6 x 16.7 x 6.5	
Physical (in.):	24.12 x 15.84~20.69 x 8.6	
Physical Without Stand (in.):	24.12 x 14.16 x 1.76	
DIMENSIONS (METRIC) (WXHXD)		
Packaging (mm):	702 x 425 x 166	
Physical (mm):	612.6 x 402.32~525.64 x 218.47	
Physical Without Stand (mm):	612.6 x 359.77 x 44.75	
GENERAL		
Regulations:	cTUVus, FCC-B, ICES003, Energy Star, EPEAT, CEC, CB	
PACKAGE CONTENTS:	VG2758-2K x1, 3-pin Plug (IEC C13 / CEE22) x1, DisplayPort Cable (v1.4; Male-Male) x1, USB Type-C Gen2 Cable (Male-Male; with Type-A adapter) x1, Quick Start Guide x1	
Recycle/Disposal:	Please dispose of in accordance with local, state or federal laws.	
Warranty:	*Warranty offered may differ from market to market	
Power Management:	Energy Star standards, EPEAT	