



HP Elite t755 Thin Client (B5VK0UT)



Overview

Optimal thin client performance, reliability, and security

Enable productivity with the performance and reliability of the HP Elite t755 Thin Client, featuring advanced security from both cyber- and physical-based attacks for IT peace of mind. Built to support demanding performance with the progressive 6-core 45w AMD Ryzen™ V2546 Processor[1], helping users tackle mission-critical tasks.

Unleash maximum performance

Elevate efficiency with the progressive 45w AMD Ryzen™ V2546 Processor.[1] Optimized for mission-critical workflows, this fast-performing processor supports seamless productivity.

Built for mission-critical work

Empower your workforce with thin clients well-equipped with industrial-grade components for reliability and longevity while delivering a seamless user and management experience. Future-ready with expanded peripheral support and device management options.

Comprehensive security

Fortify critical security apps, data, and projects at the endpoints, wiping out data after each thin client log-in session. Get advanced protection from remote cyber- and physical attacks with a read-only OS and physical intrusion detection.

Help protect our shared future

The HP Elite t755 Thin Client uses at least 50 percent post-consumer recycled plastics, the keycaps contain 50 percent PCR DVDs[2], and the outside box and cushions are 100 percent sustainably sourced or recycled.[3]

[1] Multicore is designed to improve performance of certain software products. Not all customers or software applications will necessarily benefit from use of this technology. Performance and clock frequency will vary depending on application workload and your hardware and software configurations. AMD's numbering is not a measurement of clock speed.

[2] 100 percent outer box packaging made from sustainably sourced certified and recycled fibers. Fiber cushions made from 100 percent recycled wood fiber and organic material. Any plastic cushions are made from >90% recycled plastic.

[3] Recycled plastic content percentage is based on the definition set in the IEEE 1680.1-2018 standard.

Specifications

Operating system	Windows 11 IoT Enterprise 2024 LTSC
Processor	AMD Ryzen™ Embedded V2546 (up to 3.95 GHz max boost clock, 8 MB L3 cache, 6 cores, 12 threads)
Memory	8 GB DDR4-3200 MT/s (2 x 4 GB)
Memory Slots	2 SODIMM
Internal Storage	64 GB eMMC
Graphics	Integrated
Graphics (integrated)	AMD Radeon™ Graphics
Audio	Internal amplified speaker system for basic audio playback
Dimensions (W x D x H)	5 x 21 x 21 cm (Vertical orientation.)
Dimensions (W x D x H)	1.97 x 8.26 x 8.26 in (Vertical orientation.)
Weight	1.4 kg (Weight will vary depending on configuration.)
Weight	3 lb (Weight will vary depending on configuration.)
Keyboard	HP 125 Wired Keyboard
Pointing device	HP 125 Wired Mouse
Ports	1 USB Type-C® 10Gbps signaling rate; 2 USB Type-A 5Gbps signaling rate
Expansion slots	1 half-height PCIe x16 (x8)
Ports	2 USB Type-A 5Gbps signaling rate; 2 USB 2.0 Type-A; 4 DisplayPort™ 1.2; 1 RJ-45; 1 4.5 mm power adapter; 1 security lock slot
Wireless	Realtek RTL8852BE Wi-Fi 6 (2x2) and Bluetooth® 5.3 wireless card (supporting gigabit data rate)
Protocols	Amazon WorkSpaces through PCoIP; Citrix® HDX; Citrix® ICA; VMware Horizon® View™ through RDP/PCoIP, and Blast Extreme; Remote Desktop Services Remote FX (RFX), RDP; Azure Virtual Desktop; Windows 365
Power	90 W smart external power adapter
Ecolabels	EPEAT® registered
Energy star certified	ENERGY STAR® certified
Browser supported	Mozilla Firefox (for models with HP ThinPro); Microsoft Edge (for models with Windows 10 IoT Enterprise LTSC 2021)
UPC number	198990150406

Additional specifications

Bluetooth version	Bluetooth® 5.3
Datasheet photo 1	AHID/62cbb118cede4420ca96abaf95773876ced5f1f9
Datasheet photo 3	AHID/99664cda38ef83c9faba5f1a6cd101f2a9b3df38
Datasheet photo 4	AHID/7e6f5f486be71c6b106996d4514d03adfc2b5d5b
Datasheet photo 5	AHID/8a0cd71de064ae5126f2eeda78e0cd1f18fd7bdc
ECC memory	non-ECC
I/O Port location	Front
I/O Port location	Back
Keyboard connectivity	Wired
Memory layout (slots & size)	2 x 4 GB
Memory module type	SODIMM
Memory size	8
Memory size uom	GB
Memory speed	3200
Memory speed uom	MT/s
Memory type	DDR4
Number of memory slots	2
Processor Brand	AMD
Processor cache	8 MB L3
Processor core	6
Processor family	Ryzen™
Processor maximum frequency	3.9
Processor maximum frequency uom	GHz
Processor model	V2546
Processor threads	12
Software included	HP Easy Shell
Software included	HP Easy Update
Software included	HP Device Manager
Software included	HP USB Port Manager
Software included	HP User State Tool
Software included	HP Write Manager
Software included	Microsoft SCCM/EDM Agent
Software included	HP True Graphics

Software included	HP ThinUpdate
Software included	HP Smart Zero Client Services
Software included footnote number	[6,12,15]
Software included footnote number	[6,11,12,15]
Software included footnote number	[6,12,15]
Software included footnote number	[6,12,15]
Software included footnote number	[6,12,15]
Software included footnote number	[6,12,15]
Software included footnote number	[6,12,13,15]
Software included footnote number	[6,8,12,15]
Software included footnote number	[6,12,15]
Software included footnote number	[6,12,15]
Standard memory note	Transfer rates up to 3200 MT/s.
Storage capacity	64
Storage capacity uom 01	GB
Storage type	eMMC
Storage type 01	eMMC
UNSPSC code	43211506
Wireless Model	RTL8852BE
Wireless antenna	2x2
Wireless standard	Wi-Fi 6
Wireless supplier	Realtek
Wireless transfer speeds	Supporting Gigabit data rate

Accessories for PC

Components/Upgrades

★ : Recommended

Graphics

AMD Radeon RX 6300 2 GB GDDR6 FH DP+HDMI PCIe x16 Graphics	7Y6P7AA
--	---------

Memory

HP 16GB DDR4-3200 SODIMM	13L75AA
--------------------------	---------

HP 8GB DDR4-3200 SODIMM	13L77AA
-------------------------	---------

Storage

HP 256GB 2280 PCIe NVMe Value Solid State Drive	A92L2AA
---	---------

Internal ports/Modules/Controllers

HP PCIe x1 Parallel Port Card	N1M40AA
-------------------------------	---------

HP USB to Serial Port Adapter	J7B60AA
-------------------------------	---------

Intel I226-T1 2.5GbE Ethernet Network Adapter	9P1U8AA
---	---------

Keyboards/Other Input Devices

Wired Keyboards

HP 125 Wired Keyboard	266C9AA
-----------------------	---------

HP Wired Desktop 320K Keyboard	9SR37AA
--------------------------------	---------

HP Wired Desktop 320K Keyboard	9SR37UT
--------------------------------	---------

Wired Combo

HP 225 Antimicrobial Wired Mouse and Keyboard Combo	286K3AA
---	---------

HP 225 Wired Mouse and Keyboard Combo	286J4AA
---------------------------------------	---------

HP Wired Desktop 320MK Mouse and Keyboard	9SR36AA
---	---------

HP Wired Desktop 320MK Mouse and Keyboard	9SR36UT
---	---------

Wireless Combo

HP 235 Wireless Mouse and Keyboard Combo	1Y4D0AA
--	---------

HP 235 Wireless Mouse and Keyboard Combo	1Y4D0UT
--	---------

HP 655 Wireless Keyboard and Mouse Combo	4R009AA
--	---------

HP 655 Wireless Keyboard and Mouse Combo (Bulk 10)	4R009A6
--	---------

Wireless Keyboards

HP 455 Programmable Wireless Keyboard	4R177A6
HP 455 Programmable Wireless Keyboard	4R177AA
HP 975 Dual-Mode Wireless Keyboard	3Z726AA

Mice/Pens/Other Pointing Devices

Wired Mice

HP 125 Wired Mouse	265A9AA
HP 125 Wired Mouse	265A9UT
HP 125 Wired Mouse (Bulk120)	265A9A6
HP 128 LSR WRD Mouse (Bulk120)	265D9A6
HP 128 Laser Wired Mouse	265D9AA
HP Wired Desktop 320M Mouse	9VA80AA

Wireless Mice

HP 435 Multi-Device Wireless Mouse	3B4Q5AA
HP 635 Multi-Device Wireless Mouse	1D0K2AA
HP 715 Rechargeable Multi-Device Mouse	6E6F0AA
HP 925 Ergonomic Vertical Mouse	6H1A5AA
HP 935 Creator Wireless Mouse	1D0K8AA

Video Devices

Video Devices

HP 325 FHD Webcam	53X27AA
HP 435 FHD Webcam	77B10AA
HP 965 4K Streaming Webcam	695J5AA

Port Replicators/Dongles/Docking

Port Replicators

HP 4K USB-C Multiport Hub	6G843AA
HP 4K USB-C Multiport Hub	6G843UT
HP USB-C to USB-A Hub	Z6A00AA
HP Universal USB-C Multiport Hub	50H55AA
HP Universal USB-C Multiport Hub	50H55UT

Cables/Cable Adapters/Dongles

HP DisplayPort Cable Kit	VN567AA
HP DisplayPort To VGA Adapter	AS615AA
HP DisplayPort To VGA Adapter	F7W97AA
HP DisplayPort to DVI-D Adapter	FH973AA
HP DisplayPort to HDMI True 4K Adapter	2JA63AA
HP Pavilion USB-C to HDMI 2.0 Adapter	2PC54AA
HP USB 3.0 to Gigabit RJ45 Adapter G2	4Z7Z7AA
HP USB-C to DP Adapter	N9K78AA
HP USB-C to HDMI 2.0	1WC36AA
HP USB-C to RJ45 Adapter G2	4Z527AA
HP USB-C to USB 3.0 Adapter	N2Z63AA
HP USB-C to VGA Adapter	N9K76AA
HP USB-C to VGA Display Adapter	P7Z54AA

Docking

HP USB-C Dock G5	26D32AA
HP USB-C Dock G5	5TW10AA

Stands/Mounting Brackets

Mounting Brackets

HP Quick Release Bracket 2	6KD15AA
----------------------------	---------

Audio Devices

Headset Devices

HP Stereo 3.5mm Headset G2	428K7AA
HP Stereo USB Headset G2	428K6AA

Disclaimer — Copyright

Bluetooth is a trademark of its proprietor, used by HP Inc. under license. USB Type-C® and USB-C® are registered trademarks of USB Implementers Forum. ENERGY STAR is a registered trademark of the U.S. Environmental Protection Agency. DisplayPort™ and the DisplayPort™ logo are trademarks owned by the Video Electronics Standards Association (VESA®) in the United States and other countries. Bluetooth is a trademark of its proprietor and used by HP Inc. under license. AMD and Radeon are trademarks of Advanced Micro Devices, Inc.

© Copyright 2024 HP Development Company, L.P. The information contained herein is subject to change without notice. The only warranties for HP products and services are set forth in the express warranty statements accompanying such products and services. Nothing herein should be construed as constituting an additional warranty. HP shall not be liable for technical or editorial errors or omissions contained herein.

Generated by Dynamic Collateral Tool – (us-en) – Dec 07, 2024 12:30 PM UTC+0000