



Hospital TV UM672M Series

* All images in this datasheet are for illustrative purposes only.

UL-Listed Pro:Centric® Hospital TV



| UM672M Series | | 75/65/55/50/43UM672M0UE |
|---------------|---------------------|--|
| Design | Stand Type | No Stand (Wall Mount Only) |
| | Inch | 75" / 65" / 55" / 50" / 43" |
| Display | Resolution | 3,840 × 2,160 (4K UHD) |
| | Broadcasting System | Digital: ATSC, Clear QAM, Multicast/Unicast IPTV Analog: NTSC |
| VESA | | 75": 400 × 400 |
| | | 65" / 55": 300 × 300 |
| | | 50" / 43": 200 × 200 |



Pillow Speaker Ready

The hospital TV is equipped with a pillow speaker interface* which controls the TV volume and channels directly from the patient's bedside.

* Pillow speaker is not provided by LG. (Sold separately).

Nurse Call System Ready

By using a pillow speaker* connected to the UM672M Series,, the patient can immediately alert hospital staff from his or her own bed in case of emergency.

UL Hospital Grade Listed

This hospital TV is designed specifically for healthcare environments and meets UL-tested hospital safety standards.



Slim Depth for a Sleek Look

With a slimmer* design, the UM672M series integrates smoothly into hospital interiors.

* Compared to LG's previous hospital TV UT672M series.



Embedded b-LAN


The Hospital TV supports embedded broadband local area network (b-LAN), enabling PPV (Pay Per View) and VOD service without the need for a set-top box.



USB Cloning

USB data cloning makes managing multiple displays efficient. Instead of setting up each display one by one, data can be copied to a USB* Drive for one display, and be shared to the other displays through a USB plug-in.


* USB drive is not provided by LG (Sold Separately).



Multi-code IR

This LG model supports Multi-code IR* functionality which eliminates remote-control signal interaction among nearby TVs. Patients can freely control their own TVs without disturbing the others.

* Multi-code IR remote control is not provided by LG (Sold Separately).



Pro:Centric® Management Solution

Pro:Centric Direct is a content management solution providing simple editing tools that enable service and IP network-based remote management, allowing staff to efficiently manage all LG hospital TVs throughout the facility.

* Pro:Centric Direct solution is sold separately. Some features may not be supported based on PCD versions.



Integration Options: Works with Apple AirPlay® and Google Cast™

Available through license with LG’s contracted Healthcare Patient Engagement Providers, this service allows patients and guests to stream content directly from their wireless devices to the UM672M series using Apple AirPlay or Google Cast. Simply scan the room’s QR code to pair their devices and share movies, shows, photos, games, and more during the guest’s stay. Pairing is always private and temporary.








Integration Options: Built-in Netflix® and LG Channels

Available through license with LG’s contracted Healthcare Patient Engagement Providers, this service allows patients and guests to experience a wide variety of their Netflix account’s content and over 95 free TV channels with the LG Channels application. Patients can enjoy the comfort of their room with streaming services that offer a thousands of selections.

* Netflix membership required.


DIMENSIONS



CONNECTIVITY


75"

Rear




65" / 55" / 50" / 43"

Rear



75" / 65" / 55" / 50" / 43"

Side



SPECIFICATIONS

| | | 75UM672M0UE | 65UM672M0UE | 55UM672M0UE | 50UM672M0UE | 43UM672M0UE |
|-----------------------------|---|--|---|---|---|---|
| Category | Category | Pro:Centric Smart | Pro:Centric Smart | Pro:Centric Smart | Pro:Centric Smart | Pro:Centric Smart |
| Design | Stand Type | No Stand (Wall Mount Only) | No Stand (Wall Mount Only) | No Stand (Wall Mount Only) | No Stand (Wall Mount Only) | No Stand (Wall Mount Only) |
| | Front Color | Dark Charcoal Gray | Dark Charcoal Gray | Dark Charcoal Gray | Dark Charcoal Gray | Dark Charcoal Gray |
| Display | Size | 75" | 65" | 55" | 50" | 43" |
| | Resolution | 3,840 × 2,160 (4K UHD) | 3,840 × 2,160 (4K UHD) | 3,840 × 2,160 (4K UHD) | 3,840 × 2,160 (4K UHD) | 3,840 × 2,160 (4K UHD) |
| | Brightness (Typ.) | 330 nits | 330 nits | 330 nits | 330 nits | 265 nits |
| | HDR 10 Pro / HLG | Yes / Yes | Yes / Yes | Yes / Yes | Yes / Yes | Yes / Yes |
| | Game Optimizer | Yes | Yes | Yes | Yes | Yes |
| Audio | Speaker (Audio Output) | 20 W | 20 W | 20 W | 20 W | 20 W |
| | AI Sound | Yes | Yes | Yes | Yes | Yes |
| | AI Acoustic Tuning | Yes (Ready, MMR Required) | Yes (Ready, MMR Required) | Yes (Ready, MMR Required) | Yes (Ready, MMR Required) | Yes (Ready, MMR Required) |
| | LG Sound Sync | Yes | Yes | Yes | Yes | Yes |
| Broadcasting System | Digital | ATSC / Clear QAM | ATSC / Clear QAM | ATSC / Clear QAM | ATSC / Clear QAM | ATSC / Clear QAM |
| | Analog | NTSC | NTSC | NTSC | NTSC | NTSC |
| | IPTV | Multicast/Unicast IPTV | Multicast/Unicast IPTV | Multicast/Unicast IPTV | Multicast/Unicast IPTV | Multicast/Unicast IPTV |
| Content Solution | Solution Type | Pro:Centric (Smart, Cloud, Direct, V, Server), webRTC | Pro:Centric (Smart, Cloud, Direct, V, Server), webRTC | Pro:Centric (Smart, Cloud, Direct, V, Server), webRTC | Pro:Centric (Smart, Cloud, Direct, V, Server), webRTC | Pro:Centric (Smart, Cloud, Direct, V, Server), webRTC |
| | Pro:Idiom (DRM / Media) | Yes / Yes | Yes / Yes | Yes / Yes | Yes / Yes | Yes / Yes |
| Smart Function | webOS23, Web Browser, Magic Remote Compatibility (Ready), Multi-View, Gallery Mode, Wi-Fi, Bluetooth, SoftAP, Screen Share, DIAL, Bluetooth Audio Playback, HDMI eARC/ARC (HDMI2), Voice Recognition (Standalone/Solution), IoT | | | | | |
| Features | First Use Wizard, Hospital Settings, USB Cloning, Wake on RF, WOL, Diagnostics (IP Remote), Simplink (HDMI-CEC (1.4)), IR Out (RS-232C, MPI), Multi-code IR, Installer Menu, Welcome Screen (Splash Image), Insert Image, One Channel Map (LCM), Instant ON, VLAN ID, Mobile Remote, Port Block, Lock Mode (Limited), RJP (Remote Jack Pack) Compatibility, Embedded b-LAN, Energy Saving Mode, Pillow Speaker Support, NTP Sync Timer, BEACON, Video Tag (2) | | | | | |
| Connectivity | Side | HDMI 2 (eARC/ARC), HDMI 3, USB 1 (2.0), RS-232C In (Control & SVC) (3.5 mm TRRS), Speaker Out / Line Out (3.5 mm TRS) | | | | |
| | Rear | TV-Link CFG (3.5 mm TRS), Service Only (3.5 mm TRS), MPI Port (RJ12), Pillow Speaker Interface (6 Pin), RF In, Digital Audio Out (Optical), RJ45 (Ethernet), HDMI 1, USB 2 (2.0) | | | | |
| Mechanical | VESA Compatible | 400 × 400 mm | 300 × 300 mm | 300 × 300 mm | 200 × 200 mm | 200 × 200 mm |
| | Kensington Lock | Yes | Yes | Yes | Yes | Yes |
| | Dimensions (W × H × D) | 66.1 × 38.0 × 2.4 in. 1,678 × 964 × 59.9 mm | 57.3 × 32.9 × 2.3 in. 1,454 × 838 × 57.7 mm | 48.6 × 28.1 × 2.3 in. 1,235 × 715 × 57.5 mm | 44.1 × 25.6 × 2.3 in. 1,121 × 651 × 57.1 mm | 38.1 × 22.2 × 2.3 in. 967 × 564 × 57.1 mm |
| | Shipping Dimensions (W × H × D) | 71.7 × 43.9 × 7.9 in. 1,820 × 1115 × 200 mm | 62.9 × 38.2 × 6.8 in. 1,600 × 970 × 172 mm | 53.5 × 31.9 × 6.4 in. 1,360 × 810 × 162 mm | 47.8 × 30.5 × 5.9 in. 1,215 × 775 × 152 mm | 41.5 × 25.9 × 5.6 in. 1,055 × 660 × 142 mm |
| | Weight | 69.2 lbs. / 31.4 kg | 47.4 lbs. / 21.5 kg | 30.9 lbs. / 14.0 kg | 26.8 lbs. / 12.1 kg | 19.4 lbs. / 8.8 kg |
| | On Bezel Width (L/R/T/B) | 13.9 / 13.9 / 13.9 / 19.9 mm | 12.8 / 12.8 / 12.8 / 19.9 mm | 12.8 / 12.8 / 12.8 / 19.9 mm | 12.8 / 12.8 / 12.8 / 19.9 mm | 12.8 / 12.8 / 12.8 / 19.9 mm |
| | Off Bezel Width (L/R/T/B) | 7.9 / 7.9 / 7.9 / 18.4 mm | 6.8 / 6.8 / 6.8 / 18.4 mm | 6.9 / 6.9 / 6.9 / 18.4 mm | 7.3 / 7.3 / 7.8 / 18.4 mm | 6.9 / 6.9 / 6.9 / 18.4 mm |
| Electrical | Power Supply Voltage, Frequency | 100-240 Vac, 50/60 Hz | 100-240 Vac, 50/60 Hz | 100-240 Vac, 50/60 Hz | 100-240 Vac, 50/60 Hz | 100-240 Vac, 50/60 Hz |
| | Power Consumption (Typ. / Max.) | 228 W / 202 W | 180 W / 144 W | 163 W / 135 W | 135 W / 112 W | 119 W / 82 W |
| | Standby Power Consumption | Under 0.5 W | Under 0.5 W | Under 0.5 W | Under 0.5 W | Under 0.5 W |
| Warranty & Other | Warranty | 3 Year Limited | | | | |
| | UPC | 1 95174 09207 1 | 1 95174 09206 4 | 1 95174 09205 7 | 1 95174 09204 0 | 1 95174 09203 3 |
| | Safety | Hospital UL | Hospital UL | Hospital UL | Hospital UL | Hospital UL |
| | EMC | FCC | FCC | FCC | FCC | FCC |
| | Power Cable | Yes, 1.8m (Straight 3-Conductor C5 Connector to Right-Angle AC Wall Plug for Early Models; Right-Angle 3-Conductor C5 Connector to Right-Angle AC Wall Plug for Later Models) | | | | |

* Specifications are subject to change without notice, so please contact LG sales team to verify before ordering.

Life's Good.

#LoveWhatYouSeeLG    @LGforBusinessUSA

Copyright 2025 ©LG Electronics USA, Inc., 2000 Millbrook Drive Lincolnshire, IL 60069, USA. All rights reserved. LG and the LG logo are registered trademarks of LG Corp. All other products and brand names are trademarks or registered trademarks of their respective companies. Designs, features, and specifications are subject to change without notice. All screen images are simulated for illustrative purposes only. SPEC_UM672M_0825_4.0A

