

## VP2788-5K - 27" COLORPRO 5K MAC-COMPATIBLE MONITOR WITH 100W THUNDERBOLT 4, USB C, AND DCI-P3 COLOR GAMUT

### Key Features

---

- 27-Inch 5K (5120x2880p) IPS Mac-ready monitor with 75Hz refresh rate
- Thunderbolt 4 lets you enjoy lightning-fast data transfer speeds of up to 40 Gbps while delivering up to 100W of power
- Enhance your 5K dual monitor setup with a frameless design and daisy chain via Thunderbolt 4
- 100% sRGB, 99% DCI-P3 colors, and HDR400 for deep contrasts that align perfectly with Mac's industry-leading color performance
- Advanced ergonomics (tilt, swivel, pivot, and height adjustment) for all-day comfort
- The VP2788-5K supports laptops, PCs, Macs, and more with Thunderbolt 4, USB-C, HDMI, DisplayPort, and USB inputs



27  
DISPLAY



IPS  
PANEL



5120 x 2880  
RESOLUTION



### Product Description

---

Elevate your MacBook experience with the powerful ViewSonic® ColorPro® VP2788-5K, a sleek 27" monitor designed to integrate seamlessly into your Mac ecosystem. Featuring stunning 5K resolution and a 99% DCI-P3 color gamut, it provides vibrant and precise visuals to complement Apple's renowned color performance. Seamless Thunderbolt 4 connectivity provides ultra-fast data transfer and up to 100W charging through a single cable, while also supporting daisy chaining of up to two 5K monitors for a seamless multi-display setup. Additional HDMI and DisplayPort options offer unmatched flexibility for various devices. In addition, an integrated USB-C and USB-A hub allows for connecting accessories and quick charging of your iPhone or iPad. A fully ergonomic stand allows you to customize height, tilt, and swivel for maximum comfort during long hours of use. Whether you're designing, editing, or enjoying media, this monitor's exceptional performance transforms your workspace into a powerhouse of productivity with immersive visuals.

# Specifications

|                                    | More Information                                   |
|------------------------------------|--|
| <b>UPC</b>                         | 766907029505                                       |
| <b>Screen Size</b>                 | 27   |
| <b>Viewable Area (in.)</b>         | 27   |
| <b>Panel Type</b>                  | IPS  |
| <b>Display Resolution</b>          | 5120 x 2880  |
| <b>Display Resolution</b>          | 5K (5120 x 2880)                                   |
| <b>Static Contrast Ratio</b>       | 2,000:1  |
| <b>Light Source</b>                | LED  |
| <b>Brightness</b>                  | 500 cd/m2  |
| <b>Color Space Support</b>         | 10 bit (8 bit + FRC)                               |
| <b>Aspect Ratio</b>                | 16:9   |
| <b>Response Time (Typical GTG)</b> | 14ms   |
| <b>Viewing Angles</b>              | 178° horizontal, 178° vertical                     |
| <b>Backlight Life (Hours)</b>      | 30,000   |
| <b>Panel Surface</b>               | Anti-Glare, Low-Reflection, 48% Haze               |
| <b>Refresh Rate</b>                | 75Hz   |
| <b>PC Resolution (max)</b>         | 5120 x 2880  |
| <b>Mac® Resolution (max)</b>       | 5120 x 2880  |
| <b>USB Type A</b>                  | 2  |
| <b>USB Type C</b>                  | 2 [1 upstream (15W) / 1 downstream (15W)]          |
| <b>HDMI 2.1 In</b>                 | 1  |
| <b>DisplayPort</b>                 | 1  |
| <b>Thunderbolt 4</b>               | 2 [1 upstream(100W) / 1 downstream (15W)]          |
| <b>Internal Speakers</b>           | 5W (x2)  |
| <b>Eco Mode (Conserve)</b>         | 232 w/Audio/USB; 37 w/o Audio/USB                  |
| <b>Eco Mode (optimized)</b>        | 236 w/Audio/USB; 41 w/o Audio/USB                  |
| <b>Consumption (typical)</b>       | 242 w/Audio/USB; 47 w/o Audio/USB                  |
| <b>Consumption (max)</b>           | 245 w/Audio/USB; 50 w/o Audio/USB                  |
| <b>Voltage</b>                     | 100-240 VAC  |
| <b>Stand-by</b>                    | 0.5  |
| <b>Power Supply</b>                | External   |
| <b>Cable Organization</b>          | No   |
| <b>Physical Controls</b>           | Joystick key: Up, Right, Down, Left, Center; Power |

|                                     |   |
|-------------------------------------|---|
| <b>On Screen Display</b>            | Input Select, Color Mode, ViewMode, Audio Adjust, Setup Menu  |
| <b>Temperature</b>                  | 32-104° F (0 - 40° C)   |
| <b>Humidity (non-condensing)</b>    | 20-90%  |
| <b>VESA Compatible</b>              | 100 x 100 mm  |
| <b>Height Adjust</b>                | 120 mm / 4.7 in   |
| <b>Swivel</b>                       | 60°   |
| <b>Pivot (Right/Left)</b>           | 90° / 90°   |
| <b>Tilt (Forward/Back)</b>          | 5° / 22°  |
| <b>Regulations</b>                  | cTUVus, FCC-B, ICES003, Energy Star 8.0, EPEAT Silver, CEC  |
| <b>Net (lbs)</b>                    | 14.0  |
| <b>Net Without Stand (lbs)</b>      | 9.3   |
| <b>Gross (lbs)</b>                  | 23.4  |
| <b>Net (kg)</b>                     | 6.4   |
| <b>Net Without Stand (kg)</b>       | 4.2   |
| <b>Gross (kg)</b>                   | 10.6  |
| <b>Packaging (in.)</b>              | 28.7 x 20.3 x 6.3   |
| <b>Physical (in.)</b>               | 24.13 x 16.72~21.44 x 8.26  |
| <b>Physical Without Stand (in.)</b> | 24.13 x 14.46 x 2.26  |
| <b>Packaging (mm)</b>               | 730.0 x 515.0 x 159.0   |
| <b>Physical (mm)</b>                | 612.94 x 424.73~544.55 x 209.91   |
| <b>Physical Without Stand (mm)</b>  | 612.94 x 367.23 x 57.5  |
| <b>Package Contents</b>             | VP2788-5K x1, 3-pin Plug (IEC C13 / CEE22) x1, DisplayPort Cable (v1.4; Male-Male) x1, HDMI Cable (v2.1; Male-Male) x1, TBT4 Cable (Male-Male) x1, USB Type-C to Type-A 3.2 Gen2 Cable (Male-Male) x1, AC/DC Adapter x1, Quick Start Guide x1 |
| <b>Recycle/Disposal</b>             | Please dispose of in accordance with local, state or federal laws.  |
| <b>Warranty</b>                     | Three-year limited warranty on parts, labor and backlight   |

UPC: 766907029505



### Contact Sales

[ViewSonic.com](https://www.viewsonic.com)

888.881.8781

email:

[salesinfo@viewsonic.com](mailto:salesinfo@viewsonic.com)