

Eaton EVMA1530A

Catalog Number: EVMA1530A

Eaton Managed G4 Rack PDU, 0U, 39U, L15-30 input, 10ft cord, 8.6kW, 30A, 208V, 24 outlets (12)C13 (12)C39

General specifications

Product Name	Catalog Number
Eaton Managed Rack PDU	EVMA1530A
UPC	Product Length/Depth
786689801496	2.05 in
Product Height	Product Width
68.1 in	2.09 in
Product Weight	Compliances
12.4 lb	FCC part 15 class A
	CAN ICES-003 class A
Certifications	
UL 62368-1	
cTUVus	



Product specifications

Resources

Cord length

10 ft

Phase

Three-phase

Input voltage

208V

Form factor

0U (Vertical)

Operating Temperature

0° to 60°C (32° to 140°F)

Ethernet interface

Yes

Input connection

L15-30P

Outlets

(12) C13, (12) C39



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2023 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)