



[DOWNLOAD SPECS](#)

# PIXMA PRO-200S

## Printer Overview

Printer Type	Professional 13" Wireless Inkjet Photo Printer with 8-Dye Colour Inks
Printer Functions	Wireless <sup>1</sup> , Ethernet, USB Print, Cloud Integration Service <sup>3</sup>
Ideal For	Graphic Art Printing, Photo Printing up 13" x 19" and panorama, Black & White Printing, Studio Photo Printing, Home Photo Printing, Graphic Artists, Professional Photographers

## Print

Print Features	Wireless Printing <sup>1</sup> , Fast Photo Printing <sup>11</sup> , Advanced Pattern Print, Black & White Photo Printing Mode, Borderless Printing <sup>6</sup> , Disc Label Printing, Contrast Reproduction, Paper Feed Skew Correction, Photo Printing, Grayscale Photo Printing, Index Print, Square Photo Printing, Gallery Wrap Printing
----------------	------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------

Printing Capability	Single Sided (Simplex) Printing, Borderless <sup>6</sup> Photo Printing (3.5" x 5" to 13" x 19")
Print Speed (ESAT) <sup>10</sup>	<b>11" x 14" Bordered Colour Photo (A3+):</b> Approx. 1 Minutes, 30 Seconds <b>8" x 10" Bordered Colour Photo (A4):</b> Approx. 53 Seconds
Print Head	FINE (Full-photolithography Inkjet Nozzle Engineering) Print Head <b>User Replaceable:</b> Yes
Number of Nozzles	768 Nozzles x 8 Inks <b>Total:</b> 6,144
Picoliter Size	Minimum 4 Picoliters
Print Resolution <sup>11</sup>	<b>Colour:</b> Up to 4800 x 2400 dpi
Media Handling	Top Feed, Manual Feed Slot & CD / DVD Printing Tray
Supported Paper Sizes	3.5" x 3.5" (Square), 3.5" x 5", 4" x 6", 5" x 5" (Square), 5" x 7", 7" x 10", 8" x 10", Letter (8.5" x 11"), Legal (8.5" x 14"), 10" x 12", 11" x 17" (Ledger), 12" x 12" (Square), 13" x 19" (A3+), 210 x 594mm (Panorama Size), Custom (up to 13" x 39")
Genuine Canon Media Compatibility	<b>Plain:</b> Plain Paper <b>Super High Gloss:</b> Photo Paper Pro Platinum <b>Glossy:</b> Photo Paper Plus Glossy II, Photo Paper Glossy <b>Semi-Gloss:</b> Photo Paper Plus Semi-Gloss, Photo Paper Pro Luster <b>Matte:</b> Matte Photo Paper, Photo Paper Premium Matte <b>Fine Art:</b> Premium Fine Art Rough <b>Other:</b> Printable Nail Stickers, Light Fabric Iron Transfers <b>Non-Canon:</b> Inkjet Greeting Cards, Photo Stickers, Cardstock, Printable CD / DVD / Blu-ray Discs, Recycled paper and chlorine-free paper can be used
Paper Capacity	<b>Top Feed:</b> - Plain Paper: 100 Sheets (Letter Size) - Photo Paper: 4" x 6": 20 Sheets, 8.5" x 11" (Letter) / 8" x 10": 10 Sheets, 13" x 19" (A+): 1 Sheet <b>Manual Feed Slot:</b> - Photo Paper: All Sizes: 1 Sheet <b>CD / DVD Printing Tray:</b> - 1 Printable CD / DVD / Blu-Ray Disc
Supported Media Thickness / Weight	<b>Top Feed:</b> - Plain Paper: 64 - 105 gsm - Photo Paper: Approx. 380 gsm (Canon Genuine Media)

Manual Feed Slot:

- Photo Paper: Approx. 380 gsm / 0.1 - 0.6 mm (Canon Genuine Media)

Ink Information

Ink System	8 Individual Dye-Based Ink System, ChromaLife100+ System
Ink Types	CLI-65 Dye-Based Ink Tanks
Ink Tanks	CLI-65 BK (Black) CLI-65 GY (Gray) CLI-65 LGY (Light Gray) CLI-65 C (Cyan) CLI-65 PC (Photo Cyan) CLI-65 M (Magenta) CLI-65 PM (Photo Magenta) CLI-65 Y (Yellow)
Ink Fill Volume	<b>CLI-65:</b> 12.6 ml (each)

General

Connectivity	Hi-Speed USB Wi-Fi® (Dual-Band) / Wireless <sup>1</sup> Ethernet 10 / 100
Wireless Information	<b>Wireless Standard:</b> IEEE 802.11 b/g/n/a/ac <b>Wireless Security:</b> WPA-PSK, WPA2-PSK, WEP64 <b>Wireless LAN Frequency Band:</b> 2.4 GHz / 5.0 GHz <b>Wireless Direct Connection Capable:</b> Yes
Display	3.0-Inch Colour LCD
OS Compatibility	<b>Windows:</b> <sup>12</sup> Windows® 11, Windows10, Windows 8.1, Windows 7 <b>Mac:</b> <sup>13</sup> Mac OS® v14 – macOS v11.7.10 <b>Mobile Operating Systems:</b> <sup>14</sup> iOS®, Android™, Windows 10 Mobile

Mobile Apps & Plug-ins (iOS®/ Android™)

AirPrint®<sup>5</sup>, Mopria Print Service®<sup>8</sup>, Canon PRINT app<sup>7</sup>, Canon Print Service (Android Only)

Software & Plug-in (Windows<sup>22</sup> / Mac<sup>23</sup>)

PIXMA PRO-200S Wireless 13" Professional Inkjet Photo Printer Driver  
Canon Professional Print & Layout Software<sup>2</sup>  
Media Configuration Tool

General Features

Auto Paper Width Detection, Auto Power On/Off, Auto/Manual Print Head Alignment, Driver Correction Mode, Multi-Purpose Tray, Paper Feed Skew Correction, Quiet Mode, Custom MIB (Management Information Base) Support, Optimum Image Generating (OIG) System

Supported Languages

**33 Supported Languages:** Bulgarian, Chinese (Simplified), Chinese (Traditional), Croatian, Czech, Danish, Dutch, English, Estonian, Finnish, French, German, Greek, Hungarian, Indonesian, Italian, Japanese, Korean, Latvian, Lithuanian, Norwegian, Polish, Portuguese, Romanian, Russian, Slovak, Slovene, Spanish, Swedish, Thai, Turkish, Ukrainian, Vietnamese

Firmware

**Printer Language:** Swift Graphic Raster  
**Raster Job Control Language:** IVEC  
**Status Reply:** IVEC

Power Consumption

**Energy Efficiency:** Energy Star® Certified  
**Auto Power On / Off Capable:** Yes  
**Input Voltage:** AC 100 – 240 V, 50 / 60 Hz  
**Power Consumption:** 1.6W<sup>15</sup> (1.0W Standby, 0.2W Off)

Sound Management

**Quiet Mode:** Available  
**Level:** Approx. 42.2 dB(A)<sup>16</sup> (Canon PT-201 Paper)

Operating Environment<sup>17</sup>

**Operating Temperature:** 41° - 95° F (5° - 35° C)  
**Operating Humidity:** 10 - 90% RH

Printer Dimensions (Closed)

25.2" (L) x 15" (W) x 7.9" (H)

Printer Weight

32 lbs.

Warranty<sup>18</sup>

Warranty

1-Year Limited Warranty

