



[DOWNLOAD SPECS](#)

# MegaTank MAXIFY GX5120

## Print

Printer Functions	Print
Print Features	Document Printing, Photo Printing, Wireless Printing <sup>8</sup> , Mobile Device Printing, Business Card Printing, Greeting Card Printing, Label Printing, Square Media Printing Support, Double-sided Matte Paper Support, Auto Duplex Printing
Printing Capability	Single Sided (Simplex / Duplex) Printing
Fast First Print Out (FPOT) <sup>9</sup>	As fast as 8 Seconds (from Ready Mode / Simplex / Colour)
Print Speed (ESAT) <sup>9</sup>	<b>Black Document (Letter) Simplex:</b> Approx. 24.0 ipm <b>Colour Document (Letter) Simplex:</b> Approx. 15.5 ipm
Print Resolution <sup>10</sup>	Up to 1200 x 600 dpi
Number of Nozzles	<b>Colour (C/M/Y):</b> 1,024 x 3 <b>Pigment Black:</b> 1,280

**Total:** 4,352

Duty Cycle	Up to 45,000 Pages / Month
Media Handling	<b>1 Cassette :</b> 250 Sheets <b>1 Rear Tray :</b> 100 Sheets OR 20 Sheets 4" x 6"
Supported Paper / Media Sizes	4" x 6", 5" x 5" (Square), 5" x 7", 7" x 10", 8" x 10", Letter (8.5" x 11"), Legal (8.5" x 14"), U.S. #10 <b>Custom Size:</b> Width: 3.5" - 8.5" / Length: 5" x 47"
Canon Paper / Media Compatibility	<b>Plain:</b> Plain Paper, Canon High Resolution Paper <b>Glossy:</b> Photo Paper Plus Glossy II, Photo Paper Glossy <b>Semi-Gloss:</b> Photo Paper Plus Semi-Gloss, Photo Paper Pro Luster <b>Matte:</b> Matte Photo Paper, Double-sided Matte Paper <b>Other (Canon):</b> Magnetic Photo Paper, Restickable Photo Paper <b>Other (non-Canon):</b> Cardstock, Greeting Card, U.S. #10 Envelopes, Recycled paper and Chlorine-free paper can be used
Supported Media Thickness / Weight	<b>Rear Tray:</b> - Plain Paper: 64 - 105 gsm OR - Canon Paper: Max. approx. 275 gsm (Canon PT-101 Media) <b>Bottom Cassette:</b> - Plain Paper: 64 - 105 gsm

## Ink Information

Ink system & Information	4-Colour Pigment Continuous Ink Supply System (CISS), FINE Print Heads, Integrated Ink Tanks, 'Squeeze-Free' Ink Bottles For Easy & Mess Free Ink Filling, Unique Colour Bottle Tip Shape for Correct Filling Every Time
Ink Type	GI-26 Pigment-Based Ink Bottles (Cyan, Magenta, Yellow, Black)
Ink tank & Fill volume	<b>GI-26 Black Ink Bottles:</b> 167.0 ml <b>GI-26 C, M, Y Ink Bottles:</b> 132.0 ml (each)
High Page Yield <sup>7</sup>	Up to 6,000 (Black & White) / 14,000 (Colour) Pages (Per Full Ink Bottle Set)

## Connectivity & Software / Apps

Connectivity Options	Hi-Speed USB Wi-Fi® (Wireless LAN, 2.4/5 GHz, IEEE 802.11b/g/n/a/ac) <sup>8</sup> Wired LAN (100BASE-TX) / 10BASE-T
Wireless Information	<b>Standard:</b> IEEE 802.11 b/g/n/a/ac <b>Security:</b> WPA-PSK(AES), WPA2-PSK(AES), WPA3-SAE(AES), WPA-EAP(AES), WPA2-EAP(AES), WPA3-EAP(AES) <b>Wireless LAN Frequency Band(s):</b> 2.4 GHz / 5 GHz <b>Wireless Direct Connection Capable / Wireless Connect<sup>1</sup> Capable:</b> Yes
OS Compatibility	<b>Windows:</b> <sup>15</sup> Windows 11, Windows® 10, Windows 8.1, Windows 7 SP1 <b>Mac:</b> <sup>16</sup> macOS v10.12.6 - 10.15 (Catalina) <b>Mobile Operating Systems:</b> <sup>17</sup> iOS®, iPadOS, Android™
Smart Assistant Support <sup>18</sup>	Amazon Alexa™
Mobile printing Solutions & Apps (iOS® / Android™)	AirPrint® <sup>3</sup> , Mopria® Print Service <sup>4</sup> , Canon PRINT app <sup>2</sup> , Easy PhotoPrint Editor App <sup>19</sup> , PIXMA Cloud Link <sup>2</sup> , Creative Park App <sup>21</sup>
Software (Windows <sup>15</sup> / Mac <sup>16</sup> )	GX5120 Driver, Easy-PhotoPrint Editor Software <sup>19</sup> , PosterArtist <sup>22</sup>

## General

General Features	Auto Power On/Off, Print/Scan/Copy, Quiet Mode, Wireless Direct Connection <sup>1</sup> , Wireless Connect <sup>1</sup> , Auto Paper Width Detection, User Replaceable Print Head, User Replaceable Maintenance Cartridge
Display	2 Line Screen LCD
Supported languages	<b>33 Supported Languages:</b> Japanese, English (mm & inch), German, French, Italian, Spanish, Portuguese, Dutch, Danish, Norwegian, Swedish, Finnish, Russian, Ukrainian, Polish, Czech, Slovene, Hungarian, Slovak, Croatian, Romanian, Bulgarian, Turkey, Greek, Estonian, Latvian, Lithuanian, Simplified Chinese, Korean, Traditional Chinese, Indonesian, Vietnamese

Power Information	<div>Energy Efficiency: Energy Star® Certified<sup>24</sup></div> <div>Auto Power On / Off Capable: Yes</div> <div>Input Voltage: AC 100 – 240 V, 50 / 60 Hz</div> <div>Power Consumption: 20W (0.9W Standby / 0.6W Off)</div> <div>TEC (Typical Electricity Consumption): 0.16 kWh</div>
Sound Management	<div>Quiet Mode: Available</div> <div>Noise Level: Approx. 49.0 dB(A) (Plain Paper)</div>
Operating Environment <sup>23</sup>	<div>Operating Temperature: 41° - 95° F (5° - 35° C)</div> <div>Operating Humidity: 10 - 90% RH</div>
Dimensions (Closed)	15.8" (L) x 16.4" (W) x 9.4" (H)
Weight	25.6 lbs.
Warranty*	
Waranty	3-Year or 80,000 Page* Limited Warranty