



L A P T O P S

Stealth 18 AI Studio

STEALTH 18 AI STUDIO A1VHG-019US

Specification

Manufacturer Part #	STEALTH18A1019
OS	Windows 11 Home (MSI recommends Windows 11 Pro for business)
CPU	Intel® Core™ Ultra9-185H
CPU Speed	3.8-5.1 GHz
Chipset	-
Color	Midnight Black
Screen Size	18" QHD+(2560x1600) 240Hz 100% DCI-P3
Resolution	2560x1600 16:10
GPU	NVIDIA® GeForce RTX™ 4080 Laptop GPU
Video Memory	12G GDDR6
Keyboard	SteelSeries per-Key RGB with Anti-Ghost key (99 Key)
Speaker	Sound by Dynaudio, 2x2W Speaker, 4x2W Woofer
Memory	32GB (16GB*2) DDR5 5600MHz
HDD Capacity	1TB NVMe SSD Gen4x4
HDD Interface	NVMe
LAN	Killer E3100G
WLAN	Killer WiFi 7 BE1750
Bluetooth	BT 5.4
Card Reader	Micro SD 4.0
Webcam	IR FHD w/shutter
USB	2x USB 3.2 Gen2
Type-C Port	1x Thunderbolt™ 4 w/DP2.1&PD; 1x USB 3.2 Gen 2/DP
Video Port	HDMI v2.1,
Audio Port	1 Audio Combo (1/8")
AC Power Adaptor	280W
Battery Pack	4 cell (99.9Whr) Li-Ion
Dimension	15.74"x 11.41"x 0.94"
Weight	6.39 lbs
Copilot+ Ready	*Copilot key feature availability varies by market, see aka.ms/Keysupport
Manufacturer Warranty	1 year Limited warranty (Include 1 Year Global)