



The product images are for illustration purposes only. Actual product appearance, ports, keyboard layout, and accessories may vary by model.

- Intel Core Ultra 9 275HX, 24C (8P + 16E) / 24T, Max Turbo up to 5.4GHz, 36MB Intel Smart Cache
- 2x 32GB CSODIMM DDR5-6400
- 2x 1TB SSD M.2 2280 PCIe 4.0x4 NVMe
- NVIDIA GeForce RTX 5080 16GB GDDR7, Boost Clock 2287MHz, TGP 175W, 1334 AI TOPS
- Windows 11 Pro, English
- Case color - Eclipse Black
- 1-year, Courier or Carry-in

Premium Care - Advanced Support from Real People. Real Fast.



REAL PERSON

Choose how you want to reach us - through the phone, chat or email - our expert technicians will take care of you.



REAL FAST

Highly trained technicians will provide you real-time solutions, whatever the issue, on your first contact. If needed, our team will schedule an onsite visit for the next business day.



HASSLE FREE

‘Getting started’ and ‘how-to’ assistance for hardware and software. Easy solutions that are simple to reach - that’s how Premium Care delivers you the ideal support experience.



PC HEALTH CHECK

Free annual PC Health Check that allows our experts to spot issues before you do so they can resolve them quickly and help you avoid PC problems.

Accidental Damage Protection - Protection of your PC from the unexpected.

Experience shows that a significant portion of devices may be damaged (and not covered under warranty) in the first three years. Lenovo’s Accidental Damage Protection service covers accidents beyond the system warranty such as drops, spills, bumps and even electrical surges. Make sure your new device has maximum protection, avoid unplanned costs and get peace of mind.

Base Warranty – Included with the systems you purchase, default 1- or 3-year coverage window.

Warranty Extensions & Upgrades – Service and protection that’s right for your circumstances.

- Pick Up & Return Courier
- Onsite Support
- Technician Installed Customer
- Replaceable Unit Service
- International Warranty Upgrade

Recommended Accessories Netherlands



Lenovo Wireless Headphone 2000

GXD1W20502



ThinkPad Bluetooth Presenter Mouse (Aura Edition)

4Y51T62792



Lenovo 16" Laptop Everyday Backpack B510

4X41U80414

>> [View More Accessories](#)

Recommended Services

Best

3Y Premium Care with Onsite upgrade from 1Y Courier/Carry-in (5WS0T73708)

Better

3Y Onsite upgrade from 1Y Courier/Carry-in (5WS0K76356)

Good

3Y Courier/Carry-in upgrade from 1Y Courier/Carry-in (5WS0K76347)

PERFORMANCE

Processor

Intel Core™ Ultra 9 275HX, 24C (8P + 16E) / 24T, Max Turbo up to 5.4GHz, 36MB Intel® Smart Cache

AI PC Category

AI-Powered Gaming PC^[1]

NPU

Integrated Intel® AI Boost, up to 13 TOPS

Graphics

NVIDIA GeForce RTX™ 5080 16GB GDDR7, Boost Clock 2287MHz, TGP 175W, 1334 AI TOPS

Chipset

Intel® HM870 Chipset

Memory

2x 32GB CSODIMM DDR5-6400

Memory Slots

Two DDR5 CSODIMM slots, dual-channel capable

Max Memory^[2]

Up to 64GB DDR5-6400 offering

Storage

2x 1TB SSD M.2 2280 PCIe® 4.0x4 NVMe®

Storage Slot

Two M.2 slots • One M.2 2280 PCIe® 5.0 x4 slot • One M.2 2280 PCIe® 4.0 x4 slot

Max Storage Support^[3]

Up to two drives, 2x M.2 SSD • M.2 2242 SSD up to 1TB • M.2 2280 SSD up to 2TB

Optical

None

Card Reader

No Card Reader

Audio Chip

High Definition (HD) Audio, Realtek® ALC3306 codec

Speakers

4 stereo speakers, 2W x2 (woofers), 2W x2 (tweeters), optimized with Nahimic Audio, Smart Amplifier (AMP)

Microphone

2x, Array

Camera

5.0MP with E-shutter

Battery

99.9Wh

Power Adapter

400W Slim Tip (3-pin)

Special Features

AI Chip: LA3

DESIGN

Display

16” WQXGA (2560x1600) OLED 500nits (typical) / 1100nits (peak) Glossy, 100% DCI-P3, 240Hz, DisplayHDR™ True Black 1000, Dolby Vision®, G-SYNC®, Low Blue Light, High Gaming Performance, Flicker Free

Touchscreen

None

Screen-to-Body Ratio

92% AAR (active area ratio)

Color Calibration

Factory Color Calibration

Pen

Pen Not Supported

Keyboard

Per-key RGB Backlit, English

Touchpad

Buttonless Mylar® surface multi-touch touchpad, 75 x 120 mm (2.95 x 4.72 inches)

Dimensions (WxDxH)^[4]

364.38 x 275.94 x 21.9-26.65 mm (14.35 x 10.86 x 0.86-1.05 inches)

Weight^[5]

Starting at 2.57 kg (5.67 lbs)

Case Color

Eclipse Black

Case Material

Aluminium (Top), Aluminium (Bottom)

Surface Treatment

Anodizing Sandblasting

SOFTWARE

Operating System

Windows® 11 Pro, English

Bundled Software

Office Trial + Lenovo® AI Now

CONNECTIVITY

WLAN + Bluetooth

Wi-Fi® 7, 802.11be 2x2 + BT5.4

WWAN

WWAN Not Supported

Ethernet

2.5GbE (RJ-45)

Standard Ports

- 2x USB-A (USB 5Gbps / USB 3.2 Gen 1)
- 1x USB-A (USB 10Gbps / USB 3.2 Gen 2), Always On
- 1x USB-C® (USB 10Gbps / USB 3.2 Gen 2), with USB PD 95-100W and DisplayPort™ 2.1
- 1x Thunderbolt™ 4 / USB4® 40Gbps (support data transfer and DisplayPort™ 2.1)
- 1x HDMI® 2.1, up to 8K/60Hz
- 1x Headphone / microphone combo jack (3.5mm)
- 1x Ethernet (2.5GbE RJ-45)

- 1x Slim tip Power connector

Docking

Various docking solutions supported via Thunderbolt™ or USB-C®. For more compatible docking solutions, please visit [Docking for Legion Pro 7 16IAX10H](#)

SECURITY & PRIVACY

Security Chip

Firmware TPM 2.0 Enabled

Fingerprint Reader

No Fingerprint Reader

Other Security

E-shutter

SERVICE

Base Warranty

1-year, Courier or Carry-in

Included Upgrade

None

ACCESSORIES

Bundled Accessories

None

CERTIFICATIONS

Green Certifications

- ErP Lot 3
- RoHS compliant

Other Certifications

- TÜV Rheinland® Flicker Free
- TÜV Rheinland® High Gaming Performance
- TÜV Rheinland® Low Blue Light (Hardware Solution)

MODEL

Product	: Legion Pro 7 16IAX10H Lenovo Legion™ Pro 7i (16",10)		
TopSeller	: No	EAN / UPC / JAN:	198157311800
Announce Date:	2025-03-27	End of Support	: 2031-03-08

Note:
^[1] AI-Powered Gaming PCs feature Lenovo AI Engine+ and NVIDIA GeForce RTX GPUs to handle AI-driven tasks and deliver exceptional gaming performance.
^[2] The max memory is based on the test results with current Lenovo memory offerings.
^[3] The storage capacity supported is based on the test results with current Lenovo storage offerings.
^[4] The system dimensions may vary depending on configurations.
^[5] The system weight is approximate and based on results in Lenovo lab, which varies depending on the source of component, variance of the distribution of each component, and manufacturing process. It may not be the exact weight for each specific model.

- Please refer to the official [Lenovo store website](#) or contact a local Lenovo sales representative or authorized business partner for current inventory and purchase options.
- Lenovo reserves the right to change specifications without notice.

· California Electronic Waste Recycling Fee In California, per state law, Lenovo charges an electronic waste recycling fee on this covered device at the time of sale of the product. For more information, go to: <https://www.calrecycle.ca.gov/Electronics/Consumer>