

Lenovo Slim 7 14ILL10

PERFORMANCE

Processor

Intel® Core™ Ultra 7 256V, 8C (4P + 4LPE) / 8T, Max Turbo up to 4.8GHz, 12MB

AI PC Category^[1]

Copilot+ PC

NUPU

Integrated Intel® AI Boost, up to 47 TOPS

Graphics

Integrated Intel® Arc™ Graphics 140V

Chipset

Intel® SoC Platform

Memory

16GB Soldered LPDDR5x-8533, MoP Memory

Memory Slots

Memory soldered to systemboard, no slots, dual-channel

Max Memory

16GB soldered memory, not upgradable

Storage

1TB SSD M.2 2242 PCIe® 4.0x4 NVMe®

Storage Support^[2]

One drive, up to 1TB M.2 2242 SSD

Storage Slot

One M.2 2242 PCIe® 4.0 x4 slot

Card Reader

microSD Card Reader

Audio Chip

High Definition (HD) Audio, SoundWire®, Cirrus Logic® CS42L43 codec

Speakers

4 stereo speakers, 2W x2 (woofers), 2W x2 (tweeters), optimized with Dolby Atmos®, Smart Amplifier (AMP)

Camera

5.0MP + IR with E-shutter

Microphone

4x, Array

Battery

70Wh

Power Adapter

65W USB-C® Slim (2-pin, Wall-mount)

DESIGN

Display

14" WUXGA (1920x1200) OLED 600nits (peak) / 400nits (typical) Glossy / Anti-fingerprint, 100% DCI-P3, 60Hz, Eyesafe®, Dolby Vision®, DisplayHDR™ True Black 500, Glass, Touch, X-Rite®

Touchscreen

OGS, 10-point Multi-touch

Color Calibration

Factory Color Calibration

Keyboard

Backlit, English

Touchpad

Buttonless glass surface multi-touch touchpad, supports Precision TouchPad (PTP), 80 x 135 mm (3.15 x 5.31 inches)

Case Color

Luna Grey

Surface Treatment

Aluminium Stamping (Anodized with Sandblasting)

Case Material

Aluminium (Top), Aluminium (Bottom)

Pen

Pen Not Supported

Dimensions (WxDxH)^[3]

312 x 219.3 x 13.9 mm (12.28 x 8.63 x 0.55 inches)

Weight^[4]

Starting at 1.28 kg (2.82 lbs)

SOFTWARE

Operating System

Windows® 11 Home, English

Bundled Software

Office Trial

CONNECTIVITY

Ethernet

No Onboard Ethernet

WLAN + Bluetooth®^[5]

Wi-Fi® 7, 802.11be 2x2 + BT5.4

WWAN

Non-WWAN

Standard Ports

- 1x USB-A (USB 5Gbps / USB 3.2 Gen 1), Always On
- 2x USB-C® (Thunderbolt™ 4 / USB4® 40Gbps), with USB PD 3.0 and DisplayPort™ 2.1
- 1x HDMI® 2.1, up to 4K/60Hz
- 1x Headphone / microphone combo jack (3.5mm)
- 1x microSD card reader

Docking

Various docking solutions are supported via Thunderbolt™. For more compatible docking solutions, please visit [Docking for Lenovo® Slim 7 14ILL10](#)

SECURITY & PRIVACY

PSREF

Product Specifications
Reference

Security Chip

Firmware TPM 2.0

Fingerprint Reader

None

Other Security

- Ultrasonic Human Presence Detection
- E-shutter
- IR camera for Windows® Hello (facial recognition)

SERVICE

Base Warranty

1-year, Courier or Carry-in

Included Upgrade

None

ACCESSORIES

Bundled Accessories^[6]

None

CERTIFICATIONS

Green Certifications^[7]

- Carbon Neutral Certified
- ENERGY STAR® 8.0
- EPEAT™ Gold Registered
- ErP Lot 6/26
- RoHS compliant

Other Certifications

- Intel® Evo™ Platform
- Eyesafe® Certified 2.0
- TÜV Rheinland® Flicker Free
- TÜV Rheinland® Low Blue Light (Hardware Solution)

Mil-Spec Test

MIL-STD-810H military test passed (21 test items)

MODEL

TopSeller : No

EAN / UPC / JAN : 198155399701

Announce Date : 2025-02-24

End of Support : 2031-02-27

Note:

[1] The AI features of Copilot+ PC require Windows 11 to be installed.

[2] The storage capacity supported is based on the test results with current Lenovo storage offerings.

[3] The system dimensions may vary depending on configurations.

[4] The system weight is approximate and based on results in Lenovo lab, which varies depending on the source of component, variance of the distribution of each component, and manufacturing process. It may not be the exact weight for each specific model.

[5] 6GHz Wi-Fi 7 operation is subject to the regulation.....

[6] Lenovo reserves the right to change specifications without notice.
· California Electronic Waste Recycling Fee In California, per state law, Lenovo charges an electronic waste recycling fee on this covered device at the time of sale of the product. For more information, go to: <https://www.calrecycle.ca.gov/Electronics/Consumer>

To see more note information, please link to <https://psref.lenovo.com/Detail/2657?M=83MC0001US>

Premium Care - Advanced Support from Real People. Real Fast.

REAL PERSON

Choose how you want to reach us - through the phone, chat or email - our expert technicians will take care of you.

HASSLE FREE

'Getting started' and 'how-to' assistance for hardware and software. Easy solutions that are simple to reach - that's how Premium Care delivers you the ideal support experience.

REAL FAST

Highly trained technicians will provide you real-time solutions, whatever the issue, on your first contact. If needed, our team will schedule an onsite visit for the next business day.

PC HEALTH CHECK

Free annual PC Health Check that allows our experts to spot issues before you do so they can resolve them quickly and help you avoid PC problems.

Recommended Accessories

Lenovo 65W USB-C DC Travel Adapter

Power up and stay productive on the road with this DC Travel adapter. Lenovo 65W USB-C DC Travel Adapter is the universal DC adapter, providing 65W power via USB-C for outdoor use.

Lenovo 65W USB-C GaN Adapter

The Lenovo 65W USB-C GaN Adapter ushers in a new age of safe, efficient portable charging. Powered by Gallium Nitride (GaN), this charger is up to 55% smaller, 60% lighter, 30% more power-efficient. With PD 3.0 certif...

Accidental Damage Protection - Protection of your PC from the unexpected.

Experience shows that a significant portion of devices may be damaged (and not covered under warranty) in the first three years. Lenovo's Accidental Damage Protection service covers accidents beyond the system warranty such as drops, spills, bumps and even electrical surges. Make sure your new device has maximum protection, avoid unplanned costs and get peace of mind.

Base Warranty – Included with the systems you purchase, default 1- or 3-year coverage window.

Warranty Extensions & Upgrades – Service and protection that's right for your circumstances.

- Pick Up & Return Courier
- Onsite Support
- Technician Installed Customer
- Replaceable Unit Service
- International Warranty Upgrade

Lenovo may not offer the products, services or features discussed in this document in all regions. Lenovo may withdraw an offering at any time. Consult your local representative for information on offerings available in your area. Lenovo reserves the right to change specifications or other product information without notice. Lenovo is not responsible for photographic or typographical errors. Lenovo provides this publication "as is" without warranty of any kind, either express or implied, including the implied warranties of merchantability or fitness for a particular purpose.

For a full list of accessories and services, please visit:
<https://smartfind.Lenovo.com>

PSREF

Product Specifications
Reference