



VP2456A - 24" COLORPRO™ 1080P IPS MONITOR WITH 90W USB-C, SRGB, AND PANTONE VALIDATED

Key Features



24
DISPLAY



IPS
PANEL



1920x1080
RESOLUTION



Product Description

Engineered to deliver unmatched color accuracy crucial for professional applications, the ViewSonic® VP2456A 24" (23.8" viewable) Full HD monitor displays your work with the vivid and lifelike color it deserves. With a SuperClear® IPS panel and a sleek 3-sided frameless design, the VP2456A provides a near-seamless viewing experience ideal for multi-monitor setups. The VP2456A is equipped with USB-C for single cable connectivity to deliver video, audio, and 90W of power delivery. To ensure precise, uniform color, each of our monitors is factory calibrated to deliver an amazing Delta E <2, so you can be confident what you see on screen is what your clients and customers will see as well.

Specifications

[More Information](#)

UPC	766907031782
Screen Size	24
Viewable Area (in.)	23.8
Panel Type	IPS
Display Resolution	1920 x 1080
Display Resolution	Full HD (1920x1080)
Static Contrast Ratio	1,500:1
Dynamic Contrast Ratio	20M:1
Light Source	LED
Brightness	250 cd/m2
Aspect Ratio	16:9
Response Time (Typical GTG)	5ms
Viewing Angles	178º horizontal, 178º vertical
Backlight Life (Hours)	30,000
Panel Surface	Anti-Glare type, Hard-coating (3H), Haze 25%
Refresh Rate	120Hz
PC Resolution (max)	1920x1080
Mac® Resolution (max)	1920x1080
USB Type A	3
USB Type C	90W x 1, 15W x 1
HDMI 1.4 In	1
DisplayPort	1
Internal Speakers	2W (x2)
Eco Mode (Conserve)	56.8
Eco Mode (optimized)	58.1
Consumption (typical)	59.8
Consumption (max)	70.4
Voltage	100-240 VAC
Stand-by	0.5
Power Supply	Internal
Cable Organization	No
Kensington Lock Slot	1
Physical Controls	Key 1, Key 2, Key 3, Key 4, Key 5, Key 6 (power)
On Screen Display	Input Select, Audio Adjust, ViewMode, Color Adjust, Manual Image Adjust, Setup Menu
Temperature	32-104º F (0 - 40º C)
Humidity (non-condensing)	20-90%

VESA Compatible	100 x 100 mm
Height Adjust	130 mm / 5.1 in
Swivel	120°
Pivot (Right/Left)	90° / 90°
Tilt (Forward/Back)	5° / 21°
Regulations	cTUVus, FCC-B, ICES003, EnergyStar 8.0, EPEAT Silver, NOM, Mexico Energy
Net (lbs)	14.2
Net Without Stand (lbs)	8.8
Gross (lbs)	20.1
Net (kg)	6.5
Net Without Stand (kg)	4
Gross (kg)	9.1
Packaging (in.)	24.4" x 15.4" x 9"
Physical (in.)	21.23" x 15.29"-20.41" x 8.46"
Physical Without Stand (in.)	21.23" x 12.61" x 2.09"
Packaging (mm)	620 x 392 x 228
Physical (mm)	539.2 x 388.46-518.46 x 214.96
Physical Without Stand (mm)	539.2 x 320.2 x 53.2
Package Contents	VP2456A x1, 3-pin Plug (IEC C13 / CEE22) x1, HDMI Cable (v1.4; Male-Male) x1, USB Type-C Gen2 Cable (Male-Male) x1, USB Type-C to Type-A 3.2 Gen1 Cable (Male-Male) x1, Quick Start Guide x1,
Recycle/Disposal	Please dispose of in accordance with local, state or federal laws.
Warranty	Three-year limited warranty on parts, labor and backlight

UPC: 766907031782



Contact Sales

[ViewSonic.com](https://www.viewsonic.com)

888.881.8781

email:

salesinfo@viewsonic.com