



B U S I N E S S   &   P R O D U C T I V I T Y

# Prestige 16 AI+ Evo

P R E S T I G E   1 6   A I +   E V O   B 2 V M G - 0 5 5 U S

## Specification

|                       |                                                                 |
|-----------------------|-----------------------------------------------------------------|
| Manufacturer Part #   | PRE16EVOB2055                                                   |
| OS                    | Windows 11 Home<br>(MSI recommends Windows 11 Pro for business) |
| CPU                   | Intel® Core™ Ultra 9 - 288V                                     |
| CPU Speed             | 3.3 - 5.1 GHz                                                   |
| Chipset               | -                                                               |
| Color                 | Stellar Gray                                                    |
| Screen Size           | 16" 16:10 QHD+ (2560x1600), 100% DCI-P3, IPS-Level panel        |
| Resolution            | (3840x2400)<br>16:10                                            |
| GPU                   | Intel® Arc Graphics                                             |
| Video Memory          | -                                                               |
| Keyboard              | White backlight keyboard with Finger print reader               |
| Speaker               | 2x Speakers 2W                                                  |
| Memory                | 32GB<br>LPDDR5X-8533MHz                                         |
| HDD Capacity          | 1TB NVMe SSD                                                    |
| HDD Interface         | NVMe                                                            |
| TPM                   | TPM 2.0 OPTIGA™ SLB 9672                                        |
| LAN                   | Gigabit Ethernet                                                |
| WLAN                  | Intel® Killer™ Wi-Fi 7 BE1750(w)                                |
| Bluetooth             | BT 5.4                                                          |
| Card Reader           | Full Size SD Card                                               |
| Webcam                | FHD IR 5MP Webcam with Dual Mic with Privacy shutter Design     |
| USB                   | 1x USB 3.2 Gen2 (Type-A)                                        |
| Type-C Port           | 2x Thunderbolt™ 4 [Support Power delivery, DP 1.4a, USB 4.0]    |
| Video Port            | HDMI 2.1 (8K @ 60Hz)                                            |
| Audio Port            | Mic-in/Headphone-out Combo                                      |
| AC Power Adaptor      | 100W [USB-C]                                                    |
| Battery Pack          | 4 cell (99.9Whr) Li-Polymer                                     |
| Dimension             | 14.11" x 10.02" x 0.75"                                         |
| Weight                | 3.31 lbs                                                        |
| Manufacturer Warranty | 1 year Limited warranty (Include 1 Year Global)                 |