



# OMEN 27 inch FHD 180Hz Gaming Monitor - OMEN 27 G2 (AV4K2AA)



## Overview

### TAKE YOUR FUN UP A NOTCH

Reach new possibilities with the OMEN 27-inch FHD 180 Hz Gaming Monitor. Quick performance and vibrant color let you get lost in the games you love most, while the sleek design functions to look and feel great on your desk.

180Hz

### NO LAG. ALL SPEED.

Frame by frame, experience all the action with no distractions. To keep things smooth, this display boasts a fast 180 Hz refresh rate and 1ms GTG response time with Overdrive to cut motion blur.[1] so every pixel keeps up with you. Leave screen tearing and lag in the dust, thanks to AMD FreeSync™ technology.[2]



### ALL YOUR FUN, CUSTOM

The OMEN look blends sophistication and fun with easy cable management, the adjustable stand, and ports for your PC and console. You can customize your ecosystem with OMEN Gaming Hub[4] that enhances your play in an easy and simple way.

HDR

### SEE A WORLD YOU CAN STEP INTO

Mistake virtual for IRL while you explore your favorite worlds with the crisp visuals of FHD resolution.[3] For lifelike gameplay, escape into a wide array of vibrant colors, hues, and shades with the 95% Display P3 factory color calibrated color gamut.[1] Even in shadow, easily make out details and shading with HDR 400 and up to 400 nits of brightness.[1]



### SUSTAINABILITY IN ACTION

It matters. With at least 90% recycled plastic in the enclosure,[5] 20% recycled glass in the monitor panel, [13] and 5% recycled metal in the stand base and VESA plate,[6] we are in this together.[7]

## Features

### FHD Resolution

Focus on the finer details and enjoy clear images with the 1920 x 1080 Full HD resolution on this 27" diagonal monitor.<sup>[3]</sup>

### 180 Hz refresh rate

For crisp action and responsive gameplay, this fast refresh rate practically removes all artifacting and motion blurring.<sup>[1]</sup>

### HDR 400

Explore new worlds in stunning contrast with HDR 400. With peak brightness of 400 nits, experience games how the developers intended with brighter whites, deeper blacks, and richer colors.<sup>[1,8]</sup>

### More Colors to Play With

Get deeper hues and a wide array of colors with 95% Display P3 factory color calibrated for precisely recreated colors so lifelike you get lost in your gameplay.<sup>[1]</sup>

### 1ms GTG Response Time with Overdrive

How fast your pixels can react to changing frames is critical for fast-paced gaming, and a 1ms GTG response time with Overdrive ensures even the most action-packed moments are fluid, crisp, and free of motion blur.<sup>[1]</sup>

### AMD FreeSync™ Technology

Every gamer deserves perfectly smooth gameplay and peak performance. Game confidently with a high refresh rate, low framerate compensation, and low latency. AMD FreeSync™ certified monitors are here.<sup>[2]</sup>

---

*[1] All performance specifications represent the typical specifications provided by HP's component manufacturers; actual performance may vary, either higher or lower.*

*[2] FreeSync™ is an AMD® technology that requires mandatory low framerate compensation and at least 144 Hz refresh rate with <3440 horizontal resolution, AMD Radeon Graphics and/or AMD A-Series APU-compliant monitors with DisplayPort/HDMI Adaptive-Sync required. More information is available at [www.amd.com/freesync](http://www.amd.com/freesync).*

*[3] Full high-definition (FHD) content required to view FHD images.*

*[4] Account required for full functionality. See OMEN Gaming Hub terms and conditions. Support level for non-HP products may be subject to change. Some animation effects may consume more CPU resources.*

*[5] Recycled plastic is expressed as a percentage of the total weight plastic. Post-consumer recycled is based on the definition set in the EPEAT® standard for computers, IEEE 1680.1-2018 standard.*

*[6] Recycled metal is expressed as a percentage of the total weight of the metal according to ISO 14021 definitions for metal parts over 25 grams.*

*[7] Recycling facilities not available in all locations.*

*[13] Percentage of recycled glass in the monitor panel varies by product. Recycled glass is expressed as a percentage of the total weight of the glass.*

*[8] DisplayHDR™ is the high-performance Monitor and Display Compliance Test Specification from VESA specifying HDR (High Dynamic Range) quality. See <http://displayhdr.org> for more details.*

## Specifications

<b>Color</b>	Black
<b>Display size (diagonal)</b>	27"
<b>Panel technology</b>	IPS; LCD
<b>Display size (diagonal)</b>	68.6 cm (27")
<b>Aspect ratio</b>	16:9 <sup>[1]</sup>
<b>Native resolution</b>	FHD (1920 x 1080) <sup>[1,2]</sup>
<b>Resolutions supported</b>	640 x 480 @ 60 Hz; 640 x 480 @ 75 Hz; 720 x 400 @ 70 Hz; 800 x 600 @ 60 Hz; 800 x 600 @ 75 Hz; 1024 x 768 @ 60 Hz; 1280 x 720 @ 60 Hz; 1280 x 1024 @ 60 Hz; 1440 x 900 @ 60 Hz; 1600 x 900 @ 60 Hz; 1680 x 1050 @ 60 Hz; 1920 x 1080 @ 50 Hz; 1920 x 1080 @ 60 Hz; 1920 x 1080 @ 100 Hz; 1920 x 1080 @ 120 Hz; 1280 x 1024 @ 75 Hz; 720 x 480 @ 60 Hz; 720 x 576 @ 50 Hz; 1024 x 768 @ 75 Hz; 1280 x 800 @ 60 Hz; 1920 x 1080 @ 165 Hz; 1920 x 1080 @ 180 Hz (DisplayPort only); 1920 x 1080 @ 144 Hz; 3840 x 2160 @ 60 Hz (HDMI console only)
<b>Pixel pitch</b>	0.3108 x 0.3108 mm
<b>Brightness</b>	400 nits <sup>[1]</sup>
<b>Contrast ratio</b>	1000:1 <sup>[1]</sup>
<b>Response time (typical)</b>	1ms GtG (with overdrive) <sup>[1]</sup>
<b>Dimensions (W x D x H)</b>	61.36 x 5.22 x 36.43 cm (without stand)
<b>Dimensions (W x D x H)</b>	24.16 x 2.06 x 14.34 in (without stand)
<b>Dimensions With Stand (W x D x H)</b>	61.36 x 22.33 x 52.37 cm
<b>Weight</b>	8.05 kg (with stand); 6.01 kg (without stand)
<b>Weight</b>	17.75 lb (with stand); 13.25 lb (without stand)
<b>Display features</b>	AMD FreeSync™; Anti-glare; HP Eye Ease (Eyesafe® certified); Height adjustable; Pivot; Tilt; Factory color calibration; 4K Downscaling for Console HDR Support; VESA ClearMR 5000 certified
<b>Onscreen controls</b>	Brightness+; Color; Image; Input; Power; Menu; Management; Information; Exit; Contrast; Gaming; Message control; Language
<b>Display colors</b>	Up to 16.7 million colors supported <sup>[1]</sup>
<b>Display scan frequency (horizontal)</b>	30-215 kHz <sup>[1]</sup>
<b>Display scan frequency (vertical)</b>	50-180 Hz <sup>[1]</sup>
<b>Power</b>	100 - 240 VAC 50/60 Hz
<b>Power consumption</b>	52 W (maximum), 25 W (typical), 0.29 W (standby)
<b>Operating temperature range</b>	5 to 35°C
<b>Operating humidity range</b>	20 to 80% RH (non-condensing)
<b>Sustainable impact specifications</b>	Low halogen; Contains 20% recycled glass in the monitor panel; 100% of HP paper-based packaging is from recycled or certified sustainable sources; Contains at least 85% post-consumer recycled plastic; At least 5% recycled metal
<b>Certifications and compliances</b>	BIS; BSMI; CB; CCC; CE; CEL; CSA; EAC; FCC; ISO 9241-307; KC/KCC; NOM; PSB; TUV Bauart; TUV LBL; VCCI; WEEE; California Energy Commission (CEC); PSBISC; WW application; ICE; TÜV Flicker free certified; UAE safety; UAE RoHS; South Africa safety; Ukraine safety
<b>Management Software</b>	OMEN Gaming Hub
<b>UPC number</b>	(A2K) 198701662297; (AB0) 198701662303; (AB1) 198701662310; (AB2) 198701662327; (AB4) 198701662334; (ABG) 198701662341; (ABJ) 198701662358; (ACJ) 198701662365; (AKL) 198701662389; (AR6) 198701662396; (UUF) 198701662419
<b>Manufacturer Warranty</b>	HP standard one-year limited warranty

**What's in the box**

Monitor; Warranty card; AC power cable; Quick Setup Poster; DisplayPort™ 1.4 cable; Cable holder; Base stand; Color calibration report<sup>[3]</sup>

## Additional specifications

<b>Audio port</b>	1 x 3.5 mm Audio Jack (Audio Out)
<b>Backlight lamp life</b>	30,000 hours
<b>Backlight type</b>	Edge-lit
<b>Base area footprint (imperial)</b>	8.46 x 8.26 in
<b>Base area footprint (metric)</b>	21.49 x 20.99 cm
<b>Bezel</b>	3-sided borderless
<b>Color gamut</b>	95% Display P3 <sup>[1]</sup>
<b>Curvature</b>	Flat
<b>Datasheet photo 1</b>	<a href="https://prism-pui-int.inc.hp.com/net/PRO.Crystal.1/DAMHandler/Accessories/Kerby_Fighters_27_Jetblack_CoreSet_Scrn_Front.png">https://prism-pui-int.inc.hp.com/net/PRO.Crystal.1/DAMHandler/Accessories/Kerby_Fighters_27_Jetblack_CoreSet_Scrn_Front.png</a>
<b>Datasheet photo 2</b>	<a href="https://prism-pui-int.inc.hp.com/net/PRO.Crystal.1/DAMHandler/Accessories/Kerby_Fighters_27_Jetblack_CoreSet_Scrn_FrontRight.png">https://prism-pui-int.inc.hp.com/net/PRO.Crystal.1/DAMHandler/Accessories/Kerby_Fighters_27_Jetblack_CoreSet_Scrn_FrontRight.png</a>
<b>Datasheet photo 3</b>	<a href="https://prism-pui-int.inc.hp.com/net/PRO.Crystal.1/DAMHandler/Accessories/Kerby_Fighters_27_Jetblack_CoreSet_Rear.png">https://prism-pui-int.inc.hp.com/net/PRO.Crystal.1/DAMHandler/Accessories/Kerby_Fighters_27_Jetblack_CoreSet_Rear.png</a>
<b>Datasheet photo 4</b>	<a href="https://prism-pui-int.inc.hp.com/net/PRO.Crystal.1/DAMHandler/Accessories/Kerby_Fighters_27_Jetblack_CoreSet_LeftProfile.png">https://prism-pui-int.inc.hp.com/net/PRO.Crystal.1/DAMHandler/Accessories/Kerby_Fighters_27_Jetblack_CoreSet_LeftProfile.png</a>
<b>Detachable stand</b>	Yes
<b>Display area (imperial)</b>	23.49 x 13.22 in
<b>Display area (metric)</b>	59.67 x 33.57 cm
<b>Display contrast ratio (dynamic)</b>	10,000,000:1
<b>DisplayPort™</b>	1 DisplayPort™ 1.4
<b>Ecolabels</b>	CEL; Korea MEPS; California CEC
<b>Flicker-free</b>	Yes
<b>HDCP</b>	Yes, DisplayPort™ and HDMI
<b>HDMI</b>	2 HDMI 2.0
<b>HDR</b>	HDR 400
<b>Hardness</b>	3H <sup>[1]</sup>
<b>Haze</b>	25%
<b>Height adjustment range</b>	100 mm
<b>Horizontal viewing angle</b>	178°
<b>Low blue light</b>	Yes, HP Eye Ease (Eyesafe® Certified) <sup>[1]</sup>

<b>Non-Operating Humidity Range</b>	5 to 95%
<b>Non-operating temperature - Celsius</b>	-40 to 65°C
<b>Non-operating temperature - fahrenheit</b>	-40 to 149°F
<b>Operating altitude</b>	Up to 5,000 m
<b>Operating altitude</b>	Up to 16,400 ft
<b>Operating temperature range</b>	41 to 95°F
<b>Package dimensions (W x D x H)</b>	69.9 x 16 x 44.6 cm
<b>Package dimensions (W x D x H)</b>	27.52 x 6.3 x 17.56 in
<b>Package weight</b>	11.29 kg
<b>Package weight</b>	24.89 lb
<b>Pallet (layers)</b>	Slip sheet: 5 layers; Pallet: 4 layers (20' ft, 40' ft), 5 layers (40' HQ)
<b>Pallet dimensions</b>	Slip sheet: 44.49 x 27.91 x 88.78 in (20 ft, 40 ft, 40 HQ); Pallet: 44.29 x 27.91 x 75.83 in (20 ft, 40 ft), 44.49 x 27.91 x 93.5 in (40 HQ)
<b>Pallet dimensions (W x D x H)</b>	Slip sheet: 113 x 70.9 x 225.5 cm (20 ft, 40 ft, 40 HQ); Pallet: 113 x 70.9 x 192.6 cm (20 ft, 40 ft), 113 x 70.9 x 237.5 cm (40 HQ)
<b>Pallet weight</b>	Slip sheet: 871.16 lb (20 ft, 40 ft, 40 HQ); Pallet: 723.38 lb (20 ft, 40 ft), 897.21 lb (40 HQ)
<b>Pallet weight</b>	Slip sheet: 395.15 kg (20 ft, 40 ft, 40 HQ); Pallet: 328.12 kg (20 ft, 40 ft), 407.15 kg (40 HQ)
<b>Panel bit depth</b>	True 8 bit <sup>[1]</sup>
<b>Pixels per inch (ppi)</b>	82 ppi <sup>[1]</sup>
<b>Power supply type</b>	Internal
<b>Product brand name</b>	HP
<b>Product color</b>	Black
<b>Product dimensions with stand (W x D x H)</b>	24.16 x 8.79 x 20.62 in
<b>Products per pallet</b>	Slip sheet: 35; Pallet: 28 (20 ft, 40 ft); 35 (HQ)
<b>Products per pallet layer</b>	Pallet and Slip sheet: 7

<b>Refresh rate (maximum)</b>	180 Hz
<b>Resolution (maximum)</b>	FHD (1920 x 1080 @ 180 Hz) <sup>[1]</sup>
<b>Screen treatment</b>	Anti-glare
<b>Stand color</b>	Black
<b>Stand type</b>	Base stand; With stand; Height adjustable stand
<b>Storage altitude</b>	Up to 12,192 m
<b>Storage altitude</b>	Up to 40,000 ft
<b>Technology logo 1</b>	<a href="https://h10003.www1.hp.com/digmedialib/prodimg/lowres/c09108206.png">https://h10003.www1.hp.com/digmedialib/prodimg/lowres/c09108206.png</a>
<b>Technology logo 2</b>	<a href="https://h10003.www1.hp.com/digmedialib/prodimg/lowres/c08610272.png">https://h10003.www1.hp.com/digmedialib/prodimg/lowres/c08610272.png</a>
<b>Technology logo 3</b>	<a href="https://h10003.www1.hp.com/digmedialib/prodimg/lowres/c08610275.png">https://h10003.www1.hp.com/digmedialib/prodimg/lowres/c08610275.png</a>
<b>Technology logo 4</b>	<a href="https://h10003.www1.hp.com/digmedialib/prodimg/lowres/c08829160.png">https://h10003.www1.hp.com/digmedialib/prodimg/lowres/c08829160.png</a>
<b>Tilt</b>	-5 to +20°
<b>UNSPSC code</b>	43211902
<b>VESA mounting</b>	100 x 100 mm
<b>Vertical viewing angle</b>	178°
<b>Viewable diagonal size</b>	26.96" (68.47 cm)
<b>pivot</b>	±90°

[1] All specifications represent the typical specifications provided by HP's component manufacturers, actual performance may vary either higher or lower.

[2] DisplayPort™ 1.4 or HDMI 2.0 required to drive panel at its native resolution. The video card of the connected PC must be capable of supporting 1920 x 1080 at 60 Hz with 8-bit color using one DisplayPort™, HDMI.

[3] Included cables may vary by country.

## Disclaimer — Copyright

DisplayPort™ is a trademark owned by the Video Electronics Standards Association (VESA®) in the United States and other countries. Microsoft, Encarta, MSN, and Windows are either registered trademarks or trademarks of Microsoft Corporation in the United States and/or other countries.

© Copyright 2025 HP Development Company, L.P. The information contained herein is subject to change without notice. The only warranties for HP products and services are set forth in the express warranty statements accompanying such products and services. Nothing herein should be construed as constituting an additional warranty. HP shall not be liable for technical or editorial errors or omissions contained herein.