



OMEN 27 inch QHD 180Hz Gaming Monitor - OMEN 27q G2 (AV4H6AA)



Overview

TAKE YOUR FUN UP A NOTCH

Reach new possibilities with the OMEN 27-inch QHD 180 Hz Gaming Monitor. Quick performance and vibrant color let you get lost in the games you love most, while the sleek design functions to look and feel great on your desk.

180Hz

NO LAG. ALL SPEED.

Frame by frame, experience all the action with no distractions. To keep things smooth, this display boasts a fast 180 Hz refresh rate and 1ms GTG response time with Overdrive to cut motion blur,[1] so every pixel keeps up with you. Leave screen tearing and lag in the dust, thanks to AMD FreeSync™ technology.[2]



ALL YOUR FUN, CUSTOM

The OMEN look blends sophistication and fun with easy cable management, the adjustable stand, and ports for your PC and console. You can customize your ecosystem with OMEN Gaming Hub[4] that enhances your play in an easy and simple way.

HDR

SEE A WORLD YOU CAN STEP INTO

Mistake virtual for IRL while you explore your favorite worlds with the crisp visuals of QHD resolution.[3] For lifelike gameplay, escape into a wide array of vibrant colors, hues, and shades with the 95% Display P3 factory color calibrated color gamut.[1] Even in shadow, easily make out details and shading with HDR 400 and up to 400 nits of brightness.[1]



SUSTAINABILITY IN ACTION

It matters. With at least 90% recycled plastic in the enclosure[5], 20% recycled glass in the monitor panel, [13] and 5% recycled metal in the stand base and VESA plate,[6] we are in this together.[7]

Features

QHD Resolution

Get lost in the captivating definition and sharp details of 3.7 million pixels. 2560 x 1440 Quad HD resolution transforms all your content for a remarkable entertainment experience on this 27" diagonal monitor.^[3]

HDR 400

Explore new worlds in stunning contrast with HDR 400. With peak brightness of 400 nits, experience games how the developers intended with brighter whites, deeper blacks, and richer colors.^[1,8]

1ms GTG Response Time with Overdrive

How fast your pixels can react to changing frames is critical for fast-paced gaming, and a 1ms GTG response time with Overdrive ensures even the most action-packed moments are fluid, crisp, and free of motion blur.^[1]

180Hz refresh rate

For crisp action and responsive gameplay, this fast refresh rate practically removes all artifacting and motion blurring.^[1]

More Colors to Play With

Get deeper hues and a wide array of colors with 95% Display P3 factory color calibrated for precisely recreated colors so lifelike you get lost in your gameplay.^[1]

AMD FreeSync™ Technology

Every gamer deserves perfectly smooth gameplay and peak performance. Game confidently with a high refresh rate, low framerate compensation, and low latency. AMD FreeSync™ certified monitors are here.^[2]

[1] All performance specifications represent the typical specifications provided by HP's component manufacturers; actual performance may vary, either higher or lower.

[2] FreeSync™ is an AMD® technology that requires mandatory low framerate compensation and at least 144Hz refresh rate with <3440 horizontal resolution, AMD Radeon Graphics and/or AMD A-Series APU-compliant monitors with DisplayPort/HDMI Adaptive-Sync required. More information is available at www.amd.com/freesync.

[3] Quad high-definition (QHD) content required to view QHD images.

[4] Account required for full functionality. See OMEN Gaming Hub terms and conditions. Support level for non-HP products may be subject to change. Some animation effects may consume more CPU resources.

[5] Recycled plastic is expressed as a percentage of the total weight plastic. Post-consumer recycled is based on the definition set in the EPEAT® standard for computers, IEEE 1680.1-2018 standard.

[6] Recycled metal is expressed as a percentage of the total weight of the metal according to ISO 14021 definitions for metal parts over 25 grams.

[7] Recycling facilities not available in all locations.

[13] Percentage of recycled glass in the monitor panel varies by product. Recycled glass is expressed as a percentage of the total weight of the glass.

[8] DisplayHDR™ is the high-performance Monitor and Display Compliance Test Specification from VESA specifying HDR (High Dynamic Range) quality. See <http://displayhdr.org> for more details.

Specifications

Display size (diagonal)	27"
Panel technology	IPS; LCD
Display size (diagonal)	68.6 cm (27")
Aspect ratio	16:9 ^[1]
Native resolution	QHD (2560 x 1440) ^[1,2]
Resolutions supported	640 x 480 @ 60 Hz; 640 x 480 @ 75 Hz; 720 x 400 @ 70 Hz; 800 x 600 @ 60 Hz; 800 x 600 @ 75 Hz; 1024 x 768 @ 60 Hz; 1280 x 720 @ 60 Hz; 1280 x 1024 @ 60 Hz; 1440 x 900 @ 60 Hz; 1600 x 900 @ 60 Hz; 1680 x 1050 @ 60 Hz; 1920 x 1080 @ 50 Hz; 1920 x 1080 @ 60 Hz; 1920 x 1080 @ 100 Hz; 1920 x 1080 @ 120 Hz; 1920 x 1200 @ 60 Hz; 2560 x 1440 @ 60 Hz; 2560 x 1440 @ 75 Hz; 2560 x 1440 @ 120 Hz; 1280 x 1024 @ 75 Hz; 720 x 480 @ 60 Hz; 720 x 576 @ 50 Hz; 1024 x 768 @ 75 Hz; 1280 x 720 @ 50 Hz; 1280 x 720 @ 100 Hz; 1280 x 800 @ 60 Hz; 2560 x 1440 @ 144 Hz; 2560 x 1440 @ 165 Hz (DisplayPort only); 2560 x 1440 @ 180 Hz (DisplayPort only); 3840 x 2160 @ 60 Hz (HDMI console only)
Pixel pitch	0.2331 x 0.2331 mm ^[1]
Brightness	400 nits ^[1]
Contrast ratio	1000:1 ^[1]
Response time (typical)	1ms GtG (with overdrive) ^[1]
Dimensions (W x D x H)	61.36 x 5.22 x 36.43 cm (without stand)
Dimensions (W x D x H)	24.16 x 2.06 x 14.34 in (without stand)
Dimensions With Stand (W x D x H)	61.36 x 22.33 x 52.37 cm
Weight	7.33 kg (with stand); 5.29 kg (without stand)
Weight	16.16 lb (with stand); 11.66 lb (without stand)
Display features	AMD FreeSync™; Anti-glare; HP Eye Ease (Eyesafe® certified); Height adjustable; Pivot; Tilt; Factory color calibration; 4K Downscaling for Console HDR Support; VESA ClearMR 5000 certified
Onscreen controls	Brightness+; Color; Image; Input; Power; Menu; Management; Information; Exit; Contrast; Gaming; Message control; Language
Display colors	Up to 16.7 million colors supported ^[1]
Display scan frequency (horizontal)	30-283 kHz ^[1]
Display scan frequency (vertical)	50-180 Hz ^[1]
Power	100 - 240 VAC 50/60 Hz
Power consumption	67 W (maximum), 30 W (typical), 0.29 W (standby)
Operating temperature range	5 to 35°C
Operating humidity range	20 to 80% RH (non-condensing)
Sustainable impact specifications	Low halogen; Contains 20% recycled glass in the monitor panel; 100% of HP paper-based packaging is from recycled or certified sustainable sources; Contains at least 85% post-consumer recycled plastic; At least 5% recycled metal
Certifications and compliances	BIS; BSMI; CB; CCC; CE; CEL; CSA; EAC; FCC; ISO 9241-307; KC/KCC; NOM; PSB; TUV Bauart; TUV LBL; VCCI; WEEE; ISC; California Energy Commission (CEC); WW application; ICE; TÜV Flicker free certified; UAE safety; UAE RoHS; South Africa safety; Ukraine safety
Management Software	OMEN Gaming Hub
UPC number	(A2N) 198701661184; (ABA) 198701661191; (ABB) 198701661221; (ABT) 198701661238; (ABU) 198701661252; (ABV) 198701661276; (AC8) 198701661290; (ACQ) 198701661313; (AKH) 198701661337; (UUG) 198701661344; (UUZ) 198701661351
Manufacturer Warranty	HP standard one-year limited warranty

What's in the box

Monitor; Warranty card; AC power cable; Quick Setup Poster; DisplayPort™ 1.4 cable;
Cable holder; Base stand; Color calibration report^[3]

Additional specifications

Audio port	1 x 3.5 mm Audio Jack (Audio Out)
Backlight lamp life minimum (to half brightness)	30,000 hours
Backlight type	Edge-lit
Base area footprint (imperial)	8.46 x 8.26 in
Base area footprint (metric)	21.49 x 20.99 cm
Bezel	3-sided borderless
Color gamut	95% Display P3 ^[1]
Curvature	Flat
Datasheet photo 1	https://prism-pui-int.inc.hp.com/pro/crystal.1/damhandler/accessories/ness_fighters_27_jetblack_coreset_scrn_front.png
Datasheet photo 2	https://prism-pui-int.inc.hp.com/pro/crystal.1/damhandler/accessories/ness_fighters_27_jetblack_coreset_scrn_frontright.png
Datasheet photo 3	https://prism-pui-int.inc.hp.com/pro/crystal.1/damhandler/accessories/ness_fighters_27_jetblack_coreset_rear.png
Datasheet photo 4	https://prism-pui-int.inc.hp.com/pro/crystal.1/damhandler/accessories/ness_fighters_27_jetblack_coreset_leftprofile.png
Detachable stand	Yes
Display area (imperial)	23.49 x 13.22 in
Display area (metric)	59.67 x 33.57 cm
Display contrast ratio (dynamic)	10,000,000:1
DisplayPort™	1 DisplayPort™ 1.4
Ecolabels	CEL; Korea MEPS; California CEC
Flicker-free	Yes
HDCP	Yes, DisplayPort™ and HDMI
HDMI	2 HDMI 2.0
HDR	HDR 400
Hardness	3H ^[1]
Haze	25%
Height adjustment range	100 mm
Horizontal viewing angle	178°

Low blue light	Yes, HP Eye Ease (Eyesafe® Certified) ^[1]
Non-Operating Humidity Range	5 to 95%
Non-operating temperature - Celsius	-40 to 65°C
Non-operating temperature - fahrenheit	-40 to 149°F
Operating altitude	Up to 16,400 ft
Operating altitude	Up to 5,000 m
Operating temperature range	41 to 95°F
Package dimensions (W x D x H)	69.9 x 16 x 44.6 cm
Package dimensions (W x D x H)	27.52 x 6.3 x 17.56 in
Package weight	22.96 lb
Package weight	10.42 kg
Pallet (layers)	Slip sheet: 5 layers; Pallet: 4 layers (20' ft, 40' ft), 5 layers (40' HQ)
Pallet dimensions	Slip sheet: 44.49 x 27.91 x 88.78 inch (20 ft, 40 ft, 40 HQ); Pallet: 44.29 x 27.91 x 75.83 inch (20 ft, 40 ft), 44.49 x 27.91 x 93.5 inch (40 HQ)
Pallet weight	Slip sheet: 804.03 lb (20 ft, 40 ft, 40 HQ); Pallet: 669.68 lb (20 ft, 40 ft), 830.48 lb (40 HQ)
Pallet weight	Slip sheet: 364.7 kg (20 ft, 40 ft, 40 HQ); Pallet: 303.76 kg (20 ft,40 ft), 376.7 kg (40 HQ)
Panel bit depth	True 8 bit ^[1]
Pixels per inch (ppi)	109 ppi ^[1]
Power supply type	Internal
Product brand name	HP
Product color	Black
Product dimensions with stand (W x D x H)	24.16 x 8.79 x 20.62 in
Products per pallet	Slip sheet: 35; Pallet: 28 (20 ft, 40 ft); 35 (HQ)
Products per pallet layer	Pallet and Slip sheet: 7

Refresh rate (maximum)	180 Hz
Resolution (maximum)	QHD (2560 x 1440 @ 180 Hz) ^[1]
Screen treatment	Anti-glare
Stand color	Black
Stand type	Base stand; With stand; Height adjustable stand
Storage altitude	Up to 12,192 m
Storage altitude	Up to 40,000 ft
Technology logo 1	https://h10003.www1.hp.com/digmedialib/prodimg/lowres/c09108206.png
Technology logo 2	https://h10003.www1.hp.com/digmedialib/prodimg/lowres/c08610272.png
Technology logo 3	https://h10003.www1.hp.com/digmedialib/prodimg/lowres/c08610275.png
Technology logo 4	https://h10003.www1.hp.com/digmedialib/prodimg/lowres/c08829160.png
Tilt	-5 to +20°
UNSPSC code	43211902
VESA mounting	100 x 100 mm
Vertical viewing angle	178°
Viewable diagonal size	26.96" (68.47 cm)
pivot	±90°

[1] All specifications represent the typical specifications provided by HP's component manufacturers, actual performance may vary either higher or lower.

[2] DisplayPort™ 1.4 or HDMI 2.0 required to drive panel at its native resolution. The video card of the connected PC must be capable of supporting 2560 x 1440 at 60 Hz with 8-bit color using one DisplayPort™, HDMI.

[3] Included cables may vary by country.

Disclaimer — Copyright

DisplayPort™ is a trademark owned by the Video Electronics Standards Association (VESA®) in the United States and other countries. Microsoft, Encarta, MSN, and Windows are either registered trademarks or trademarks of Microsoft Corporation in the United States and/or other countries.

© Copyright 2025 HP Development Company, L.P. The information contained herein is subject to change without notice. The only warranties for HP products and services are set forth in the express warranty statements accompanying such products and services. Nothing herein should be construed as constituting an additional warranty. HP shall not be liable for technical or editorial errors or omissions contained herein.