



Poly Voyager Legend 30 Headset (AV4P5AA)



Overview

Clear calls — indoors and out.

Enjoy crystal clear calls, anywhere. This headset combines exceptional voice clarity with an all-day wear ergonomic design. Simply connect it to your preferred device and enjoy noise-reducing technology wherever you go.

Yes, everyone can hear you

Stay connected and sound professional no matter the location. Your voice shines through — clear and consistently — whether you're in a bustling café or outdoors with a breeze. Enjoy high-quality calls wherever work takes you.

Freedom to connect on the go

Navigate through your day effortlessly with a flexible and versatile headset. Whether you're heading to a meeting or tackling tasks at home, easily manage calls with on-headset controls and smart sensors.

The comfort you deserve

Designed for all-day wear, this headset features an ergonomic design that wraps you in comfort with a secure fit so you can stay focused on your conversations — even in the busiest environments.

Features

Be heard above the chaos

Important calls can happen anywhere. Make sure your voice is always heard, even when your surroundings get loud, with an aerodynamic boom and 4 noise-canceling microphones.

Years of innovation for everyday comfort

Built to keep up with your busiest days, this legendary headset features a modern look-and-feel, an ergonomic ear loop, and 3 earbud sizes for a better and more secure fit. So comfortable, you'll forget you're wearing it.

Smart controls for easy calls

Manage your calls effortlessly. Smart sensors on the headset answer calls when you put it on and turns on mute when you remove it. Enjoy the freedom to stay engaged in your tasks while staying connected to what matters most.

Take the call anywhere

Six layers of our unique WindSmart technology detect wind direction and respond accordingly so your voice comes through clearly especially outdoors.

Tuned in to the world around you

Stay connected to your calls while remaining aware of your surroundings. The mono design of this headset keeps one ear free, allowing you to stay engaged with what's happening around you — whether you're in a busy office or on the go.

Simple and easy button controls

A legendary design that keeps things simple. Easy-to-find buttons let you control your calls: adjust the volume, mute yourself, even answer and end calls — all right at your fingertips. No fumbling, no hassle, just clear communication.

Specifications

Audio	WindSmart technology
Dimensions (W x D x H)	29.3 x 63.93 x 102.89 mm (headset); 63.49 x 24 x 114.48 mm (charge case)
Dimensions (W x D x H)	1.15 x 2.52 x 4.05 in (headset); 2.5 x 0.95 x 4.51 in (charge case)
Weight	20.5 g (headset); 100 g (charge case)
Weight	0.045 lb (headset); 0.22 lb (charge case)
Package dimensions (W x D x H)	99 x 44 x 159 mm
Package weight	206 g
Battery life	Up to 10 hours
Special features	Smart sensor technology
UPC number	(ABB) 198701663348; (ABL) 198701663355; (ABV) 198990751276; (AC3) 198701663362; (UUF) 198701663386
Manufacturer Warranty	Poly two-years limited warranty
What's in the box	USB Type-C® charging cable; S/M/L eartips; Wireless headset; USB Type-C® to USB Type-A adapter; Quick start guide

Additional specifications

Acoustic protection technology	SoundGuard ^[1]
Battery type	Rechargeable Li-ion
Bluetooth version	Bluetooth® Core 5.4
Boom mic length (ft)	0.25 ft
Boom mic length (mm)	74.8 mm
Button user controls	Power on/off; Mute; Volume +/-; Pairing; Call answer/ignore/end; Voice Assistant
Cartons per layer	15 (ocean and air)
Cartons per pallet	90 (ocean); 120 (air)
Charge time	<1.5 hours
Color	Black
Compatible Operating Systems	Windows 11; macOS; Android™; iOS
Connection type	Wireless: Bluetooth®
Country of origin	Made in Vietnam
Datasheet photo 1	AHID/65d815fdeffd2591db5d8d2260efd9fba4c62c0b
Datasheet photo 2	AHID/61a0ffa6bf4803b7db0c1bc42b53d483a0839a36
Datasheet photo 3	AHID/d87b2337782e580aac01dd433633b6b0085a19a5
Datasheet photo 4	AHID/188861038b376240938580f813c148d0fa37a926
Ear cushions	Silicone (surface material)
Ecolabels	TCO Certified
Headphone type	In-ear (monoaural)
Impedance	16 ohms
Management Software	Poly Lens
Microphone bandwidth	100 Hz to 8 kHz
Microphone type	Noise cancelling
Multipoint technology	Yes, connects to two devices at the same time
Package dimensions (W x D x H)	3.9 x 1.7 x 6.3 in
Package weight	0.45 lb
Paired devices	Up to 8
Pallet (layers)	8 (ocean); 6 (air)
Pallet dimensions	47.2 x 39.4 x 72.8 in (ocean); 47.2 x 39.4 x 55.7 in (air)
Pallet dimensions (W x D x H)	120 x 100 x 185 cm (ocean); 120 x 100 x 141.6 cm (air)
Pallet weight	979.6 lb (ocean); 659.2 lb (air)

Pallet weight	399 kg (ocean); 299 kg (air)
Products per pallet	1440 (ocean); 1080 (air)
Products per pallet layer	180 (ocean and air)
Sensitivity (microphone)	-37 dB FS/Pa
Sensitivity (speaker)	95.5 dB SPL at 1 kHz with 200 mV input
Signal-to-noise ratio	>68 dB
Speaker bandwidth	100 Hz to 20 kHz
Speaker size	13.6 mm
Supported bluetooth profiles	A2DP 1.3; DID 1.3; HSP 1.2; BAS 0.0; AVRCP 1.5; HFP 1.6
UNSPSC code	43191638
Voice alerts	Muted; Incoming call; Battery status
Voice commands	Answer; Ignore
Wireless range	Up to 30 m
Wireless range (imperial)	Up to 98 ft

[1] Protects against Acoustic Shock by limiting sounds to below 118 dBA.

Hybrid Work Solutions

Audio

★ : Recommended

Audio Accessories

Poly Voyager Legend 50/30 Eartips S/M/L	AV4P4AA
Poly Voyager Legend 50/30 Eartips S/M/L	AW6U4AA
Poly Voyager Legend 50/30 Mobile Charge Case	AV4P3AA

Disclaimer — Copyright

© Copyright 2025 HP Development Company, L.P. The information contained herein is subject to change without notice. The only warranties for HP products and services are set forth in the express warranty statements accompanying such products and services. Nothing herein should be construed as constituting an additional warranty. HP shall not be liable for technical or editorial errors or omissions contained herein.

Generated by Dynamic Collateral Tool – (ww-en) – Mar 05, 2025 8:42 PM UTC+0000