



BUSINESS & PRODUCTIVITY

Modern 14

MODERN 14 C13M-1452US

Specification

| | |
|-----------------------|---|
| Manufacturer Part # | MOD14131452 |
| OS | Windows 11 Home (MSI recommends Windows 11 Pro for business) |
| CPU | Intel® Core™ i3-1315u |
| CPU Speed | 1.2 - 4.5Ghz |
| Chipset | - |
| Color | Classic Black |
| Screen Size | 14" FHD IPS-Level 60Hz 45% NTSC |
| Resolution | (1920x1080) 16:9 |
| GPU | UHD Graphics |
| Video Memory | - |
| Keyboard | White backlight keyboard (84 Key) |
| Speaker | 2x Speakers 2W |
| Memory | 8GB (8GB*1) DDR4 3200MHz |
| HDD Capacity | 512GB NVMe SSD |
| HDD Interface | NVMe |
| TPM | - |
| LAN | - |
| WLAN | Intel WiFi 6E AX211 (2x2) |
| Bluetooth | BT 5.3 |
| Card Reader | Micro SD |
| Webcam | 720p HD Webcam |
| USB | 1x USB 3.2 Gen 2; 2x USB 2.0 |
| Type-C Port | 1x USB 3.2 Gen 2 Type C |
| Video Port | HDMI 1.4 (4K @ 30Hz) |
| Audio Port | Mic-in/Headphone-out Combo |
| AC Power Adaptor | 65W [DC-in] |
| Battery Pack | 3 cell (39.3Whr) Li-Polymer |
| Dimension | 12.59" x 8.78" x 0.76" |
| Weight | 3.09 lbs |
| Manufacturer Warranty | 1 year Limited warranty (Include 1 Year Global) |