

Specifications

Eaton 9PX5KTF5G2



Eaton 9PXG2 5000VA 5000W 120/208V
Online Double-Conversion UPS - L6-30P or
Hardwired Input, 18x 5-20R, 2x L6-20R, 1x
L6-30R Outlets, Cybersecure Network Card,
6U Rack/Tower

General specifications

PRODUCT NAME	Eaton 9PX UPS
CATALOG NUMBER	9PX5KTF5G2
UPC	037332294296
PRODUCT LENGTH/DEPTH	27 in
PRODUCT HEIGHT	10.2 in
PRODUCT WIDTH	17.3 in
PRODUCT WEIGHT	203 lb
WARRANTY	3 year limited
COMPLIANCES	CISPR22 Class A / FCC part 15 Class A CE Marked FCC Part 15
CERTIFICATIONS	NOM cULus Listed IEC 62040-2:2006 Cat C2 ENERGY STAR certified



Powering Business Worldwide

Battery

BATTERY MANAGEMENT	ABM+ technology uses battery replacement analytics to predict when you should replace UPS batteries based on real-life usage and conditions.
BATTERY REPLACEMENT	Hot-swappable internal batteries and extended battery modules (EBMs). Replacement battery part # EBP-1805 (qty 1 per UPS)
BATTERY TYPE	Sealed, lead-acid
EXTENDED BATTERY CAPABILITY	Add up to 12 EBMs, part # 9PXEBM180RTG2

Electrical input

INPUT CONNECTION	L6-30P and hardwire input supported
INPUT CORD LENGTH	10 ft
INPUT NOMINAL VOLTAGE	208V default (200/208/220/230/240V)
INPUT FREQUENCY RANGE	60 Hz: 50–70 Hz, 50 Hz: 40–60 Hz
INPUT POWER FACTOR	>0.99 typical

Environmental

ALTITUDE	3000 m
BTU RATING	Online: 655 BTU/hr, Battery: 935 BTU/hr, High Efficiency: 190 BTU/hr
NOISE LEVEL	<43 dB at 1 meter
RELATIVE HUMIDITY	0-95% non-condensing
TEMPERATURE RANGE	0° to 40°C (32° to 104°F)

Electrical output

RECEPTACLE	(18) 5-20R, (2) L6-20R, (1) L6-30R, Hardwire (200-240V)
TOPOLOGY	Online/Double-conversion
WATTAGE	5000W
VA RATING	5000 VA
OUTPUT WAVEFORM	True sine wave
VOLTAGE	120/208V
OUTPUT POWER FACTOR	1.0
OUTPUT VOLTAGE RANGE	±1% steady-state
OUTPUT FREQUENCY	50/60 Hz

Communications

EXPANSION SLOTS	(1) Mini-Slot (MS) expansion port with Gigabit Network Card (NETWORK-M3) included
ETHERNET INTERFACE	Yes
INCLUDES NETWORK CARD	Yes
SOFTWARE COMPATIBILITY	Brightlayer Data Centers suite
USER INTERFACE	Graphical display, 5-button programmable menu, LED indicator

Additional specifications

SPECIAL FEATURES	Gigabit Network Card (NETWORK-M3) included
FORM FACTOR	Rack/tower
RACK SIZE	6U
RACK MOUNTING KIT	Yes
EFFICIENCY	96%

PACKAGE CONTENTS	<ul style="list-style-type: none">• 5000VA 5000W 9PX G2 Online Double-Conversion UPS• 9PXTFMR5G2 120V step-down transformer• NETWORK-M3 Gigabit network card• USB cable• RS-232 cable• Cable gland for hardwire connection• Rack-mounting hardware• Tower support stands• Quick Start Guide
-------------------------	---

SURGE PROTECTION	Yes
-------------------------	-----

INTERNAL BYPASS

Yes

Warranty and support

STANDARD FACTORY WARRANTY

- 3-YEAR FACTORY WARRANTY
- - 3 years
- - Parts, electronics and batteries coverage
- - Standard ground shipping
- - Technical support

EXTENDED SERVICE PLANS

- ADVANCED DEPOT EXCHANGE
- - 5-year depot repair: 9SW5Y-6000UC
- - Expedited parts coverage for 5 years
- - Parts, electronics and UPS batteries coverage
- - Next business day shipping
- - Technical support
-
- 5 YEAR ON-SITE PLAN: WFLN75XX-6009UC
- - On-site parts and labor coverage for 5 years
- - Parts, electronics and UPS batteries coverage
- - 24x7 on-site labor coverage, next day response
- - Next-day shipping
- - Technical support

Resources

BROCHURES

[9PX G2 3-11kVA VRLA full brochure](#)

[9PX5KTF5G2 feature focus](#)

DRAWINGS

[Eaton 9PX G2 UPS 9PX3K3UG2 9PX5KG2 9PX6KG2 2D drawing](#)

[Eaton 9PX G2 9PXTFMR5G2 2D drawing](#)

SPECIFICATIONS AND DATASHEETS

[9PX5KTF5G2 runtime graph](#)

TECHNICAL DATA SHEETS

[Eaton 9PX G2 UPS 5-6kVA technical specifications](#)

WARRANTY GUIDES

[9PX three year limited warranty](#)

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

Follow us on social media to get the latest product and support information.

All other trademarks are property of their respective owners.

