

DURABOOK

Prepared for the Unexpected



R11L Tablet

Ultra affordable with feature-rich functionality

- 11.6" FHD DynaVue® SR display with 1000 nits
- Long-Life Battery up to 15 hours
- 12th Generation Intel® Pentium® 8505
- Optional barcode, RFID & smart card reader
- Intel® Wi-Fi 6E AX211 & Bluetooth® V5.3
- 10-point capacitive multi-touch panel with four touch modes



**Dyna
Vue**

DURABILITY	- MIL-STD 810H certified (Drop, Shock, Vibration, Rain, Dust, Altitude, Freeze/Thaw, High/Low Temperature, Temperature Shock, Humidity) - MIL-STD 461F certified (Conduction, Radiation, Conducted Susceptibility, Radiated Susceptibility) - Optional ANSI/UL 121201, Class I, Division 2 4' drop 26 faces - IP 66 certified - Aluminum-magnesium alloy chassis - Port covers - Optional sunlight readable display
OPERATING SYSTEM	Windows® 11 Pro 64-bit
PROCESSOR	Intel® Pentium® Gold Processor 8505 (12MB Cache, up to 4.4 GHz, 1P+4E cores)
GRAPHICS	Intel® UHD Graphics
MEMORY	1 slot 8GB (4800MHz DDR5)
STORAGE	128GB NVMe PCIe SSD
DISPLAY	11.6" FHD (1920 × 1080) - Optional 1000 nits DynaVue® sunlight readable display with capacitive multi-touch screen - User selectable touch mode for Finger/Wa-ter, Glove, or Stylus programmable function
AUDIO	- Integrated microphone - Intel® High Definition Audio Compliant - Integrated speaker × 1
CAMERA	- Integrated 2.0 MP front-facing camera - Optional 8.0 MP auto-focus rear camera with flash
KEYBOARD & INPUT	6 buttons (2 user-definable keys)
COMMUNICATONS	- Intel® Wi-Fi 6E AX211 (802.11 ax) - Bluetooth® V5.3 - Optional dedicated GPS module (UBLOX-NEO-M8N)¹ - Optional GPS and 4G LTE multi-carrier mobile broadband¹ - Optional RF antenna pass-through for GPS and WWAN¹

SECURITY	- TPM 2.0 - NIST BIOS compliant - Stealth mode - Kensington lock - Optional night vision mode⁴ - Optional smart card reader² - Optional LF/HF-RFID (NFC) reader²
I/O INTERFACES	- Thunderbolt 4 × 1 - USB 3.2 Gen 2 (type A) × 1 - Micro HDMI × 1 - Audio in/out (combo jack) × 1 - microSD card (microSDXC) × 1 - Docking connector (35-pin Pogo) × 1 - Nano SIM card × 1 - DC-In jack × 1 - Optional 10/100/1000 Ethernet (RJ-45) × 1² - Optional smart card reader × 1² - Optional 1D/2D barcode reader × 1 - Optional RF antenna pass-through for GPS and WWAN¹
EXPANSION SLOT	Optional RJ-45 × 1 or LF/HF-RFID (NFC) or smart card reader or MSR+smart card reader or RJ-45/RS-232/smart card reader²
POWER	AC adapter : 100-240V, 50Hz-60Hz, 65W Main battery Li-Ion, 11.1V, 3950mAh, 8.5 hours ³ Optional long life battery Li-Ion 11.1V, 6900mAh, 15 hours³
ENVIRONMENT	- Temperature Operating : - 20°C ~ 60°C / - 4°F ~ 140°F Storage : - 40°C ~ 71°C / - 40°F ~ 160°F - Humidity : 5% ~ 95%
DIMENSION & WEIGHT	11.73" (L) × 7.56" (W) × 0.79" (H) 2.65lbs
WARRANTY	3-year Accidental Damage Warranty

1. GPS/WWAN and dedicated GPS are mutually exclusive.
2. Mutually exclusive options.
3. Tested using the MobileMark 2014 battery life benchmark. Results may vary under different situations including hardware configuration, software, operating conditions, power management settings and other factors.
4. Night vision mode is available only for sunlight readable display.