

OVERVIEW

Basic rPDUs deliver reliable power to critical IT equipment within a rack or cabinet.

Benefits

- Reliable rack power distribution.
- Every unit is 100% tested for reliability and functionality.
- Simple and convenient configuration options for cord lengths and chassis colors.
- Standard five-year limited warranty.



Part #: VP0N3100

Model Number: MN00X1R1-16MCQ9-3TL14A0A10-S

Category: Basic

Sub Category: Standard

Power Configuration: 30A, 120/208V, 5.7kW

Physical Configuration: 19in / 483mm, Horizontal


Product Summary: rPDU, Basic, Standard, 30A, 120/208V, 5.7kW, Horizontal, (12) Combination C13/C19, (4) NEMA 5-20R, 10ft power cord with L14-30P, Black Powder Coat.

Plug Form:



L14-30P

Receptacle:



Combination C13/C19
(Quantity: 12)



NEMA 5-20R
(Quantity: 4)

Chassis Color Options:



To discuss color options, contact your local sales representative.

Product Specification and Options

System Features	
Quantity Of Inputs	1
Voltage	100-120/200-240V
Current	30A
VA per Input (Load Capacity)	5.7kW (208V)
Frequency	50/60Hz
Over Current Protection	(2) 20A Double Pole Magnetic Breakers (10kAIC Rated)
Switch	Breaker/Switch Combination
Power Cable Wire Gauge	10/4
Power Cable Length	10ft / 3m
Power Entry Location	Rear
Plug Type	NEMA L14-30P Twistlock
Combined Total Receptacle/Socket Quantity	16
Receptacle/Socket Type #1	Combination C13/C19
- Quantity on Rear	12
- Quantity per Breaker	6
- Style	Banks of 6
- Voltage per Receptacle/Socket	208V
Receptacle/Socket Type #2	NEMA 5-20R
- Quantity on Rear	4
- Quantity per Breaker	2
- Style	Individual
- Voltage per Receptacle/Socket	120V
Maximum Operating Temperature	60C / 140F
Heavy Steel - Powder Coat Finish	Black
Configuration	1U
Adjustable Mount Brackets	Yes
Country of Origin	USA, TAA Compliant and Buy American Act COTS Compliant
Product Warranty	5-year limited warranty
Certification/Agency Approvals	UL & c-UL Listed 62368-1
Certification/Agency Approvals	RoHS Compliant
Chassis Dimensions (HxWxD)	1.72in x 17in x 8.5in / 44mm x 432mm x 216mm
Shipped Weight	15lbs (6.8kg)