



HP Series 3 Pro 23.8 inch FHD Monitor - 324ph (B0BU9UT)

Overview

Redefine the everyday

Expand your view in comfort with a spacious, thoughtfully designed 23.8 inches of workspace. Boasting a crisp, smooth screen and a simple yet functional design, this HP Series 3 Pro 23.8" FHD monitor lets you work better all day.

100Hz

Elevate your visual experience

Make your day more productive and enjoyable with an expanded workspace for projects and assignments. This sleek 23.8-inch FHD monitor boasts a quality IPS screen that's visible from any angle and up to 100 Hz refresh rate[1] for sharp images and fluid motion.



Clean design

Keep the focus on your screen with a sleek, simple design. Make borders disappear with a 3-sided micro-edge bezel ideal for clean dual-monitor setups and 2 x 2W downfiring speakers built right in. Easily customize settings with the joystick OSD button.

HP Eye Ease

Focus in comfort

Stay in the zone without sacrificing eye comfort with a flicker-free screen and HP Eye Ease, an always-on hardware low-blue light filter that doesn't impact color accuracy. Plus, find your perfect angle with a 100 mm height- and tilt-adjustable stand.



Built for a better tomorrow

This thoughtfully designed monitor contains at least 85% recycled plastic content in the enclosure, 5% recycled metal, and 20% recycled glass in the panel[2]. Plus, it meets high energy-saving standards with ENERGY STAR® certification and EPEAT® registration[3].

Features

IPS Technology

No matter where you stand, IPS technology ensures image accuracy and consistency across wide 178-degree horizontal and vertical viewing angles.

100 Hz Refresh Rate

Experience smooth scrolling, life-like video and clear detail with a 100 Hz refresh rate that provides fluid movement from frame to frame.^[1]

Plenty of Ports

This monitor is ready to connect for sharp FHD visuals with multiple ports including 1 x VGA, 1 x HDMI 1.4, and 1 x DisplayPort™ 1.2.^[4,5]

HP Eye Ease

HP Eye Ease, an always-on, hardware low-blue light filter, helps keep your eyes comfortable throughout the day by reducing blue light without the yellow color shift.

Height and Tilt Adjust

The 100 mm height- and tilt-adjustable slim stand helps you find the right angle so you can maximize productivity and work comfortably.

3-Sided Micro-Edge Bezel

See and do more on your screen with a 3-sided micro-edge bezel that maximizes your viewing area for a sleek design and virtually seamless dual-monitor setups.

[1] All performance specifications represent the typical specifications provided by HP's component manufacturers; actual performance may vary either higher or lower. 100 Hz refresh rate can be supported via HDMI and DisplayPort™ cable connection only. 60 Hz refresh rate with VGA.

[2] Recycled plastic content percentage is based on the definition set in the IEEE 1680.1-2018 EPEAT® standard. Recycled plastic is expressed as a percentage of the total weight plastic. Recycled metal is expressed as a percentage of the total weight of the metal according to ISO 14021 definitions for metal parts over 25 grams. Percentage of recycled glass in the monitor panel varies by product. Recycled glass is expressed as a percentage of the total weight of the glass.

[3] Based on US EPEAT® registration according to IEEE 1680.1-2018 EPEAT®. EPEAT® status varies by country. Visit www.epeat.net for more information.

[4] FHD content is required to view FHD images.

[5] Cable included in box varies by region.

Specifications

Color	Black
Display size (diagonal)	23.8"
Panel technology	IPS; LCD
Display size (diagonal)	60.5 cm (23.8")
Aspect ratio	16:9 ^[1]
Native resolution	FHD (1920 x 1080) ^[1,2]
Resolutions supported	640 x 480 @ 60 Hz; 720 x 400 @ 70 Hz; 800 x 600 @ 60 Hz; 1024 x 768 @ 60 Hz; 1280 x 720 @ 60 Hz; 1280 x 1024 @ 60 Hz; 1440 x 900 @ 60 Hz; 1600 x 900 @ 60 Hz; 1680 x 1050 @ 60 Hz; 1920 x 1080 @ 60 Hz; 640 x 480 @ 75 Hz (digital inputs only); 800 x 600 @ 75 Hz (digital inputs only); 1024 x 768 @ 75 Hz (digital inputs only); 1280 x 1024 @ 75 Hz (digital inputs only); 1920 x 1080 @ 50 Hz (digital inputs only); 1920 x 1080 @ 75 Hz (digital inputs only); 1920 x 1080 @ 100 Hz (digital inputs only); 1280 x 800 @ 60 Hz
Pixel pitch	0.2745 x 0.2745 mm ^[1]
Brightness	250 nits ^[1]
Contrast ratio	1000:1 ^[1]
Response time (typical)	5ms GtG (with overdrive) ^[1]
Dimensions (W x D x H)	53.89 x 4.94 x 32.42 cm (without stand)
Dimensions (W x D x H)	21.22 x 1.94 x 12.76 in (without stand)
Dimensions With Stand (W x D x H)	53.89 x 19.63 x 46.92 cm
Weight	3.4 kg (without stand); 4.71 kg (with stand)
Weight	7.5 lb (without stand); 10.38 lb (with stand)
Onscreen controls	Brightness+; Color; Image; Input; Power; Menu; Management; Information; Exit
Display colors	Up to 16.7 million colors supported ^[1,3]
Display scan frequency (horizontal)	30-115 kHz ^[1]
Display scan frequency (vertical)	48-100 Hz ^[1]
Power	100 - 240 VAC 50/60 Hz
Power consumption	35 W (maximum), 23 W (typical), 0.5 W (standby)
Operating temperature range	5 to 35°C
Operating humidity range	20 to 80% RH (non-condensing)
Sustainable impact specifications	Low halogen; Molded paper pulp cushion inside box is 100% sustainably sourced and recyclable; 85% post-consumer recycled plastic; Contains 20% recycled glass in the monitor panel; At least 5% recycled metal
Certifications and compliances	Australia MEPS; Bauart; CCC; CE; CEL; C-Tick; cTUVus; EAC; E-standby (Korea); EUP Lot-5; EUP Lot-6; FCC; ISO 9241-307; KC (Korean) requirements; KCC (Korean) requirements; NOM (Mexico); PSB for Singapore; RCM; SEPA; S-Mark for Argentina; Taiwan BSMI; VCCI; Vietnam MEPS; Ukraine Energy label; California Energy Commission (CEC); South Africa Energy; EUP Lot 26; Mexico Energy; UAE; TGM; India BIS; Cambodia ISC; IC; NRCS; PSE; Ukraine CoC; Ukraine DOC; CEL Grade 2; CB(62368-1); CB 60950
Physical security	Security lock-ready ^[5]
Management Software	HP Display Center; HP Client Management Script Library
UPC number	198828035578
Manufacturer Warranty	HP three-year limited warranty
What's in the box	Monitor; HDMI cable; Warranty card; Quick Setup Poster; AC power cord ^[4]

Additional specifications

Backlight lamp life minimum (to half brightness)	30,000 hours
Backlight type	Edge-lit; WLED
Base area footprint (imperial)	7.28 x 7 in
Base area footprint (metric)	18.5 x 17.8 cm
Bezel	3-sided borderless
Color gamut	72% NTSC
Country of origin	Made in China and Thailand
Curvature	Flat
Datasheet photo 1	https://hp.widen.net/content/iv3dmfjgnw/png/HP_Series_3_Pro_23.8inch_FHD_Monitor_324pf_Black_Coreset_ScrnSS_Front_WhiteBG_M2867794.png?w=800&h=800&position=c&color=ffffff00&quality=80&u=dlkxlp
Datasheet photo 2	https://hp.widen.net/content/mhca8kbdun/png/HP_Series_3_Pro_23.8inch_FHD_Monitor_324pf_Black_Coreset_ScrnSS_FrontRight_WhiteBG_M2867792.png?w=800&h=800&position=c&color=ffffff00&quality=80&u=dlkxlp
Datasheet photo 3	https://hp.widen.net/content/kh7eh3qc8f/png/HP_Series_3_Pro_23.8inch_FHD_Monitor_324pf_Black_Coreset_Rear_WhiteBG_M2867795.png?w=800&h=800&position=c&color=ffffff00&quality=80&u=dlkxlp
Datasheet photo 4	AHID/62013cc9ea293bbc65cf178bb2e35fea9ee22fa
Detachable stand	Yes
Display area (imperial)	20.75 x 11.67 in
Display area (metric)	52.7 x 29.65 cm
Display contrast ratio (dynamic)	8000000:1
DisplayPort™	1 DisplayPort™ 1.2
Ecolabels	TCO Certified; TCO Certified Edge; EPEAT® registered with Climate+
Energy star certified	ENERGY STAR® certified
Flicker-free	Yes (TÜV certified)
HDCP	Yes, DisplayPort™ and HDMI
HDMI	1 HDMI 1.4
Hardness	3H ^[1]
Haze	25%
Height adjustment range	100 mm
Horizontal viewing angle	178°
Low blue light	Yes, HP Eye Ease (TÜV Low Blue Light Hardware Solution certified) ^[1]
Non-Operating Humidity Range	5 – 95%
Non-operating temperature - Celsius	-40 to 65°C
Non-operating temperature - fahrenheit	-40 to 149°F

Operating altitude	Up to 16,400 ft
Operating altitude	Up to 5,000 m
Operating temperature range	41 to 95°F
Package dimensions (W x D x H)	23.43 x 4.88 x 15.39 in
Package dimensions (W x D x H)	59.5 x 12.4 x 39.1 cm
Package weight	14.86 lb
Package weight	6.74 kg
Pallet (layers)	Pallet: 5 layers (20 ft, 40 ft); Slip sheet: 6 layers (40 ft HQ)
Pallet dimensions	Slip sheet: 47.24 x 39.45 x 77.95 in (20 ft, 40 ft); Slip sheet: 47.24 x 39.45 x 93.46 in (40 ft HQ); Pallet: 47.24 x 39.45 x 82.68 inch (20 ft, 40 ft); Pallet: 47.24 x 39.45 x 98.19 in (40 ft HQ)
Pallet dimensions (W x D x H)	Slip sheet: 120 x 100.2 x 198 cm (20 ft, 40 ft); Slip sheet: 120 x 100.2 x 237.4 cm (40 ft HQ); Pallet: 120 x 100.2 x 210 cm (20 ft, 40 ft); Pallet: 120 x 100.2 x 240 cm (40 ft HQ)
Pallet weight	Slip sheet: 11898.35 lb (20 ft); Slip sheet: 24974.41 lb (40 ft); Slip sheet: 29967.08 lb (40 ft HQ); Pallet: 11931.42 lb (20 ft); Pallet: 25007.48 lb (40 ft); Pallet: 30000.15 lb (40 ft HQ)
Pallet weight	Slip sheet: 5397 kg (20 ft); Slip sheet: 11328.2 kg (40 ft); Slip sheet: 13592.84 kg (40 ft HQ); Pallet: 5412 KG (20 ft); Pallet: 11343.2 kg (40 ft); Pallet: 13607.84 kg (40 ft HQ)
Panel bit depth	8 bit (6 bit + FRC) ^[1]
Pixels per inch (ppi)	93 ppi ^[1]
Power supply type	Internal
Product caption image	https://prismui-int.inc.hpcorp.net/PRO.Crystal.1/DAMHandler/Accessories/324ph - Cinder Front_Adnotation.png
Product caption image	https://prismui-int.inc.hpcorp.net/PRO.Crystal.1/DAMHandler/Accessories/324ph - Cinder Rear_Adnotation.png
Product color	Black
Product dimensions with stand (W x D x H)	21.22 x 7.73 x 18.47 in
Products per pallet	80
Products per pallet layer	16
Refresh rate (maximum)	100 Hz
Resolution (maximum)	FHD (1920 x 1080 @ 100 Hz) ^[1]
Screen treatment	Anti-glare
Speaker output power	2 x 2 W
Speaker type	Built-in speakers
Special features	Works with Chromebook
Stand color	Black
Stand type	Base stand; With stand; Height adjustable stand
Storage altitude	Up to 12,192 m
Storage altitude	Up to 40,000 ft

Technology logo 1	https://h10003.www1.hp.com/digmedialib/prodimg/lowres/c03123379.png
Technology logo 2	https://h10003.www1.hp.com/digmedialib/prodimg/lowres/c08717783.png
Technology logo 3	https://h10003.www1.hp.com/digmedialib/prodimg/lowres/c08737446.png
Tilt	-5 to +23°
UNSPSC code	43211902
VESA mounting	100 x 100 mm
VGA	1 VGA
Vertical viewing angle	178°
Viewable diagonal size	23.8" (60.45 cm)

[1] All specifications represent the typical specifications provided by HP's component manufacturers, actual performance may vary either higher or lower.

[2] DisplayPort™ 1.2 or HDMI 1.4 required to drive panel at its native resolution. The video card of the connected PC must be capable of supporting 1920 x 1080 at 60 Hz with 8-bit color using one HDMI, DisplayPort™ or VGA.

[3] Number of colors through A-FRC technology.

[4] Included cables may vary by country.

[5] Lock sold separately.

Services

HP Care Pack Services

★ : Recommended

Personal Systems Hardware Support Onsite Service

HP 3y Next Business Day Response Onsite Large Display Hardware Support	U7NR9E ★
HP 4y Next Business Day Response Onsite Large Display Hardware Support	U7936E ★
HP 5y Next Business Day Response Onsite Large Display Hardware Support	U7937E ★
HP 1y Post Warranty Next Business Day Response Onsite Large Display Hardware Support	U4926PE

Workforce Computing

Certified Refurbished Services (Workforce Computing)

HP Carbon Neutral Computing Services - To the Door Service for Displays.	U53DHE
HP Carbon Neutral Computing Services - To the Door with Usage Service for Displays	U53DJE

Accessories for PC

Stands/Mounting Brackets

★ : Recommended

Mounting Brackets

HP B200 PC Mounting Bracket	762T5AA
HP B550 PC Mounting Bracket	16U00AA

Stands

HP Quick Release Monitor Single Arm	762U0AA
-------------------------------------	---------

Security

Security Cables

HP Business PC Security Lock v3 Kit	3XJ17AA
-------------------------------------	---------

Disclaimer — Copyright

EPEAT® is a registered trademark of Green Electronics Council. ENERGY STAR® is a registered mark owned by the U.S. government. © 2024 Google LLC All rights reserved. Chrome is a trademarks of Google LLC.

The product could differ from the images shown. © 2014 Hewlett-Packard Development Company, L.P. The Information contained herein is subject to change without notice. Warranties for HP products and services are set out in the express warranty statements accompanying such products and services. In addition, our products and services come with guarantees that cannot be excluded under the Australian Consumer Law. Subject to the foregoing, nothing herein should be construed as constituting an additional warranty. HP shall not be liable for technical or editorial errors or omissions contained herein.

Generated by Dynamic Collateral Tool – (au-en) – May 11, 2025 9:06 AM UTC+0000