



L A P T O P S

Thin A15

T H I N A 1 5 B 7 V E - 2 1 4 U S

Specification

Manufacturer Part #	THINA15B7214
OS	Windows 11 Home (MSI recommends Windows 11 Pro for business)
CPU	Ryzen 5 7535HS
CPU Speed	3.2 - 4.75GHz
Chipset	-
Color	Black
Screen Size	15.6" FHD, IPS-Level 144Hz 45% NTSC
Resolution	(1920x1080) 16:9
GPU	NVIDIA® GeForce RTX™ 4050 Laptop GPU
Video Memory	6G GDDR6
Keyboard	Blue keyboard with Anti-Ghost key (99 Key)
Speaker	2x Speakers 2W
Memory	16GB (8G*2) DDR4 3200MHz
HDD Capacity	512GB NVMe SSD
HDD Interface	NVMe
TPM	AMD fTPM
LAN	Gb LAN
WLAN	AMD RZ616 Wi-Fi 6E
Bluetooth	BT 5.3
Card Reader	-
Webcam	720p HD Webcam
USB	3x USB 3.2 Gen1
Type-C Port	1x USB 3.2 Gen1 w/DP1.4
Video Port	v 2.1 8K@60Hz 4K@120Hz
Audio Port	1 Mic in/ 1 headphone out
AC Power Adaptor	120W
Battery Pack	3 cell , 52.4Whr Li-Polymer
Dimension	14.13"x9.99"x0.85"
Weight	4.10 lbs
Copilot+ Ready	*Copilot key feature availability varies by market, see aka.ms/Keysupport
Manufacturer Warranty	1 year Limited warranty (Include 1 Year Global)