

Specifications



Eaton

EMAGKEA5A5A5A5L

3-Phase Managed HDX Rack PDU G4, 208V, 48 Outlets (24 C13 + 24 C39), 100A, 36kW, Hardwired Input, 0U Vertical, TAA

General specifications

PRODUCT NAME	Eaton managed PDU
CATALOG NUMBER	EMAGKEA5A5A5A5L
UPC	037332296351
PRODUCT LENGTH/DEPTH	2.48 in
PRODUCT HEIGHT	75.98 in
PRODUCT WIDTH	4.09 in
PRODUCT WEIGHT	29.83 lb
COMPLIANCES	CE Marked FCC Class A TAA Compliant
CERTIFICATIONS	UL Listed cUL Listed

Product specifications

FORM FACTOR	0U (Vertical)
PHASE	3-Phase
INPUT CONNECTION	Hardwire
OUTLETS	48
CORD LENGTH	0
FREQUENCY RATING	50/60 Hz
OPERATING TEMPERATURE	0° to 60°C (32° to 140°F)

Resources

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

