


Specifications



Eaton

EMAGFFA5A5A5A5L

3-Phase Managed HDX Rack PDU G4,
240/415V, 48 Outlets (24 C13 + 24 C39), 60A,
35kW, 560P6W Input, 6 ft. Cord, 0U Vertical,
TAA

General specifications

PRODUCT NAME	Eaton managed PDU
CATALOG NUMBER	EMAGFFA5A5A5A5L
PRODUCT LENGTH/DEPTH	2.48 in
PRODUCT HEIGHT	75.98 in
PRODUCT WIDTH	4.09 in
PRODUCT WEIGHT	29.83 lb
COMPLIANCES	CE Marked FCC Class A TAA Compliant
CERTIFICATIONS	UL Listed cUL Listed

Product specifications

FORM FACTOR	0U (Vertical)
PHASE	3-Phase
INPUT CONNECTION	Other
OUTLETS	48
CORD LENGTH	6 ft
FREQUENCY RATING	50/60 Hz
OPERATING TEMPERATURE	0° to 60°C (32° to 140°F)

Resources

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

