

PERFORMANCE

Processor

Intel® Core™ Ultra 7 265T, 20C (8P + 12E) / 20T, Max Turbo up to 5.3GHz, 30MB

AI PC Category^[1]

AI PC

NPU

Integrated Intel® AI Boost, up to 13 TOPS

Graphics

Integrated Intel® Graphics

Chipset

Intel® Q870 Chipset

Memory

1x 16GB SO-DIMM DDR5-5600

Memory Slots

Two DDR5 SO-DIMM slots, dual-channel capable

Max Memory^[2]

Up to 64GB DDR5-5600

Storage

512GB SSD M.2 2280 PCIe® 4.0x4 NVMe® Opal 2.0

Max Storage Support^{[3][4]}

Up to two drives, 2x M.2 SSD
• M.2 SSD up to 1TB each

Optical

External 9.0mm DVD±RW

Audio Chip

High Definition (HD) Audio, Realtek® ALC233NL-VB2-CG codec

Speakers

2Wx2

Camera

5.0MP + IR Hybrid

Microphone

2x, Array

Power Supply

90W 89% Adapter

DESIGN

Display^[5]

23.8" FHD (1920x1080) IPS Anti-glare 250nits, 120Hz, 99% sRGB, hardware low blue light, flicker free, eyesafe, touch

Touchscreen

10-point Multi-touch

Keyboard

USB, Calliope, Black, English (US)

Mouse

USB Calliope Mouse, Black

Expansion Slots

Three M.2 slots (one for WLAN, two for SSD / discrete NPU)

Case Color

Black

Stand

UltraFlex V Stand

Mounting

VESA mount

Pen

Pen Not Supported

Form Factor

AIO (23.8 inches)

Dimensions (WxDxH)^[6]

Lowest in flat mode: 539.6 x 333.45 x 224.10 mm (21.24 x 13.13 x 8.82 inches)

Highest in vertical mode: 539.6 x 264.91 x 455.94 mm (21.24 x 10.43 x 17.95 inches)

Weight^[7]

7.16 kg (15.79 lbs, maximum configuration)

CONNECTIVITY

WLAN + Bluetooth®

Intel® Wi-Fi® 6E AX211, 802.11ax 2x2 + BT5.3, vPro®

WWAN

Non-WWAN

Ethernet

Integrated 100/1000M

Rear Ports

- 2x USB-A (USB 10Gbps / USB 3.2 Gen 2)
- 2x USB-A (USB 5Gbps / USB 3.2 Gen 1), one supports Smart Power On
- 1x HDMI® (HDMI® in 1.4 / HDMI® out 2.1 TMDS combo port)
- 1x DisplayPort™ 1.4a (HBR2)
- 1x Ethernet (RJ-45)

Right Ports

- 1x USB-A (USB 10Gbps / USB 3.2 Gen 2)
- 1x USB-C® (USB 10Gbps / USB 3.2 Gen 2), support data transfer and 5V@3A charging
- 1x headphone / microphone combo jack (3.5mm)

SECURITY & PRIVACY

Security Chip

Discrete TPM 2.0, TCG certified, FIPS 140-2 certified

Fingerprint Reader

No fingerprint reader

Physical Locks

Kensington® Security Slot™, 3 x 7 mm

Other Security

ThinkShutter camera cover (camera models)

MANAGEABILITY

System Management^[8]

Intel® vPro® Enterprise

SERVICE

Base Warranty

3-year, Onsite

CERTIFICATIONS

Green Certifications

- ENERGY STAR® 9.0
- EPEAT™ Gold Registered
- TCO edge
- TCO Certified 10.0
- ErP Lot 3
- GREENGUARD®
- RoHS compliant

Other Certifications

- Anti-dust
- IP55-compliant (front face, for touch models)
- Healthcare compliance: Part of IEC 60601-1 / IEC 60601-1-2
- Eyesafe® Certified 2.0
- SGS Performance Tested certification: Extreme Comfortable Noise
- TÜV Rheinland® Flicker Free
- TÜV Rheinland® Low Blue Light (Hardware Solution)

Mil-Spec Test

MIL-STD-810H military test passed (Low Pressure [Altitude], High Temperature, Low Temperature, Temperature Shock, Humidity, Sand and Dust, Vibration, Shock, Fungus, Solar Radiation, Contamination by Fluids, Salt Fog)

SOFTWARE

Operating System

Windows® 11 Pro, English

MODEL

TopSeller	: Yes	Announce Date	: 2025-03-25
EAN / UPC / JAN	: 198157007888	End of Support	: N/A

Note:

^[1] AI PCs have a NPU capable of 10+ TOPs to run the Copilot assistant by pressing the optional Microsoft Copilot key or using Win + C.

^[2] The max memory is based on the test results with current.....

• Lenovo reserves the right to change specifications without notice.

• California Electronic Waste Recycling Fee In California, per state law, Lenovo charges an electronic waste recycling fee on this covered device at the time of sale of the product. For more information, go to: <https://www.calrecycle.ca.gov/Electronics/Consumer>

To see more note information, please access the [web page](#).

Premier Support - A direct 24x7x365 line to our most elite technicians.



Advanced technical support, 24x7x365, in more than 100 markets



Technical Account Managers for proactive relationship and escalation management



Comprehensive hardware & OEM software support



Priority on service delivery and repair parts



Single point of contact for simplified end-to-end case management



Lenovo Service Connect Portal for customized reporting and product support

Accidental Damage Protection - Protection of your PC from the unexpected.

Experience shows that a significant portion of devices may be damaged (and not covered under warranty) in the first three years. Lenovo's Accidental Damage Protection service covers accidents beyond the system warranty such as drops, spills, bumps and even electrical surges. Make sure your new device has maximum protection, avoid unplanned costs and get peace of mind.

Base Warranty - Included with the systems you purchase, default 1- or 3-year coverage window.

Warranty Extensions & Upgrades - Service and protection that's right for your circumstances.

- Pick Up & Return Courier
- Onsite Support
- Technician Installed Customer
- Replaceable Unit Service
- International Warranty Upgrade

Lenovo may not offer the products, services or features discussed in this document in all regions. Lenovo may withdraw an offering at any time. Information is subject to change without notice. Consult your local representative for information on offerings available in your area. Lenovo reserves the right to change specifications or other product information without notice. Lenovo is not responsible for photographic or typographical errors. Lenovo provides this publication "as is" without warranty of any kind, either express or implied, including the implied warranties of merchantability or fitness for a particular purpose.

Recommended Accessories



Lenovo USB-C to Ethernet Adapter

4X90S91831

The Lenovo USB-C to Ethernet Adapter is quick and easy way to connect your USB-C enabled notebook to Ethernet connections. It's ideal for imaging of systems or transferring large files quickly.

Recommended Services

BEST	4Y Premier Support Plus upgrade from 3Y Onsite (5WS1L39082)
BETTER	3Y Premier Support Plus upgrade from 3Y Onsite (5WS1L39129)
GOOD	3Y Premier Support Upgrade from 3Y Onsite (5WS0U26648)

Please click [here](#) to view the full list of accessories.



PSREF
Product Specifications
Reference