

PERFORMANCE

Processor
Intel® Core™ Ultra 5 235T, 14C (6P + 8E) / 14T, Max Turbo up to 5.0GHz, 24MB

AI PC Category^[1]
AI PC

NPU
Integrated Intel® AI Boost, up to 13 TOPS

Graphics
Integrated Intel® Graphics

Chipset
Intel® Q870 Chipset

Memory
1x 16GB SO-DIMM DDR5-5600

Memory Slots
Two DDR5 SO-DIMM slots, dual-channel capable

Max Memory^[2]
Up to 64GB (2x 32GB DDR5 SO-DIMM)

Storage
512GB SSD M.2 2280 PCIe® 4.0x4 NVMe® Opal

Max Storage Support^[3]
Up to two drives, 2x M.2 2280 SSD
• M.2 2280 SSD up to 2TB

RAID Preset
None

Card Reader
No card reader

Optical
None

Audio Chip
High Definition (HD) Audio, Realtek® ALC233VB or Conexant CX11771 codec

Speakers
2Wx1

Power Supply
90W 89% Adapter

DESIGN

Keyboard
USB Traditional Keyboard, Black, English

Mouse
USB Calliope Mouse, Black

Expansion Slots
Three M.2 slots (one for WLAN, two for SSD / discrete NPU)

Case Color
Black

Stand
Vertical Stand

Adapter Cage
None

Toolless Chassis Screw
None

Dust Filter
None

Mounting
None

IO Box
None

Pen
Pen Not Supported

Form Factor
Tiny (1L)

Dimensions (WxDxH)^[4]
179 x 182.9 x 36.5 mm (7.05 x 7.2 x 1.44 inches)

Weight^[5]
Around 1.18 kg (2.6 lbs)

CONNECTIVITY

WLAN + Bluetooth^[6]
Intel® Wi-Fi® 6E AX211, 802.11ax 2x2 + BT5.3, vPro®

WWAN
Non-WWAN

Ethernet
Integrated 100/1000M

Front Ports

- 1x USB-C® (USB 10Gbps / USB 3.2 Gen 2), data transfer only
- 2x USB-A (USB 10Gbps / USB 3.2 Gen 2), one supports Always On and 5V@2.1A charging
- 1x headphone / microphone combo jack (3.5mm)

Rear Ports

- 2x USB-A (USB 10Gbps / USB 3.2 Gen 2)
- 2x USB-A (USB 5Gbps / USB 3.2 Gen 1), one supports Smart Power On
- 1x HDMI® 2.1 TMDS
- 1x DisplayPort™ 1.4a (HBR2)
- 1x Ethernet (GbE RJ-45)

Optional Rear Ports (configured)
DP 1.4

SECURITY & PRIVACY

Security Chip
Discrete TPM 2.0, TCG certified, FIPS 140-2 certified

Fingerprint Reader
No fingerprint reader

Physical Locks
Kensington® Security Slot™, 3 x 7 mm

Kensington® Cable Lock
None

Chassis Intrusion Switch
Chassis Intrusion Switch

MANAGEABILITY

System Management^[7]
Intel® vPro® Enterprise

SERVICE

Base Warranty
3-year, Onsite

Included Upgrade
None

CERTIFICATIONS

Green Certifications

- ENERGY STAR® 9.0
- RoHS compliant
- TCO Certified 10.0

Mil-Spec Test
MIL-STD-810H military test passed (Low Pressure [Altitude], High Temperature, Low Temperature, Temperature Shock, Humidity, Sand and Dust, Vibration, Shock, Solar Radiation, Contamination by Fluids, Salt Fog)

SOFTWARE

Operating System
Windows® 11 Pro, English

Bundled Software
None

ACCESSORIES

Bundled Accessories
None

MODEL

TopSeller	: Yes	Announce Date	: 2025-05-13
EAN / UPC / JAN	: 199271049556	End of Support	: 2031-12-13

Note:
^[1] AI PCs have a NPU capable of 10+ TOPs to run the Copilot.....

- Lenovo reserves the right to change specifications without notice.
- California Electronic Waste Recycling Fee In California, per state law, Lenovo charges an electronic waste recycling fee on this covered device at the time of sale of the product. For more information, go to: <https://www.calrecycle.ca.gov/Electronics/Consumer>

To see more note information, please access the [web page](#).

Premier Support - A direct 24x7x365 line to our most elite technicians.



Advanced technical support, 24x7x365, in more than 100 markets



Technical Account Managers for proactive relationship and escalation management



Comprehensive hardware & OEM software support



Priority on service delivery and repair parts



Single point of contact for simplified end-to-end case management



Lenovo Service Connect Portal for customized reporting and product support

Accidental Damage Protection - Protection of your PC from the unexpected.

Experience shows that a significant portion of devices may be damaged (and not covered under warranty) in the first three years. Lenovo's Accidental Damage Protection service covers accidents beyond the system warranty such as drops, spills, bumps and even electrical surges. Make sure your new device has maximum protection, avoid unplanned costs and get peace of mind.

Base Warranty - Included with the systems you purchase, default 1- or 3-year coverage window.

Warranty Extensions & Upgrades - Service and protection that's right for your circumstances.

- Pick Up & Return Courier
- Onsite Support
- Technician Installed Customer
- Replaceable Unit Service
- International Warranty Upgrade

Lenovo may not offer the products, services or features discussed in this document in all regions. Lenovo may withdraw an offering at any time. Information is subject to change without notice. Consult your local representative for information on offerings available in your area. Lenovo reserves the right to change specifications or other product information without notice. Lenovo is not responsible for photographic or typographical errors. Lenovo provides this publication "as is" without warranty of any kind, either express or implied, including the implied warranties of merchantability or fitness for a particular purpose.

Recommended Accessories



Lenovo USB-C to Ethernet Adapter

4X90S91831

The Lenovo USB-C to Ethernet Adapter is quick and easy way to connect your USB-C enabled notebook to Ethernet connections. It's ideal for imaging of systems or transferring large files quickly.



Lenovo Professional Wireless Combo Keyboard & Mouse (US English)

4X30H56796

This sleek and stylish full-size keyboard and mouse combo offers exceptional quality in a modern wireless solution. The slim 3-zone keyboard with number pad has responsive quiet keys and a premium typing experience. O...

Please click [here](#) to view the full list of accessories.



PSREF
Product Specifications
Reference