

PERFORMANCE

Processor

Intel® Core™ Ultra 5 235, 14C (6P + 8E) / 14T, Max Turbo up to 5.0GHz, 24MB

AI PC Category^[1]

AI PC

Graphics

Integrated Intel® Graphics

Chipset

Intel® Q870 Chipset

Memory

2x 8GB UDIMM DDR5-5600

Memory Slots

Four DDR5 UDIMM slots, dual-channel capable

Max Memory^[2]

Up to 128GB DDR5

Storage

512GB SSD M.2 2280 PCIe® 4.0x4 NVMe® Opal 2.0

Max Storage Support^{[3][4]}

Up to six drives, 2x 3.5" HDD + 1x 2.5" HDD + 3x M.2 SSD
 • 3.5" HDD up to 2TB
 • 2.5" HDD bay is only for customer self upgrade
 • M.2 SSD up to 2TB each

Optical

DVD±RW

Audio Chip

High Definition (HD) Audio, Realtek® ALC623-CG codec

Speakers

2Wx1

Power Supply

310W 92%

DESIGN

Keyboard

USB Traditional Keyboard, Black, English

Mouse

USB Calliope Mouse, Black

Optional Bay

2nd M.2 Bracket + 2nd 3.5" HDD Bracket

Expansion Slots

- One PCIe® 5.0 x16
- One PCIe® 4.0 x16 (x4 signal)
- Two PCIe® 3.0 x1
- Four M.2 slots (one for WLAN, three for SSD / discrete NPU)

Case Color

Black

Stand

No stand

Pen

Pen Not Supported

Form Factor

Tower (17L)

Dimensions (WxDxH)^[5]

170 x 298 x 376 mm (6.7 x 11.7 x 14.8 inches)

Weight^[6]

6.5 kg (14.3 lbs, maximum configuration)

CONNECTIVITY

WLAN + Bluetooth®

Intel® Wi-Fi® 6E AX211, 802.11ax 2x2 + BT5.3, vPro®

WWAN

Non-WWAN

Ethernet

Integrated 100/1000M

Front Ports

- 1x USB-C® (USB 20Gbps / USB 3.2 Gen 2x2), with 15W charging
- 2x USB-A (USB 5Gbps / USB 3.2 Gen 1)
- 2x USB-A (USB 10Gbps / USB 3.2 Gen 2)
- 1x headphone / microphone combo jack (3.5mm)

Rear Ports^[7]

- 2x USB-A (Hi-Speed USB / USB 2.0)
- 2x USB-A (USB 5Gbps / USB 3.2 Gen 1)
- 1x HDMI® 2.1 TMDS
- 2x DisplayPort™ 1.4a (HBR2, DSC)
- 1x Ethernet (RJ-45)
- 1x line-out (3.5mm)

Optional Rear Ports (configured)

1x DP 1.2 (Flex IO)

SECURITY & PRIVACY

Security Chip

Discrete TPM 2.0, TCG certified, FIPS 140-2 certified

Fingerprint Reader

No fingerprint reader

Physical Locks

- Kensington® Security Slot™, 3 x 7 mm
- Padlock Loop

MANAGEABILITY

System Management^[8]

Intel® vPro® Enterprise

SERVICE

Base Warranty

3-year, Onsite

CERTIFICATIONS

Green Certifications

- ENERGY STAR® 9.0
- EPEAT™ Gold Registered
- TCO Certified 10.0
- ErP Lot 3
- GREENGUARD®
- RoHS compliant

Mil-Spec Test

MIL-STD-810H military test passed (Low Pressure [Altitude], High Temperature, Low Temperature, Temperature Shock, Humidity, Sand and Dust, Vibration, Shock, Solar Radiation, Contamination by Fluids, Salt Fog)

SOFTWARE

Operating System

Windows® 11 Pro, English

MODEL

TopSeller	: Yes	Announce Date	: 2025-05-15
EAN / UPC / JAN	: 198157851641	End of Support	: 2031-11-29



intel

Product image is a sample, it may not match the real color of this model

Note:

[1] AI PCs have a NPU capable of 10+ TOPs to run the Copilot assistant by pressing the optional Microsoft Copilot key or using Win + C.

[2] The max memory is based on the test results with current Lenovo memory offerings.

[3] The max capacity of each disk type is based on the test results with current Lenovo storage offerings.

[4] 2.5" HDD bay and 2nd 3.5" bay are optional parts, and.....

• Lenovo reserves the right to change specifications without notice.

• California Electronic Waste Recycling Fee In California, per state law, Lenovo charges an electronic waste recycling fee on this covered device at the time of sale of the product. For more information, go to: <https://www.calrecycle.ca.gov/Electronics/Consumer>

To see more note information, please access the [web page](#).

Premier Support - A direct 24x7x365 line to our most elite technicians.



Advanced technical support, 24x7x365, in more than 100 markets



Technical Account Managers for proactive relationship and escalation management



Comprehensive hardware & OEM software support



Priority on service delivery and repair parts



Single point of contact for simplified end-to-end case management



Lenovo Service Connect Portal for customized reporting and product support

Accidental Damage Protection - Protection of your PC from the unexpected.

Experience shows that a significant portion of devices may be damaged (and not covered under warranty) in the first three years. Lenovo's Accidental Damage Protection service covers accidents beyond the system warranty such as drops, spills, bumps and even electrical surges. Make sure your new device has maximum protection, avoid unplanned costs and get peace of mind.

Base Warranty - Included with the systems you purchase, default 1- or 3-year coverage window.

Warranty Extensions & Upgrades - Service and protection that's right for your circumstances.

- Pick Up & Return Courier
- Onsite Support
- Technician Installed Customer
- Replaceable Unit Service
- International Warranty Upgrade

Lenovo may not offer the products, services or features discussed in this document in all regions. Lenovo may withdraw an offering at any time. Information is subject to change without notice. Consult your local representative for information on offerings available in your area. Lenovo reserves the right to change specifications or other product information without notice. Lenovo is not responsible for photographic or typographical errors. Lenovo provides this publication "as is" without warranty of any kind, either express or implied, including the implied warranties of merchantability or fitness for a particular purpose.

Recommended Accessories



Lenovo USB-C to Ethernet Adapter

4X90S91831

The Lenovo USB-C to Ethernet Adapter is quick and easy way to connect your USB-C enabled notebook to Ethernet connections. It's ideal for imaging of systems or transferring large files quickly.

Recommended Services

BEST	4Y Premier Support Plus upgrade from 3Y Onsite (5WS1L39206)
BETTER	3Y Premier Support Plus upgrade from 3Y Onsite (5WS1L39278)
GOOD	3Y Premier Support Upgrade from 3Y Onsite (5WS0V07841)

Please click [here](#) to view the full list of accessories.



PSREF
Product Specifications
Reference