



CU34G4

Dominate with the CU34G4 34" WQHD Curved Monitor, featuring a 3440x1440 resolution, HDR10, and a 180Hz refresh rate.

Elevate your gaming with the CU34G4 34" WQHD curved monitor. Enjoy smooth gameplay with a 180Hz refresh rate and 1ms GtG response time. The 1500R curved Fast VA panel provides immersive visuals, while HDR10 enhances color and contrast. Equipped with AdaptiveSync, low input lag, and MBR MPRT 0.5ms, this monitor is built for speed and precision. The HAS stand and G-Menu software allow for customizable settings and ergonomic comfort.

GENERAL	
Model Name	CU34G4
Channel	Gaming
Product line	AOC Gaming
Design family	G4

SCREEN	
Screen size (inch)	34
Screen size (cm)	86.36
Flat / Curved	Curved
Curvature Radius	1500R
Panel treatment	Antiglare (AG)
Panel resolution	3440x1440
Resolution name	UWQHD
Aspect ratio	21:9
Panel type	Fast VA
Backlight type	WLED
Max Refresh rate	180 Hz
Response time GtG	1 ms
Response time MPRT	0.5 ms
Static contrast ratio	2500:1
Viewing angle (CR10)	178/178
Display colours	16.7 Million
Brightness in nits	300 cd/m2
Pixels per Inch	109.6

EXTERIOR

Bezel type (front)	3-sided frameless
Bezel Colour (front)	Black
Bezel finishing (front)	Matt
Cabinet colour (backside)	Black, Red
Cabinet finishing (backside)	Matt

ERGONOMICS

Vesa wallmount	100x100
Tilt	$3.5^{\circ} \pm 1.5^{\circ} \sim 21.5^{\circ} \pm 1.5^{\circ}$
Swivel	$20^{\circ} \pm 2^{\circ} \sim 20^{\circ} \pm 2^{\circ}$
Height adjust (mm)	130mm

CONNECTIVITY AND MULTIMEDIA

HDMI	HDMI 2.0 x 2
DisplayPort	DisplayPort 1.4 x 1

MULTIMEDIA

Audio Output	Headphone out (3.5mm)
--------------	-----------------------

FEATURES

Sync technology (VRR)	Adaptive Sync
AMD FreeSync™	AMD FreeSync Premium
Blue Light Technology	Low Blue Light
Multiview (PbP, PiP)	PiP+PbP
Flicker-Free	Flicker Free
Kensington Lock	✓
Colour space (DCI-P3) CIE 1976 %	92.3

GAMING FEATURES

Gaming style	Shooters, MMORPG, Action, RTS, Beat'm up, Racing
Gaming convenience	G-menu
Low input Lag	✓
Game Color	✓
Shadow Control	✓
Motion Blur Reduction	✓
Crosshair / Dial Point	✓
Frame Counter	✓
Good for Console Gaming	✓
PS5 Compatibility	2560x1440@120Hz
Xbox X Compatibility	2560x1440@120Hz
Xbox S Compatibility	2560x1440@120Hz

POWER / ENVIRONMENTAL

Power supply	Internal
Power consumption standby in watts	0.3
Power consumption off in watts	0.3

PRODUCT DIMENSIONS (METRIC)

Product dimensions incl. base (WxHxD) mm	808.1 x (435.7~534.7) x 269.4
Product dimensions excl. base (WxHxD) mm	808.1 x 368.4 x 109.0
Packaging dimensions (WxHxD) mm	1070 x 553 x 188
Gross weight incl. package (in kg)	11.35
Product with stand (kg)	8.08
Product without stand (kg)	5.82

WHAT'S IN THE BOX

HDMI cable	1x
Displayport cable	1x