



Reliable power solutions for the public sector.



APC NetShelter rPDU, Smart-UPS and NetBotz solutions for BAA & TAA applications

apc.com/TAA




Table of contents

Overview of Portfolio

1

Empowering growth with
Domestic Preference compliance

BAA & TAA Compliant Products

2

APC Smart-UPS™ compliant
solutions portfolio details

TAA Compliant Products

3

APC NetShelter™, Smart-UPS and NetBotz™
compliant solutions portfolio details


Empowering growth with Domestic Preference compliance

Portfolio for BAA and TAA compliant solutions.

For over 180 years globally and 135 in America, Schneider Electric has led industrial technology in electrification, digitalization, and automation, transforming energy use and making an impact for efficiency. We're committed to meeting federal standards, including domestic preference laws, to strengthen local economies, enhance energy resiliency, bolster supply chains, and drive innovation.

We are committed to meeting the standards set by federal infrastructure funding and domestic preference laws and regulations in the U.S.

Our compliance and commitment to Domestic Preference reflects our dedication to strengthening local and state economies by offering a robust portfolio for Buy America projects, promoting efficiency and prioritizing speed, enhancing supply chain resilience and driving continuous innovation.



Buy American Act (BAA) Compliant Portfolio

The Buy American Act (BAA) is a law in the United States that encourages the federal government to procure U.S.-made products. The act aims to support domestic manufacturing, American workers and businesses, and ensure that taxpayer money benefits the U.S. economy.

Reliability at the edge matters, especially to agencies charged with administering critical programs and services. APC by Schneider Electric offers products to enable access to the resources needed to power state programs where operational continuity is critical and our BAA offers are also compliant with TAA.

Our experts can help you find compliant solutions and provide a free quote for your new or modernization project.

BAA & TAA Portfolio ›

BAA Compliant Portfolio*



Smart-UPS Double Conversion Online Essential Series
Ideal for data networks, voice networks, industrial applications, and medical devices/lab. Helps support applications with demanding power conditions and aggressive runtimes.

[View models ›](#)

*Both BAA and TAA Compliant

Smart-UPS On-Line

Mount	SKU	Rating (VA/Watts)	U-Space	Voltage	Battery	Runtime (Half/Full)	Inlet	Outlets
Rackmount or Tower Convertible	SRT5KRMXLT-A	5400/4800	3U	208	VRLA	10.7 / 3.5 min.	NEMA L6-30P	(2) NEMA L6-20R, (2) NEMA L6-30R
	SRT5KRMXLT-5KTF-A	5000/4800	5U	208	VRLA	10.7 / 3.5 min.	NEMA L6-30P	(12) NEMA 5-20R, (2) NEMA L6-20R, (2) NEMA L6-30R
	SRT6KRMXLT-A	6000/6000	4U	208	VRLA	8.3 / 2.3 min.	Hard Wire 3-wire (2PH + G) 1	(2) NEMA L6-20R, (3) NEMA L6-30R
	SRT8KRMXLT-A	8000/8000	6U	208	VRLA	14.4 / 5.2 min.	Hard Wire 3-wire (2PH + G) 1	(4) NEMA L6-20R, (2) NEMA L6-30R
	SRT10KRMXLT-A	10000/10000	6U	208	VRLA	11.4 / 3.7 min.	Hard Wire 3-wire (2PH + G) 1	(4) NEMA L6-20R, (2) NEMA L6-30R

Trade Agreements Act (TAA) Compliant Portfolio

Trade Agreements Act (TAA) compliance in the United States refers to the requirement that government contractors must ensure that the products they sell to federal agencies are made or substantially transformed in designated countries that have trade agreements with the US. This is intended to protect domestic industry and promote fair trade and friendly relationships with other countries.

APC by Schneider Electric provides state and federal institutions with reliable power and distribution solutions that help support critical applications.

Our experts can help you find compliant solutions and provide a free quote for your new or modernization project.

TAA Portfolio ›

TAA Compliant Portfolio



NetShelter Rack PDU Advanced
Best-in-class intelligent rack power distribution with up to 50% more power.

[View models ›](#)



NetShelter Rack PDU
Our standard PDUs with industry-leading reliability, manageability, and security.

[Metered ›](#)

[Switched ›](#)

[Metered-by-outlet ›](#)

[Switched Metered ›](#)



Smart-UPS Ultra
Ultra-high power density, on-line power protection with lithium-ion batteries and scalable runtime options.

[View models ›](#)



Smart-UPS
Intelligent and efficient network power protection from entry level to scalable runtime.

[On-line ›](#)

[Line Interactive ›](#)

[Special Applications ›](#)



NetBotz
Security and environmental appliances and accessories are designed to help protect IT infrastructure.

[View models ›](#)

NetShelter Rack PDU Advanced

Type	SKU	Mounting	U-Space	Input Voltage	Input circuit	Nominal power	Cord length	Breakers	Input plug type*	Output receptacles			
Switched	APDU11452SWUS	Vertical	0U	208	60 A, 3ph	17.3 kW	3.0 m	6	IEC-309 60A 3P+PE 	(21) C13/15 	(21) 4-in-1 		
	APDU11350SWUS	Vertical	0U	400–415	30 A, 3ph	17.3 kW	3.0 m	6	IEC-309 30A 3P+N+PE 	(24) C13/15 	(24) 4-in-1 		
Metered	APDU11451MEUS	Vertical	0U	208	50 A, 3ph	14.4 kW	3.0 m	6	CS8365C 	(21) C13/15 	(21) 4-in-1 		
Switched Metered	APDU11151SMUS	Vertical	0U	208	30 A, 1ph	5.0 kW	3.0 m	2	NEMA L6-30P 	(20) C13/15 	(20) 4-in-1 		
	APDU11351SMUS	Vertical	0U	208	30 A, 3ph	8.6 kW	3.0 m	3	NEMA L21-30P 	(24) C13/15 	(24) 4-in-1 		
	APDU11450SMUS	Vertical	0U	400–415	60 A, 3ph	34.6 kW	3.0 m	12	IEC-309 60 A 3P+N+PE 	(21) C13/15 	(21) 4-in-1 		

*IEC Input Plug options listed are IP44 plug types

NetShelter Metered Rack PDU

Input Voltage	SKU	Mounting	U-Space	Input circuit	Nominal power	Cord length	Input plug type*	Output receptacles						
100V – 120V	AP8830US	Vertical	0U	20 A	1.9 kW	3.0 m	NEMA L5-20P		(24) 5-20					
	AP8832US	Vertical	0U	30 A	2.9 kW	3.0 m	NEMA L5-30P		(24) 5-20					
200V – 208V	AP8841US	Vertical	0U	30 A	5.0 kW	3.0 m	NEMA L6-30P		(36) C13		(6) C19			
208 V 3ph	AP8861US	Vertical	0U	20 A	5.7 kW	1.8 m	NEMA L21-20P		(36) C13		(6) C19		(2) 5-20	
	AP8865US	Vertical	0U	30 A	8.6 kW	1.8 m	NEMA L21-30P		(36) C13		(6) C19		(2) 5-20	
	AP8868US	Vertical	0U	50 A	10.0 kW	1.8 m	CS8365C		(36) C13		(6) C19			
	AP8866US	Vertical	0U	60 A	17.3 kW	1.8 m	IEC-309 60 A 3P+PE		(12) C19		(4) C13			
	AP8867US	Vertical	0U	60 A	17.3 kW	1.8 m	IEC-309 60 A 3P+PE		(30) C13					

*IEC Input Plug options listed are IP44 plug types

NetShelter Metered-by-Outlet Rack PDUs

Input Voltage	SKU	Mounting	U-Space	Input circuit	Nominal power	Cord length	Input plug type	Output receptacles				
208V 3Ph	AP8641US	Vertical	0U	20 A, 3Ph	5.7 kW	1.8 m	NEMA L21-20P		(21) C13		(3) C19	


NetShelter Switched Rack PDUs



Input Voltage	SKU	Mounting	U-Space	Input circuit	Nominal power	Cord length	Input plug type*	Output receptacles			
100V – 120V	AP8932US	Vertical	0U	30 A	2.9 kW	3.0 m	NEMA L5-30P		(24) 5-20		
200V – 240V	APDU9941US	Vertical	0U	30 A	5.0 kW	3.0 m	NEMA L6-30P		(21) C13/15		(3) C19/21
208V 3Ph	AP8962US	Vertical	0U	20 A	6.0 kW	3.0 m	NEMA L21-20P		(24) 5-20		
	APDU9965US	Vertical	0U	30 A	8.6 kW	1.8 m	NEMA L21-30P		(21) C13/15		(3) C19/21
	APDU9967US	Vertical	0U	60 A	17.3 kW	2.0 m	IEC-309 60 A 3P+PE		(42) C13/15		(6) C19/21

*IEC Input Plug options listed are IP44 plug types **Remote switching control available through EcoStruxure™ IT Expert in the 8000, and 9000 Series PDUs.

NetShelter Metered-by-Outlet with Switching Rack PDUs



Input Voltage	SKU	Mounting	U-space	Input circuit	Nominal power	Cord length	Input plug type	Output receptacles			
100V – 120V	AP8632US	Vertical	0U	30 A	2.9 kW	3.0 m	NEMA L5-30P		(21) C13		(3) C19

**Remote switching control available through EcoStruxure IT Expert in the 8000, and 9000 Series PDUs.



Smart-UPS Ultra

Mount	SKU	Rating (VA/Watts)	Voltage	Battery	Runtime (Half/Full)	Inlet	Outlets	XBP**	*
Rackmount or Tower Convertible	SRTL2K2RM1UCUS	2200/2200	120V	Lithium-Ion	12.7 / 6.1 min.	NEMA 5-20P	(5) NEMA 5-20R; (1) NEMA L5-20R	SRTL50RMBP1U-LI	*
	SRTL2K2RM1UNCUS	2200/2200	120V	Lithium-Ion	12.7 / 6.1 min.	NEMA 5-20P	(5) NEMA 5-20R; (1) NEMA L5-20R	SRTL50RMBP1U-LI	*
	SRTL3KRM1UCUS	2880/2880	120V	Lithium-Ion	9.6 / 4.4 min.	NEMA L5-30P	(5) NEMA 5-20R; (1) NEMA L5-30R	SRTL50RMBP1U-LI	*
	SRTL3KRM1UNCUS	2880/2880	120V	Lithium-Ion	9.6 / 4.4 min.	NEMA L5-30P	(5) NEMA 5-20R; (1) NEMA L5-30R	SRTL50RMBP1U-LI	*
	SRTL5KRM2UTUS	4900/4900	208/	Lithium-Ion	12 / 5.6 min.	NEMA L6-30P	(2) NEMA L6-20R; (2) NEMA L6-30R	SRTL180RM2UBP	*

*Model is available in 2027 **External Battery Pack (XBP) listed for reference only and are not TAA compliant.

Smart-UPS On-Line

Mount	SKU	Rating (VA/Watts)	Voltage	Battery	Runtime (Half/Full)	Inlet	Outlets	XBP**
Rackmount or Tower Convertible	SRT3000XLAUS	3000/2700	120V	VRLA	10.3 / 3.2 min.	NEMA L5-30P	(8) NEMA 5-20R; (1) NEMA L5-30R	SRT72RMBP
	SRT5KXLTUS	5000/4800	208V	VRLA	10.7 / 3.5 min.	NEMA L6-30P	(2) NEMA L6-30R; (2) NEMA L6-20R	SRT192BP
	SRT6KXLTUS	6000/6000	208V	VRLA	8.3 / 2.3 min.	Hard Wire: 3-wire (2PH+G)	(2) NEMA L6-20R; (3) NEMA L6-30R; (1) Hard Wire 3-wire (2PH + G)	SRT192BP
	SRT8KXLTUS	8000/8000	208V	VRLA	14.4 / 5.2 min.	Hard Wire: 3-wire (2PH+G)	(4) NEMA L6-20R; (2) NEMA L6-30R; (1) Hard Wire 3-wire (2PH + G)	SRT192BP2
	SRT10KXLTUS	10000/10000	208V	VRLA	11.4 / 3.7 min.	Hard Wire: 3-wire (2PH+G)	(2) NEMA L6-30R; (4) NEMA L6-20R; (1) Hard Wire 3-wire (2PH + G)	SRT192BP2
Rackmount	SRT1000RMXLA-NCUS	1000/900	120V	VRLA	25.4 / 10.5 min.	NEMA 5-15P	(6) NEMA 5-15R	SRT48RMBP
	SRT1500RMXLA-NCUS	1500/1350	120V	VRLA	13.2 / 4.6 min.	NEMA 5-15P	(6) NEMA 5-15R	SRT48RMBP
	SRT1500RMXLAUS	1500/1350	120V	VRLA	13.2 / 4.6 min.	NEMA 5-15P	(6) NEMA 5-15R	SRT48RMBP
	SRT2200RMXLAUS	2200/1800	120V	VRLA	10.3 / 3.3 min.	NEMA 5-20P	(1) NEMA L5-20R; (6) NEMA 5-20R	SRT72RMBP
	SRT2200RMXLA-NCUS	2200/1800	120V	VRLA	9.6 / 3.3 min.	NEMA 5-20P	(6) 5-20R; (1) L5-20R NEMA	SRT72RMBP
	SRT3000RMXLA-NCUS	3000/2700	120V	VRLA	10.3 / 3.2 min.	NEMA L5-30P	(8) 5-20R; (1) L5-30R NEMA	SRT96RMBP
	SRT3000RMXLAUS	3000/2700	120V	VRLA	10.3 / 3.2 min.	NEMA L5-30P	(8) 5-20R; (1) L5-30R NEMA	SRT96RMBP
	SRT3000RMXLT-NCUS	3000/2700	208V	VRLA	11.4 / 3.8 min.	NEMA L6-20P	(2) L6-20R; (1) NEMA L6-30R	SRT96RMBP
	SRT3000RMXLTUS	3000/2700	208V	VRLA	11.4 / 3.8 min.	NEMA L6-20P	(2) L6-20R; (1) NEMA L6-30R	SRT96RMBP

**External Battery Pack (XBP) listed for reference only and are not TAA compliant.

Smart-UPS On-Line (continued)

Mount	SKU	Rating (VA/Watts)	Voltage	Battery	Runtime (Half/Full)	Inlet	Outlets	XBP**
Rackmount	SRT5KRMXLTUS	5000/4800	208V	VRLA	10.7 / 3.5 min.	NEMA L6-30P	(2) NEMA L6-20R; (2) NEMA L6-30R	SRT192RMBP
	SRT10KRMXLTUS	1000/10000	208V	VRLA	11.4 / 3.7 min.	Hard Wire: 3-wire (2PH+G)	(4) L6-20R; (2) NEMA L6-30R	SRT192RMBP3

**External Battery Pack (XBP) listed for reference only and are not TAA compliant.

Smart-UPS Line-Interactive Lithium-Ion Battery

Mount	SKU	Rating (VA/Watts)	Voltage	Battery	Runtime (Half/Full)	Inlet	Outlets
Rackmount	SCL500RM1UCUS	500/400	120V	Lithium-Ion	7.7 / 3.4 min.	NEMA 5-15P	(4) NEMA 5-15R
Rackmount or Tower Convertible	SMTL750RM2UCUS	750/600	120V	Lithium-Ion	12.9 / 6.2 min.	NEMA 5-15P	(6) NEMA 5-15R
	SMTL1000RM2UCUS	1000/800	120V	Lithium-Ion	16.1 / 7.8 min.	NEMA 5-15P	(6) NEMA 5-15R
	SMTL1500RM3UCUS	1440/1350	120V	Lithium-Ion	11.2 / 5.2 min.	NEMA 5-15P	(6) NEMA 5-15R
	SMTL2200RM2UCNCUS	1920/1920	120V	Lithium-Ion	16.1 / 7.7 min.	NEMA 5-20P	(2) NEMA 5-20R; (6) NEMA 5-15R
	SMTL2200RM2UCUS	1920/1920	120V	Lithium-Ion	16.1 / 7.7 min.	NEMA 5-20P	(2) NEMA 5-20R; (6) NEMA 5-15R
	SMTL3000RM2UCNCUS	2880/2700	120V	Lithium-Ion	11.5 / 5.3 min.	NEMA L5-30P	(2) NEMA 5-20R; (6) NEMA 5-15R
	SMTL3000RM2UCUS	2880/2700	120V	Lithium-Ion	11.5 / 5.3 min.	NEMA L5-30P	(2) NEMA 5-20R; (6) NEMA 5-15R

Smart-UPS Line-Interactive Lead Acid Battery

Mount	SKU	Rating (VA/Watts)	Voltage	Battery	Runtime (Half/Full)	Inlet	Outlets
Rackmount	SMT1500RM2UCNCUS	1440/1000	120V	VRLA	25.9 / 7.2 min.	NEMA 5-15P	(6) NEMA 5-15R
	SMT1500RM2UCUS	1440/1000	120V	VRLA	25.9 / 7.2 min.	NEMA 5-15P	(6) NEMA 5-15R
	SMT2200RM2UNCUS	1920/1920	120V	VRLA	15.9 / 5.4 min.	NEMA 5-20P	(6) NEMA 5-15R; (2) NEMA 5-20R
	SMT2200RM2UCUS	1920/1920	120V	VRLA	18.7 / 6.4 min.	NEMA 5-20P	(6) NEMA 5-15R; (2) NEMA 5-20R
	SMT3000RM2UCUS	2880/2700	120V	VRLA	10.8 / 2.8 min.	NEMA L5-30P	(6) NEMA 5-15R; (2) NEMA 5-20R
	SMT3000RM2UNCUS	2880/2700	120V	VRLA	11.7 / 3.4 min.	NEMA L5-30P	(6) NEMA 5-15R; (2) NEMA 5-20R
Tower	SMT750CUS	750/500	120V	VRLA	15.9 / 4.6 min.	NEMA 5-15P	(6) NEMA 5-15R
	SMT1000CUS	1000/700	120V	VRLA	19.1 / 5.8 min.	NEMA 5-15P	(8) NEMA 5-15R
	SMT1500CUS	1440/1000	120V	VRLA	23.1 / 6.5 min.	NEMA 5-15P	(8) NEMA 5-15R
	SMT2200CUS	1920/1920	120V	VRLA	28.3 / 10.1 min.	NEMA 5-20P	(8) NEMA 5-15R; (2) NEMA 5-20R
	SMT3000CUS	2880/2700	120V	VRLA	17.5 / 5.1 min.	NEMA L5-30P	(8) NEMA 5-15R; (2) NEMA 5-20R

Smart-UPS X Line-Interactive

Mount	SKU	Rating (VA/Watts)	Voltage	Battery	Runtime (Half/Full)	Inlet	Outlets	XBP**
Rackmount or Tower Convertible	SMX750CUS	750/600	120V	VRLA	37.8 / 14.2 min.	NEMA 5-15P	(8) NEMA 5-15R	SMX48RMBP2
	SMX1000CUS	1000/800	120V	VRLA	24.2 / 8.1 min.	NEMA 5-15P	(8) NEMA 5-15R	SMX48RMBP2
	SMX1500RM2UCNCUS	1440/1200	120V	VRLA	17.2 / 5.8 min.	NEMA 5-15P	(8) NEMA 5-15R	SMX48RMBP2
	SMX1500RM2UCUS	1440/1200	120V	VRLA	17.2 / 5.8 min.	NEMA 5-15P	(8) NEMA 5-15R	SMX48RMBP2
	SMX2000LVNCUS	1920/1800	120V	VRLA	27.6 / 10.9 min.	NEMA 5-20P	(3) NEMA 5-20R; (1) NEMA L5-20R; (6) NEMA 5-15R	SMX120BP
	SMX2000LVUS	1920/1800	120V	VRLA	27.6 / 10.9 min.	NEMA 5-20P	(3) NEMA 5-20R; (1) NEMA L5-20R; (6) NEMA 5-15R	SMX120BP
	SMX2KRMLVNCUS	1920/1800	120V	VRLA	27.6 / 10.9 min.	NEMA 5-20P	(3) NEMA 5-15R; (1) NEMA L5-20R; (3) NEMA 5-20R	SMX120RMBP2U
	SMX2000RMLV2U-US	1920/1800	120V	VRLA	27.6 / 10.9 min.	NEMA 5-20P	(3) 5-15R; (3) 5-20R; (1) L5-20R NEMA	SMX120RMBP2U
	SMX2200RMLVUS	2200/1980	120V	VRLA	25.3 / 9.8 min.	NEMA L5-30P	(6) NEMA 5-15R; (2) NEMA 5-20R	SMX120RMBP2U
	SMX3000LVUS	2880/2700	120V	VRLA	18.1 / 6.3 min.	NEMA L5-30P	(3) NEMA 5-20R; (1) NEMA L5-30R; (6) NEMA 5-15R	SMX120BP
	SMX3000LVNCUS	2880/2700	120V	VRLA	18.1 / 6.3 min.	NEMA L5-30P	(3) NEMA 5-20R; (1) NEMA L5-30R; (6) NEMA 5-15R	SMX120BP
	SMX3000RMLVUS	2880/2700	120V	VRLA	18.1 / 6.3 min.	NEMA L5-30P	(3) NEMA 5-20R; (1) NEMA L5-30R; (3) NEMA 5-15R	SMX120RMBP2U
	SMX3KRMLVNCUS	2880/2700	120V	VRLA	18.1 / 6.3 min.	NEMA L5-30P	(3) NEMA 5-20R; (1) NEMA L5-30R; (3) NEMA 5-15R	SMX120RMBP2U
	SMX3000RMHV2U-US	3000/2700	230V	VRLA	18.1 / 6.3 min.	IEC 320 C20	(8) C13; (1) C19 IEC	SMX120RMBP2U
	SMX3000HVTUS	3000/2700	208V	VRLA	18.1 / 6.3 min.	NEMA L6-20P	(2) NEMA L6-20R; (4) IEC 320 C13; (2) IEC 320 C19; (3) IEC Jumpers	SMX120BP

**External Battery Packs (XBP) listed for reference only and are not TAA compliant.

Smart-UPS Line Interactive - Marine Application

Mount	SKU	Rating (VA/Watts)	Voltage	Battery	Applications	Inlet	Outlets	XBP**
Tower	SMT750X93	750/500	120V	VRLA	Shipboard	NEMA 5-15P	(6) NEMA 5-15R	-
	SMT1500X93	1440/1000	120V	VRLA	Shipboard	NEMA 5-15P	(8) NEMA 5-15R	-
Rackmount	SMT1500RMX93	1440/1000	120V	VRLA	Shipboard	NEMA 5-15P	(6) NEMA 5-15R	-
	SMX3000RMX93	2880/2700	120V	VRLA	Shipboard	NEMA 5-15P	(3) NEMA 5-15R	SMX120RMBP2U

Smart-UPS Line Interactive - Multi-standard Application

Mount	SKU	Rating (VA/Watts)	Voltage	Battery	Application	Inlet	Outlets	XBP**
Tower	SMT700X167	700/450	120V	VRLA	Multi-region	NEMA 5-15P	(8) NEMA 5-15R	-
Rackmount	SMT2200R2X167	2200/1980	120V	VRLA	Multi-region	NEMA 5-15P Schuko CEE 7 / EU1-16P BS1363A British CEI 23-16 Italian	(10) NEMA 5-15R	-


**External Battery Pack (XBP) listed for reference only and are not TAA compliant.

NetBotz Appliances

Mount	SKU	Rack Units	Number of Universal Sensor Ports	Number of Sensor Pods Supported	Camera Frame Rate	Communication
Wall	NBWL0755TAA	0	4	2	Up to 30fps	A-Link DHCP HTTPS IPv4/IPv6 SNMP v1 SNMP v3 SSH v2 TCP/IP
Rackmount	NBRK0750TAA	1	6	12	Up to 30fps	A-Link DHCP HTTPS IPv4/IPv6 SNMP v1 SNMP v3 SSH v2 TCP/IP
	NBRK0250TAA	1	6	12	N/A	A-Link HTTPS HTTP IPv4/IPv6 SNMP SNMP v3 TCP/IP Modbus

NetBotz Accessories

SKU	Description
NBES0301	Spot Fluid Sensor
NBES0302	Door Switch Sensor 3rd Party Racks
NBES0303	Door Switch Sensor APC Racks - Pair
NBES0303S	Door Switch Sensor APC Racks - Single
NBES0304	Dry Contact Cable
NBES0305	0-5V Cable
NBES0306	Vibration Sensor
NBES0307	Smoke Sensor
NBES0308	Leak Rope Sensor
NBES0309	Leak Rope Extension
AP9324	Alarm Beacon
NBHN0125	Rack Access 125kHz Handle Pair
NBHN0125S	Rack Access 125kHz Handle Single
NBHN1356	Rack Access 13.56kHz Handle Pair
NBHN1356S	Rack Access 13.56kHz Handle Single
NBPD0165	Sensor Expansion Pod
NBPD0175TAA	Rack Access Expansion Pod
NBPD0150TAA	Camera Pod 165



To learn more about Federal Infrastructure
Funding & Domestic Preference:

Visit our site >



Schneider Electric
One Boston Place, Suite 2700
Boston, Massachusetts, 2108, USA
Phone: (617) 904-9422

