



HP Series 5 Pro 27 inch FHD Monitor - 527pf (B28F5UT)

Overview



Reimagine how work looks and feels

Stay focused and in your flow. The HP Series 5 Pro 27" FHD Monitor keeps you working productively and comfortably. See your work come to life seamlessly and lightning-fast, with clear details and consistent colors. All built into a sleek, modern design.

Work smarter, smoother, and more brilliantly

Accelerate your work on this 27" FHD monitor. Experience every detail and lightning-fast, smoother scrolling with 120Hz refresh rate^[1]. See your work with more bright, vibrant, consistent colors with 100% sRGB^[1] and HP Progressive White Balance^[2].

Designed to inspire

Change the way you see your desk. See more of your display with the 3-sided borderless with micro-edge bezel design. To get even more done, pair this display with another HP Series 5 Pro 27" FHD monitor^[3] and a dock^[4] for the perfect dual display setup ^[5].

Designed and certified for all-day comfort

Feel your best all day. Find the optimal position with 4-way adjustability optimized by the step-by-step Ergonomic Setup Guide^[6]. Keep your eyes comfortable with TUV Rheinland Eye Comfort 3.0 and HP Eye Ease.

Materials that make an impact

This energy-efficient monitor is thoughtfully designed with at least 90% recycled plastic content in the monitor's enclosure, 20% recycled glass in the monitor panel, and 90% recycled aluminum in the stand^[7]. Plus, 100% of the paper-based packaging is sustainably sourced or recycled^[8].

Features

FHD Resolution

Focus on the finer details and enjoy sharp visuals and crystal clear images with the 1920 x 1080 FHD resolution on this 27" diagonal monitor.^[1]

IPS Technology

No matter where you are or sit, IPS technology ensures image accuracy and consistency across wide 178-degrees horizontal and vertical viewing angles.^[1]

120Hz Refresh Rate

With a 120Hz refresh rate this monitor is capable of crisp, clear details, while smoothly moving from frame to frame with a lightning-fast response.^[1]

More Contrast

See the nuanced differences of color, shadow, and highlights thanks to the enhanced 1500:1 contrast ratio.

High Brightness

350 nits of brightness lets you see clearly. Enhance your visual performance for work or simply enjoying entertainment.^[1]

100% sRGB Color Gamut

Enjoy highly accurate colors on screen with 100% sRGB. This HP monitor provides ideal color reproduction with minimal effort.^[1]

[1] All performance specifications represent the typical specifications provided by HP's component manufacturers; actual performance may vary, either higher or lower.

[2] HP's Progressive White Balance feature is designed to calibrate 100% full white on HP Series 5 Pro monitors. This adjustment is intended to align the white point more closely among various HP Series 5 Pro monitors. However, due to the nature of monitors, perceptible differences in the white color may still occur when the monitors are viewed from varying angles.

[3] HP Series 5 Pro 27" FHD - 527pf Monitor sold separately.

[4] Dock sold separately. Both HP Series 5 Pro 27" FHD Monitor - 527pf monitors need to be connected to the dock for a dual display setup.

[5] Configuration may vary based on port availability of host PC. Two video inputs, HDMI or DisplayPort, needed for a dual display setup.

[6] Ergonomic Setup Guide is available through HP Display Center. Host PC requires Windows 10 or higher. HP Display Center is available on the Microsoft store.

[7] Recycled plastic is expressed as a percentage of the total weight plastic. Post-consumer recycled is based on the definition set in the EPEAT® standard for computers, IEEE 1680.1-2018 standard. Percentage of recycled glass in the monitor panel varies by product. Recycled glass is expressed as a percentage of the total weight of the glass. Recycled metal is expressed as a percentage of the total weight of the metal according to ISO 14021 definitions for metal parts over 25 grams.

[8] HP paper and fiber based packaging for PCs, displays, home and office print, and supplies is reported by suppliers as recycled or certified, with a minimum of 97% by volume verified by HP. Packaging is the box that comes with the product and all paper-based materials inside the box. Packaging for personal systems accessories and spare parts is not included.

Specifications

Color	Black
Display size (diagonal)	27"
Panel technology	IPS; LED
Display size (diagonal)	68.6 cm (27")
Aspect ratio	16:9 ^[1]
Native resolution	FHD (1920 x 1080) ^[1,2]
Resolutions supported	640 x 480 @ 60 Hz; 640 x 480 @ 75 Hz; 720 x 400 @ 70 Hz; 800 x 600 @ 60 Hz; 800 x 600 @ 75 Hz; 1024 x 768 @ 60 Hz; 1280 x 720 @ 60 Hz; 1280 x 1024 @ 60 Hz; 1440 x 900 @ 60 Hz; 1600 x 900 @ 60 Hz; 1680 x 1050 @ 60 Hz; 1920 x 1080 @ 50 Hz; 1920 x 1080 @ 60 Hz; 1920 x 1080 @ 100 Hz; 1920 x 1080 @ 120 Hz; 1280 x 1024 @ 75 Hz; 720 x 480 @ 60 Hz; 720 x 576 @ 50 Hz; 1024 x 768 @ 75 Hz; 1280 x 720 @ 50 Hz; 1280 x 720 @ 100 Hz; 1280 x 800 @ 60 Hz; 1920 x 1080 @ 75 Hz
Pixel pitch	0.3114 x 0.3114 mm ^[1]
Brightness	350 nits ^[1]
Contrast ratio	1500:1 ^[1]
Response time (typical)	5ms GtG (with overdrive) ^[1]
Dimensions (W x D x H)	61.17 x 7.41 x 35.57 cm (without stand)
Dimensions (W x D x H)	24.08 x 2.92 x 14 in (without stand)
Dimensions With Stand (W x D x H)	61.17 x 22.9 x 54.31 cm
Weight	6.1 kg (with stand); 4.4 kg (without stand)
Weight	13.45 lb (with stand); 9.7 lb (without stand)
Display features	Height Adjust/Tilt/Swivel/Pivot ^[1]
Onscreen controls	Brightness+; Color; Image; Input; Power; Menu; Management; Information; Exit
Display colors	Up to 16.7 million colors supported ^[3]
Display scan frequency (horizontal)	30-138 kHz ^[1]
Display scan frequency (vertical)	50-120 Hz ^[1]
Power	100 - 240 VAC 50/60 Hz
Power consumption	60 W (maximum), 22 W (typical) ^[16]
Operating temperature range	5 to 35°C
Operating humidity range	20 to 80% RH (non-condensing)
Sustainable impact specifications	Low halogen; 90% post-consumer recycled plastic; Contains ocean-bound plastic; Contains 20% recycled glass in the monitor panel; Outside box and corrugated cushions are 100% sustainably sourced or recyclable; At least 35% recycled metal including 90% recycled aluminum and 10% recycled steel in the stand; Molded paper pulp cushion inside box is 100% sustainably sourced or recyclable
Certifications and compliances	Australian-New Zealand MEPS; BIS; BSMI; CB; CCC; CE; CSA; EAC; FCC; ISO 9241-307; KC; KCC; NOM; PSB; RCM; TUV-S; VCCI; Vietnam MEPS; WEEE; ISC; Low blue light; UAE; TUV-GS; Ukraine certificates; NRCS; PSE; EMF; UL; Flicker free; TUV Eye Comfort 3.0 4-Star; NFPA99; ISED
Physical security	Security lock-ready ^[5]
Management Software	HP Display Center; HP Client Management Script Library ^[6,7]
UPC number	(A2K) 198828548627; (A2N) 198828548634; (AB0) 198828548641; (AB1) 198828548658; (AB2) 198828548665; (AB4) 198828548672; (ABA) 198828548689; (ABB) 198828548696; (ABG) 198828548702; (ABJ) 4582712557745; (ABT) 198828548719; (ABU) 198828548726; (ABV) 198828548733; (ABY) 198828548740; (AC4) 198828548757; (AC8) 198828548764; (ACJ) 198828548771; (ACQ) 198828548788; (AH3) 198828548795; (AKH) 198828548801; (AKL) 198828548818; (AR6) 198828548825; (UUU) 198828548832; (UUZ) 198828548849
Manufacturer Warranty	HP three-year limited warranty
What's in the box	Monitor; DisplayPort™ 1.2 cable; HDMI cable; Warranty card; USB Type-A to B cable; AC power cable; Quick Setup Poster ^[4]

Additional specifications

Backlight lamp life minimum (to half brightness)	30,000 hours
Backlight type	Edge-lit
Base area footprint (imperial)	10.08 x 8.15 in
Base area footprint (metric)	25.6 x 20.7 cm
Bezel	3-sided micro-edge
Color gamut	100% sRGB ^[1]
Curvature	Flat
Datasheet photo 1	https://hp.widen.net/content/b5saojukok/png/Rhone_527pf_Jetblack_Catalog_VisID_GrayBG_Front_3229193.png?w=800&h=800&position=c&color=ffff00&quality=80&u=dlkxlp
Datasheet photo 2	https://hp.widen.net/content/0542nolxn4/png/Rhone_527pf_Jetblack_Catalog_WhiteBG_FrontRight_3229197.png?w=800&h=800&position=c&color=ffff00&quality=80&u=dlkxlp
Datasheet photo 3	https://hp.widen.net/content/vdj1bubjix/png/Rhone_527pf_Jetblack_Catalog_VisID_GrayBG_Rear_3229803.png?w=800&h=800&position=c&color=ffff00&quality=80&u=dlkxlp
Datasheet photo 4	https://hp.widen.net/content/3rqysmomg9/png/Rhone_527pf_Jetblack_Catalog_VisID_GrayBG_LepftPropfile_3229241.png?w=800&h=800&position=c&color=ffff00&quality=80&u=dlkxlp
Detachable stand	Yes
Display area (imperial)	23.54 x 13.24 in
Display area (metric)	59.79 x 33.63 cm
Display contrast ratio (dynamic)	10,000,000:1
DisplayPort™	1 DisplayPort™ 1.2
Ecolabels	CECP; SEPA; Taiwan Green Mark; Japan PC Green Label; TCO Certified; TCO Certified Edge; EPEAT® registered with Climate+; CEL Grade 1; Ukraine EE; Korea MEPS; California CEC
Energy efficiency class	C
Energy efficiency class logo	https://h10003.www1.hp.com/digmedialib/prodimg/lowres/c07055644.png
Energy star certified	ENERGY STAR® certified
Flicker-free	Yes
HDCP	Yes, DisplayPort™ and HDMI
HDMI	1 HDMI 1.4
Hardness	3H ^[1]
Haze	25%
Height adjustment range	150 mm
Horizontal viewing angle	178°
Low blue light	Yes, HP Eye Ease (TÜV Low Blue Light Hardware Solution certified) ^[1]

Non-Operating Humidity Range	5 - 95%
Non-operating temperature - Celsius	-40 to 65°C
Non-operating temperature - fahrenheit	-40 to 149°F
On mode power demand in Standard Dynamic Range (SDR)	13 W
Operating altitude	Up to 5,000 m
Operating altitude	Up to 16,400 ft
Operating temperature range	41 to 95°F
Package dimensions (W x D x H)	69.9 x 16 x 44.6 cm
Package dimensions (W x D x H)	27.52 x 6.3 x 17.56 in
Package weight	19.8 lb
Package weight	9 kg
Pallet (layers)	Slip Sheet: 5 layers (20 ft, 40 ft, 40 ft HQ); Pallet: 4 layers (20' ft & 40' ft); 5 layers (40' ft HQ)
Pallet dimensions	Slip sheet: 44.49 x 27.91 x 88.35 in (20 ft, 40 ft, 40 HQ); Pallet: 44.49 x 27.91 x 75.63 in (20 ft, 40 ft); Pallet: 44.49 x 27.91 x 93.19 in (40 HQ)
Pallet dimensions (W x D x H)	Slip sheet: 113 x 70.9 x 224.4 cm (20 ft, 40 ft, 40 HQ); Pallet: 113 x 70.9 x 192.1 cm (20 ft, 40 ft); Pallet: 113 x 70.9 x 236.7 cm (40 HQ)
Pallet weight	Slip sheet: 704.6 lb (20 ft, 40 ft, 40 HQ); Pallet: 592.2 lb (20 ft, 40 ft); 733.3 lb (40 HQ)
Pallet weight	Slip sheet: 319.6kg (20 ft, 40 ft, 40 HQ); Pallet: 268.6 kg (20 ft, 40 ft); 332.6 kg (40 HQ)
Panel bit depth	6 bit + FRC ^[1]
Pixels per inch (ppi)	82 ppi
Power supply type	Internal
Product caption image	https://prismpuoint.int.inc.hpicorp.net/PRO.Crystal.1/DAMHandler/Accessories/Rhone_527f_Jetblack_Catalog_VisID_GrayBG_Rear_Callouts.png
Product caption image	https://prismpuoint.int.inc.hpicorp.net/PRO.Crystal.1/DAMHandler/Accessories/Rhone_527f_Jetblack_Catalog_VisID_GrayBG_Front_Callouts_Wallpaper.png
Product color	Black
Product dimensions with stand (W x D x H)	24.08 x 9.02 x 21.38 in
Products per pallet	Slip Sheet: 35 (20 ft, 40 ft, 40 ft HQ); Pallet: 28 (20 ft, 40 ft); 35 (40 ft HQ)

Products per pallet layer	7
Refresh rate (maximum)	120 Hz
Resolution (maximum)	FHD (1920 x 1080 @ 120 Hz) ^[1]
Screen treatment	Anti-glare
Special features	Ergonomic OOBE setup coaching; Progressive white balance ^[15]
Stand color	Black; Silver
Stand type	With stand; Height adjustable stand
Standby mode power demand	0.5 W
Storage altitude	Up to 40,000 ft
Storage altitude	Up to 12,192 m
Swivel	±45°
Technology logo 1	https://h10003.www1.hp.com/digmedialib/prodimg/lowres/c03123379.png
Technology logo 2	https://h10003.www1.hp.com/digmedialib/prodimg/lowres/c08717783.png
Tilt	-5 to +20°
UNSPSC code	43211902
USB Type-A	4 USB Type-A 5Gbps signaling rate (1 charging)
Usb b (hub enablement)	1 USB-B
VESA mounting	100 x 100 mm
Vertical viewing angle	178°
Video connectors	HDMI; DisplayPort™-in
Viewable diagonal size	27" (68.58 cm)
pivot	±90°

^[1] All specifications represent the typical specifications provided by HP's component manufacturers, actual performance may vary either higher or lower.

^[2] DisplayPort™ 1.2 or HDMI 1.4 required to drive panel at its native resolution. The video card of the connected PC must be capable of supporting 1920 x 1080 at 60 Hz with 6-bit color using one DisplayPort™, HDMI.

^[3] Number of colors through A-FRC technology.

^[4] Included cables may vary by country.

^[5] Lock sold separately.

^[6] Host PC requires Windows 10 and above. HP Display Center is available on the Microsoft store.

^[7] The Client Management Script Library must be downloaded to the connected PC to run CMSL commands. Some limitations may apply to legacy displays. Visit hp.com to download HP CMSL.

^[15] Ergonomic Setup Guide is available through HP Display Center. Host PC requires Windows 10 or higher. HP Display Center is available on the Microsoft store.

^[16] Maximum brightness and contrast setting with maximum power loading on USB downstream ports (for power consumption maximum); Factory default brightness and contrast setting with 25% power loading on USB downstream ports (for power consumption typical).

Accessories for PC

Stands/Mounting Brackets

★ : Recommended

Mounting Brackets

HP B560 PC Mounting Bracket

763U8AA

Stands

HP Quick Release Monitor Single Arm

762U0AA

Security

Security Cables

HP Business PC Security Lock v3 Kit

3XJ17AA

Components/Upgrades

Chassis/Rails

HP Desktop Mini v4+ VESA Sleeve

99T54AA

Audio Devices

PC Speakers

HP S101 Speaker Bar

5UU40AA

Disclaimer — Copyright

© Copyright 2025 HP Development Company, L.P. The information contained herein is subject to change without notice. The only warranties for HP products and services are set forth in the express warranty statements accompanying such products and services. Nothing herein should be construed as constituting an additional warranty. HP shall not be liable for technical or editorial errors or omissions contained herein.

Generated by Dynamic Collateral Tool – (ww-en) – Aug 08, 2025 10:25 AM UTC+0000