

Key Features

- **Lifelike Visuals:** Pantone-validated display covering 100% of the sRGB spectrum to offer vivid colors
- **Precise Color:** Factory-calibrated to professional-grade Delta E<2 color accuracy
- **Seamless Connectivity:** 90W fast-charging USB-C port, HDMI 2.0, DisplayPort 1.4, and USB-A 3.2 ports
- **Unlimited Flexibility:** Auto Pivot & Ergonomic Stand with tilt, swivel, pivot and height adjustments
- **The Visible Difference:** 2K (2560*1440) resolution IPS panel with 27" frameless design



Product Description

Designed with creative professionals in mind, the ViewSonic VP2756A-2K delivers stunning true-to-life colors on screen. Pantone validated 100% sRGB coverage provides precise color reproduction, ensuring your work looks how it should, every time. A fast 120Hz refresh rate offers fluid visuals and smoother motion for both creative tasks and everyday use. A USB-C port that easily connects with your devices for easy charging and data transfer. Ergonomic engineering gives you the flexibility to do more without injury, while Auto Pivot lets shift between horizontal and vertical orientations effortlessly, letting your work be viewed how it's supposed to be.

Visit Us www.viewsonic.com

DISPLAY

Display Size (in.):	27
Viewable Area (in.):	27
Panel Type:	IPS Technology
Resolution:	2560 x 1440
Resolution Type:	QHD (Quad HD)
Static Contrast Ratio:	1,500:1 (typ)
Dynamic Contrast Ratio:	20M:1
Light Source:	LED
Brightness:	350 cd/m ² (typ)
Colors:	16.7M
Color Space Support:	8 bit true
Aspect Ratio:	16:9
Response Time (Typical GTG):	5ms
Response Time (GTG w/OD):	5ms
Viewing Angles:	178° horizontal, 178° vertical
Backlight Life (Hours):	30000 Hrs (Min)
Curvature:	Flat
Refresh Rate (Hz):	120
Variable Refresh Rate Technology:	Yes
Low Blue Light:	Hardware solution
Flicker-Free:	Yes
Color Gamut:	Adobe RGB: 87% size / 83% coverage (Typ) DCI-P3: 87% size / 86% coverage (Typ) EBU: 116% size / 100% coverage (Typ) REC709: 118% size / 100% coverage (Typ) SMPTE-C: 127% size / 100% coverage (Typ) NTSC: 83% size (Typ) sRGB: 118% size / 100% coverage (Typ)
Pixel Size:	0.233 mm (H) x 0.233 mm (V)
Surface Treatment:	Anti-Glare, Hard Coating (3H)

COMPATIBILITY

PC Resolution (max):	2560x1440
Mac® Resolution (max):	2560x1440
PC Operating System:	Windows 10/11 certified; macOS tested
Mac® Resolution (min):	2560x1440

CONNECTOR

USB 3.2 Type A Down Stream:	3
USB 3.2 Type C Down stream:	1 (15W power charger)
USB 3.2 Type C Up Stream; DisplayPort Alt mode :	1 (90W power charger)
HDMI 2.0:	1
DisplayPort:	1
Power in:	3-pin Socket (IEC C14 / CEE22)

AUDIO

Internal Speakers:	2Watts x2
--------------------	-----------

POWER

Eco Mode (Conserve):	17.1W
Eco Mode (optimized):	20.2W
Consumption (typical):	27.5W
Consumption (max):	44.8W
Voltage:	AC 100-240V
Stand-by:	0.3W
Power Supply:	Internal Power Supply

ADDITIONAL HARDWARE

Kensington Lock Slot:	1
-----------------------	---

CONTROLS

Physical Controls:	Key 1, Key 2, Key 3, Key 4, Key 5, Key 6 (power)
On Screen Display:	Input Select, Audio Adjust, ViewMode, Color Adjust, Manual Image Adjust, Setup Menu

OPERATING CONDITIONS

Temperature:	32°F to 104°F (0°C to 40°C)
Humidity (non-condensing):	20% to 90%

WALL MOUNT

VESA Compatible:	100 x 100 mm
------------------	--------------

INPUT SIGNAL

Frequency Horizontal:	15 ~ 200KHz
Frequency Vertical:	50 ~ 120Hz

VIDEO INPUT

Digital Sync:	TMDS - HDMI (v2.0), PCI-E - DisplayPort (v1.4), Micro-Packet - Type C
---------------	---

ERGONOMICS

Height Adjust (mm):	130
Swivel:	120°
Tilt (Forward/Back):	-5° / 21°
Pivot (Right/Left):	90° / 90°

WEIGHT (IMPERIAL)

Net (lbs):	16
Net Without Stand (lbs):	10.6
Gross (lbs):	25.2

WEIGHT (METRIC)

Net (kg):	7.3
Net Without Stand (kg):	4.8
Gross (kg):	11.4

DIMENSIONS (IMPERIAL) (WXHxD)

Packaging (in.):	29.1 x 18.3 x 8.9
Physical (in.):	24.15 x 16.15~21.27 x 8.46
Physical Without Stand (in.):	24.15 x 14.28 x 2.1

DIMENSIONS (METRIC) (WXHxD)

Packaging (mm):	740 x 465 x 225
Physical (mm):	613.38 x 410.31~540.31 x 214.96
Physical Without Stand (mm):	613.38 x 362.73 x 53.3

GENERAL

Regulations:	cTUVus, FCC-B, ICES003, Energy Star, EPEAT, CEC, BSMI
PACKAGE CONTENTS:	VP2756A-2K x1, 3-pin Plug (IEC C13 / CEE22) x1, HDMI Cable (v2.0; Male-Male) x1, USB Type-C Cable (Male-Male) x1, USB A/B Cable (v3.2; Male-Male) x1, Quick Start Guide x1
Recycle/Disposal:	Please dispose of in accordance with local, state or federal laws.
Warranty:	*Warranty offered may differ from market to market
Power Management:	Energy Star standards, EPEAT