

ThinkStation P3 Tower Gen 2 30HT006SUS

Lenovo

PSREF
Product Specifications
Reference

PERFORMANCE

Processor

Intel® Core™ Ultra 9 285, 24C (8P + 16E) / 24T, Max Turbo up to 5.6GHz, 36MB Intel® Smart Cache

AI PC Category^[1]

AI-Ready Workstations

Processor Sockets

1x FCLGA1851

Integrated Graphics

Integrated Intel® Graphics

Discrete Graphics

1x NVIDIA® RTX A400 4GB

Chipset

Intel® W880 Chipset

Memory

1x 16GB UDIMM DDR5-5600 Non-ECC

Memory Slots

Four DDR5 UDIMM slots, dual-channel capable

Max Memory^[2]

Up to 256GB (4x 64GB DDR5 CUDIMM)

PCIe® NVMe® Controller

Integrated NVMe® Controller

PCIe® NVMe® Drive

1x 512GB SSD M.2 2280 PCIe® 4.0x4 Performance NVMe® Opal

SATA Controller

Onboard Intel® RSTe SATA RAID

SATA/SAS Drive

None

Optical

9.0mm DVD±RW

Audio Chip

High Definition (HD) Audio, Realtek® ALC623-CG codec

Power Supply

750W Platinum Fixed

DESIGN

Keyboard

USB Traditional Keyboard, Black, English

Mouse

USB Calliope Mouse, Black

Dimensions (WxDxH)^[3]

180 x 370 x 415 mm (7.09 x 14.57 x 16.34 inches)

Weight^[4]

14.38 kg (31.70 lbs, maximum configuration)

CONNECTIVITY

Onboard Ethernet

Intel® I219-LM, 1x GbE RJ-45

Optional Ethernet

None

WLAN + Bluetooth®

Intel® Wi-Fi® 7 BE200, 802.11be 2x2 + BT5.4, vPro®

Card Reader

SD Card Reader

Front Ports

- 1x USB-C® (USB 20Gbps / USB 3.2 Gen 2x2), data transfer only
- 2x USB-A (USB 5Gbps / USB 3.2 Gen 1)
- 2x USB-A (USB 10Gbps / USB 3.2 Gen 2)
- 1x headphone / microphone combo jack (3.5mm)
- 1x microphone (3.5mm)

Optional Front Ports (configured)

1x SD card reader

Rear Ports

- 2x USB-A (Hi-Speed USB / USB 2.0)
- 2x USB-A (USB 5Gbps / USB 3.2 Gen 1), one supports Smart Power On
- 1x HDMI® 2.1 TMDS
- 2x DisplayPort™ 1.4
- 1x Ethernet (RJ-45)
- 1x line-out (3.5mm)

Optional Rear Ports (configured)

1x DP (Flex IO)

SECURITY & PRIVACY

Security Chip

Discrete TPM 2.0, TCG certified, FIPS 140-2 certified

Physical Locks

- Kensington® Security Slot™, 3 x 7 mm
- Padlock Loop

Cover Lock

None

Cable Lock

No Cable

Chassis Intrusion Switch

None

MANAGEABILITY

System Management

Intel® vPro® Enterprise with Intel® AMT 16

SERVICE

Base Warranty

3-year, Onsite

Included Upgrade

None

CERTIFICATIONS

ISV Certifications

Please visit [ISV certifications for Lenovo® Workstations](#)

Mil-Spec Test

MIL-STD-810H military test passed

SOFTWARE

Operating System

Windows® 11 Pro, English (US) / English (UK)

Bundled Software

None

MODEL

TopSeller : Yes **Announce Date** : 2025-06-10

EAN / UPC / JAN : 199271559536 **End of Support** : 2033-05-17



Product image is a sample, it may not match the real color of this model

Note:

[1] With scalable configurations of higher-performance CPUs and professional NVIDIA RTX GPUs, in addition to advantage of the same modern AI PC technology, AI-Ready workstation power the demanding AI consumption & development workflows.

[2] The max memory is based on the test results with current Lenovo memory offerings.

[3] The system dimensions may vary depending on configurations.

[4] The system weight is approximate and based on results in Lenovo lab, which varies depending on the source of component, variance of the distribution of each component, and manufacturing process. It may not be the exact weight for each specific model.

· Lenovo reserves the right to change specifications without notice.

To see more note information, please access the [web page](#).

Premier Support - A direct 24x7x365 line to our most elite technicians.



Advanced technical support, 24x7x365, in more than 100 markets



Technical Account Managers for proactive relationship and escalation management



Comprehensive hardware & OEM software support



Priority on service delivery and repair parts



Single point of contact for simplified end-to-end case management



Lenovo Service Connect Portal for customized reporting and product support

Accidental Damage Protection - Protection of your PC from the unexpected.

Experience shows that a significant portion of devices may be damaged (and not covered under warranty) in the first three years. Lenovo's Accidental Damage Protection service covers accidents beyond the system warranty such as drops, spills, bumps and even electrical surges. Make sure your new device has maximum protection, avoid unplanned costs and get peace of mind.

Base Warranty - Included with the systems you purchase, default 1- or 3-year coverage window.

Warranty Extensions & Upgrades - Service and protection that's right for your circumstances.

- Pick Up & Return Courier
- Onsite Support
- Technician Installed Customer
- Replaceable Unit Service
- International Warranty Upgrade

Lenovo may not offer the products, services or features discussed in this document in all regions. Lenovo may withdraw an offering at any time. Information is subject to change without notice. Consult your local representative for information on offerings available in your area. Lenovo reserves the right to change specifications or other product information without notice. Lenovo is not responsible for photographic or typographical errors. Lenovo provides this publication "as is" without warranty of any kind, either express or implied, including the implied warranties of merchantability or fitness for a particular purpose.

Recommended Accessories



Lenovo USB-C to Ethernet Adapter

4X90S91831

The Lenovo USB-C to Ethernet Adapter is quick and easy way to connect your USB-C enabled notebook to Ethernet connections. It's ideal for imaging of systems or transferring large files quickly.

Recommended Services

BEST	4Y Premier Support Plus upgrade from 3Y Onsite (5WS1L39273)
BETTER	3Y Premier Support Plus upgrade from 3Y Onsite (5WS1L39093)
GOOD	3Y Premier Support Upgrade from 3Y Onsite (5WS0U26646)

Please click [here](#) to view the full list of accessories.



PSREF
Product Specifications
Reference