



HP DesignJet T950 36-in Printer (2Y9H1A)

Overview



The world's most efficient A4/A-A0/E printing experience to boost productivity[1]

Boost productivity with the world's most efficient A4/A to A0/E experience.[1] Print multi-size CAD, posters, and more with the integrated input/output tray. Save time with HP Click.[4] And meet environmental needs with this compact plotter.

EFFICIENT—Save time, get through more jobs

Print it all—from renders and CAD drawings to educational posters and durable retail signage, you'll see high-quality results across print sizes with pigment-based HP Flex Tech Inks.

SUSTAINABLE—Save energy[5] and minimize waste[6][7]

Invest in a compact, robust plotter made with at least 35% recycled plastic.[6]

CONNECTED—Seamless and secure by design

Simplify printing with HP Click[4]—available as a driver and app. Save time with real-print preview and automatic error detection.

[1] Based on test results using HP Click with the HP DesignJet T850. This solution enables printing in fewer steps compared to main competitor printing solutions. Printing a 5-page mixed job set with A1 and A3 takes 3 steps using HP Click vs. 12 steps with competitor A and 8 steps with competitor B. Testing performed by Sogeti, April 2023. Detailed test report is available upon request.

[4] HP Click App is compatible with Windows and Mac. HP Click Driver is compatible with Windows 11 only. HP Click software is only compatible with Original HP ink supplies. Applicable to PDF, JPEG, TIFF, DWF, and HP-GL/2 files.

[5] The percentage reductions in energy consumption are based on tests conducted by HP, 2024. Data based on the implementation of auto-scheduled on/off usage in various printer models, measured on a monthly basis. Actual savings may vary depending on the specific usage patterns, printer models, and environmental conditions.

[6] Declared %RCP content is based on the quantity and weight of parts made with RCP resin over the total plastic parts.

[7] Program availability varies. See <https://www.hp.com/go/recycle>.

Specifications

Print quality color (best)	Up to 2400 x 1200 optimized dpi
Functions	Print
Connectivity, standard	Gigabit Ethernet (1000Base-T), Wi-Fi 802.11b/g/n
Software included	HP Click App, HP Click Driver for Windows 11, HP app for Windows, macOS, Android, and iOS
Technical features	A3 input tray;Stacker;A3 sheet organizer;Auto-power on/off scheduler;Max. resolution 2400 x 2400 dpi;HP Wolf Pro Security;130/300 ml cartridges;HP Flex Tech Inks
Energy star certified	Yes
Dimensions (W x D x H)	1407 x 720 x 967 mm
Dimensions (W x D x H)	55.4 x 28.3 x 38.1 in
Weight	56 kg
Weight	123.5 lb
Power consumption	35 W (printing), <5.5 W (ready), <2.5 W (sleep), <0.2 W (off). Auto-scheduled printer on/off usage.
Environmental certification	ENERGY STAR, EPEAT, UL ECOLOGO® certified inks, CE marking (including WEEE, RoHS, REACH, ErP). In compliance with applicable WW RoHS materials restriction requirements.
What's in the box	HP DesignJet T950 Printer, printhead, introductory ink cartridges, printer stand, spindle, guide, warranty flyer, power cord

Additional specifications

Acoustic power emissions (active, printing)	5.8 B(A) (operating), <3.4 B(A) (idle)
Acoustic pressure emissions	42 dB(A) (operating), <16 dB(A) (idle)
Additional storage	2.7 GB reprint queue
Cartridge volume	130 ml; 300 ml
Color ink technology	Pigment
Datasheet photo 1	https://hp.widen.net/content/acbtqd5srp/png/HP%20DesignJet%20T950%20Printer%20-%20Front%20AEC_4636864.png
Dynamic security	Dynamic security enabled printer
Electromagnetic compatibility	Compliant with Class B requirements, including: USA (FCC rules), Canada (ICES), EU (RED Directive), Australia (ACMA), New Zealand (RSM), China (CCC), Japan (VCCI); Korea (KCC)
Features	Sheet input tray; Automatic horizontal cutter; Stand; Wi-Fi; USB
Finished output handling	Sheet feed, roll feed, front-loading input tray (100 sheet capacity), sheet organizer (50 sheet capacity[4]), stacker (40 sheet capacity[4]), automatic horizontal cutter
Functions	Print
HP ePrint capability	Yes
Ink drop	6 pl (C, M, Y); 12.6 pl (mK)
Ink types	Pigment-based (C, M, Y, mK)
Internal Storage	None
Line accuracy	±0.1%[2]
Maximum optical density (black)	15 L* min/1.7 D[3]
Maximum roll diameter	5.5 in
Media sizes standard (metric rolls)	369 to 914 mm
Media sizes standard (sheets, rolls)	14.5 to 36 in
Media sizes supported	Input tray: A4, A3; Manual feed: A4, A3, A2, A1, A0
Media sizes supported	Input tray: A, B; Manual feed: A, B, C, D, E
Media sizes, custom	Front-loading input tray: 210 x 279 to 305 x 457 mm; Manual feed: 210 x 279 to 914 x 1676 mm

Media sizes, custom	Front-loading input tray: 8.3 x 11 to 12 x 18 in; Manual feed: 8.3 x 11 to 36 x 66 in
Media thickness	Up to 11.8 mil
Media thickness maximum (metric)	Up to 0.3 mm
Media types	Bond and coated paper (bond, coated, heavyweight coated, plain, bright white, blueprint), technical paper (natural tracing), film (clear, matte), photographic paper (ID satin, ID gloss), self-adhesive (adhesive matte/gloss, adhesive polypropylene gloss), Polypropylene (matte), banner, signage
Media weight, recommended	60 to 280 g/m ² (roll/manual feed); 64 to 220 g/m ² (front-loading input tray)
Media width, maximum	36 in
Media width, maximum	914 mm
Memory	1 GB
Model size	914 mm
Model size	36 in
Network ready	Standard
Non-Operating Humidity Range	0 to 95% RH
Non-printable area (cut-sheet)	5 x 5 x 5 x 5 mm
Non-printable area (cut-sheet)	0.2 x 0.2 x 0.2 x 0.2 in
Non-printable area (roll media)	0.2 x 0.2 x 0.2 x 0.2 in
Non-printable area (roll media)	5 x 5 x 5 x 5 mm
Number of cartridges	4
Operating altitude	Up to 3000 m
Operating altitude	Up to 9843 ft
Operating humidity range	20 to 80% RH
Operating temperature range	5 to 40°C
Operating temperature range	41 to 104°F
Orderable supplies	HP Original Ink: HP 738 cartridges (Black, Cyan, Magenta, Yellow), and HP 739 printhead

Package dimensions (W x D x H)	1575 x 630 x 780 mm
Package dimensions (W x D x H)	62 x 24.8 x 30.7 in
Package weight	185.3 lb
Package weight	84 kg
Playbook TS icon connectivity	https://h10003.www1.hp.com/digmedialib/prodimg/lowres/c08201987.png
Playbook TS icon dimensions AiO	https://h10003.www1.hp.com/digmedialib/prodimg/lowres/c08192862.png
Playbook TS icon display AiO	https://h10003.www1.hp.com/digmedialib/prodimg/lowres/c08169148.png
Post consumer recycled plastic in hardware by weight of plastic	40%
Power	Input voltage (auto ranging): 100-240 V (±10%), 50/60 Hz (±3 Hz), 1.2 A max
Print Cartridge/Bottle, Color(s)	Cyan, magenta, yellow, matte black
Print Cartridges/Bottle, Number	4 (C, M, Y, mK)
Print Technology	Ink
Print cartridge/bottle volume	300 ml, 130 ml
Print head nozzles	1376 per color; 5504 in total
Print heads	1 (C, M, Y, mK)
Print languages	TIFF, JPEG, URF, PDF, HP-GL/2, HP-RTL, CALS G4
Print multi-size files in one click	Yes
Print speed	21 sec/page on A1, 120 A1 prints per hour[1]
Print speed	20 to 30 sec/page on D size
Print speed	21 sec/page for D size, 120 D size 24" x 36" prints per hour[1]
Print technology	HP Thermal Inkjet
Printer Applications	Architecture; Engineering; Maps
Printer drivers included	Raster driver for macOS and Windows, HP Click Driver for Windows 11, HP-GL/2 driver for Windows

Printing path	Wi-Fi Direct, remote printing, HP Click App, HP Click Driver for Windows 11, Apple AirPrint and HP app for Android and iOS devices, Windows and macOS printer drivers, printing support for Chrome OS
Product logos	AirPrint; CE marking; ENERGY STAR; EPEAT green; UL ECOLOGO; IPv6 Ready; Mac; Wi-Fi Certified; Windows 11 Compatible; HP Wolf Pro Security
Recommended media	HP Universal Bond Paper (FSC® certified)[4] (recyclable)[5]; HP Coated Paper (FSC® certified)[4] (recyclable)[5]; HP Heavyweight Coated Paper (FSC® certified)[4] (recyclable) [5]; HP Recycled[7] Removable Adhesive Fabric (REACH compliant)[6]; HP Opaque Scrim Banner (REACH compliant)[6]; HP Production Matte Canvas (REACH compliant)[6]; HP Universal Instant-dry Gloss Photo Paper (REACH compliant, FSC® certified)[4,6]; HP Universal Instant-dry Satin Photo Paper (REACH compliant, FSC® certified)[4,6]; HP Everyday Matte Polypropylene (REACH compliant)[6]
Remote print enabled	Yes
Roll external diameter	5.5 in
Roll external diameter	140 mm
Roll maximum input	1
Roll maximum weight	13 kg
Roll maximum weight	28.6 lb
Roll size	Up to 36 in
Safety	USA and Canada (CSA certified); EU (RED Directive, EN 62368-1 compliant); Singapore (PSB); China (CCC); Mexico (NYCE); Argentina (IRAM); India (BIS)
Security features	HP Wolf Pro Security, HP Secure Boot, Allowlisting, Security event logging, Disable network ports and protocols, SNMPv3, 802.1x compatibility, TLS/SSL, Semi-permanent-queue Erase, HP Web JetAdmin, HP Security Manager, SIEM Integration
Storage	2.7 GB reprint queue
Storage temperature range	-25 to 55°C
Storage temperature range	-13 to 131°F
Supported Primary Applications	Banners; Line drawings; Maps; Posters; Presentations; Renderings; Signage
Sustainability Impact	ENERGY STAR®; EPEAT®; UL Ecologo
Technology logo 1	AHID/cce10ebbd356d96074154a12dc62032a64b058f3
Technology logo 2	AHID/60d2a69d632efba286c546dd6a2fcfdb5c3c9e1f

Technology logo 3 AHID/cd33e848211911e4369b10008531951b0aa3cde7

Technology logo 4 AHID/c51bf05ff1023abad6fda02c5a970763b91946f4

Technology logo 5 AHID/6615658f92b8dd21f3c5b78f3bea628bd257123b

Technology logo 6 AHID/0e41ea2a916263d4c3403cc03016fcaae7311969

Technology logo 7 AHID/1f8b1ff3a68a6ba2a0939f2536845c50fe9dec4f

Theoretical minimum line width 0.02 mm (via raster driver)

Theoretical minimum line width 0.0008 in (via raster driver)

UNSPSC code 43212104

UPC number (AB1) 198701770640; (ABG) 196548313099; (AC4) 197498560588; (ACJ) 196548313105; (AKV) 197498560595; (B19) 196548313112; (B1K) 196548313129; (BCD) 196548313136; (EMU) 196548313143

Web address for additional information <https://www.hp.com/go/designjet-t950>

Ink/Toner/Paper/Printer Supplies

Ink Supplies

★ : Recommended

HP Graphic Arts Inks/Printheads

HP 4287 DesignJet Printhead	7FP50A
HP 738 130-ml Black DesignJet Ink Cartridge	498N4A
HP 738 130-ml Cyan DesignJet Ink Cartridge	498N5A
HP 738 130-ml Magenta DesignJet Ink Cartridge	498N6A
HP 738 130-ml Yellow DesignJet Ink Cartridge	498N7A
HP 738 130-ml Yellow DesignJet Ink Cartridge	A4TL5A
HP 738 300-ml Black DesignJet Ink Cartridge	498N8A
HP 738 300-ml Cyan DesignJet Ink Cartridge	676M6A
HP 738 300-ml Magenta DesignJet Ink Cartridge	676M7A
HP 738 300-ml Yellow DesignJet Ink Cartridge	676M8A
HP 738 300-ml Yellow DesignJet Ink Cartridge	A4TL7A
HP 738B 130-ml Black DesignJet Ink Cartridge	498P2A
HP 738B 300-ml Black DesignJet Ink Cartridge	498P6A
HP 739 DesignJet Printhead Replacement Kit	498N0A

Accessories

Paper Handling

★ : Recommended

Roll Core Adapters

HP DesignJet 3-in Core Adapter

CN538A

Spindles

HP DesignJet 36-in Spindle

7F2C8A

Scanners/Copiers/Faxes

Scanners

★ : Recommended

Large Format Scanners

HP HD Pro 2 42-in Scanner	5EK00A
HP SD Pro 2 44-in Scanner	5EK01A

Disclaimer — Copyright

© Copyright 2025 HP Development Company, L.P. The information contained herein is subject to change without notice. The only warranties for HP products and services are set forth in the express warranty statements accompanying such products and services. Nothing herein should be construed as constituting an additional warranty. HP shall not be liable for technical or editorial errors or omissions contained herein.

Generated by Dynamic Collateral Tool – (ww-en) – Sep 13, 2025 7:35 PM UTC+0000