

PERFORMANCE

Processor	Intel® Core™ Ultra 5 235, 14C (6P + 8E) / 14T, Max Turbo up to 5.0GHz, 24MB
AI PC Category ^[1]	AI PC
NPU	None
Graphics	Integrated Intel® Graphics
Chipset	Intel® Q870 Chipset
Memory	1x 32GB SO-DIMM DDR5-5600
Memory Slots	Two DDR5 SO-DIMM slots, dual-channel capable
Max Memory	Up to 64GB (2x 32GB DDR5 SO-DIMM)
Storage	256GB SSD M.2 2280 PCIe® 4.0x4 NVMe® Opal 2.0
Max Storage Support	Up to three drives, 3x M.2 2280 SSD • M.2 2280 SSD up to 2TB each
Card Reader	No card reader
Optical	None
Audio Chip	High Definition (HD) Audio, Realtek® ALC233VB or Conexant CX11771 codec
Speakers	Premium, 2Wx1
Power Supply	135W 90% Adapter
DESIGN	
Keyboard	USB Traditional Keyboard, Black, English
Mouse	USB Calliope Mouse, Black
Expansion Slots	• One PCIe® 4.0 x8, low-profile • Three M.2 PCIe® Gen 4x4 slots (for SSD) • One M.2 slot (for WLAN)
Case Color	Black
Stand	Vertical Stand

Adapter Cage	None
Toolless Chassis Screw	None
Dust Filter	None
Mounting	None
IO Box	None
Pen	Pen Not Supported
Form Factor	Tiny (1L)
Dimensions (WxDxH)	179 x 182.9 x 36.5 mm (7.05 x 7.2 x 1.44 inches)
Weight	Around 1.34 kg (2.95 lbs)
CONNECTIVITY	
WLAN + Bluetooth®	Intel® Wi-Fi® 6E AX211, 802.11ax 2x2 + BT5.3, vPro®
WWAN	Non-WWAN
Ethernet	Integrated 100/1000M
Front Ports	• 1x USB-C® (USB 20Gbps / USB 3.2 Gen 2x2), data transfer only • 1x USB-A (USB 10Gbps / USB 3.2 Gen 2), Always On • 1x USB-A (USB 10Gbps / USB 3.2 Gen 2) • 1x headphone / microphone combo jack (3.5mm)
Rear Ports	• 1x USB-A (USB 5Gbps / USB 3.2 Gen 1) • 3x USB-A (USB 10Gbps / USB 3.2 Gen 2), one supports Smart Power On • 1x HDMI® 2.1 TMDS • 1x DisplayPort™ 1.4 • 1x Ethernet (GbE RJ-45)
Optional Rear Ports (configured)	1x DP
SECURITY & PRIVACY	
Security Chip	Discrete TPM 2.0, TCG certified, FIPS 140-2 certified
Fingerprint Reader	No fingerprint reader
Physical Locks	Kensington® Security Slot™, 3 x 7 mm

Chassis Intrusion Switch	Chassis Intrusion Switch
--------------------------	--------------------------

MANAGEABILITY

System Management	Intel® vPro® Enterprise
-------------------	-------------------------

SERVICE

Base Warranty	3-year, Onsite
Included Upgrade	None

CERTIFICATIONS

Green Certifications	• ENERGY STAR® 9.0 • ErP Lot 3 • RoHS compliant • TCO Certified, generation 10
----------------------	--

Mil-Spec Test	MIL-STD-810H military test passed (Low Pressure [Altitude], High Temperature, Low Temperature, Temperature Shock, Humidity, Sand and Dust, Vibration, Shock, Solar Radiation, Contamination by Fluids, Salt Fog)
---------------	--

SOFTWARE

Operating System	Windows® 11 Pro, English
------------------	--------------------------

Bundled Software	None
------------------	------

ACCESSORIES

Bundled Accessories	None
---------------------	------

MODEL

TopSeller	: Yes	Announce Date	: 2025-07-01
EAN / UPC / JAN	: 199271850916	End of Support	: 2031-12-27

Note:
[1] AI PCs have a NPU capable of 10+ TOPs to run the Copilot assistant by pressing the optional Microsoft Copilot key or using Win + C.
· Lenovo reserves the right to change specifications without notice.
· California Electronic Waste Recycling Fee In California, per state law, Lenovo charges an electronic waste recycling fee on this covered device at the time of sale of the product. For more information, go to: <https://www.calrecycle.ca.gov/Electronics/Consumer>
To see more note information, please access the [web page](#).

Premier Support - A direct 24x7x365 line to our most elite technicians.



Advanced technical support, 24x7x365, in more than 100 markets



Technical Account Managers for proactive relationship and escalation management



Comprehensive hardware & OEM software support



Priority on service delivery and repair parts



Single point of contact for simplified end-to-end case management



Lenovo Service Connect Portal for customized reporting and product support

Accidental Damage Protection - Protection of your PC from the unexpected.

Experience shows that a significant portion of devices may be damaged (and not covered under warranty) in the first three years. Lenovo's Accidental Damage Protection service covers accidents beyond the system warranty such as drops, spills, bumps and even electrical surges. Make sure your new device has maximum protection, avoid unplanned costs and get peace of mind.

Base Warranty - Included with the systems you purchase, default 1- or 3-year coverage window.

Warranty Extensions & Upgrades - Service and protection that's right for your circumstances.

- Pick Up & Return Courier
- Onsite Support
- Technician Installed Customer
- Replaceable Unit Service
- International Warranty Upgrade

Lenovo may not offer the products, services or features discussed in this document in all regions. Lenovo may withdraw an offering at any time. Information is subject to change without notice. Consult your local representative for information on offerings available in your area. Lenovo reserves the right to change specifications or other product information without notice. Lenovo is not responsible for photographic or typographical errors. Lenovo provides this publication "as is" without warranty of any kind, either express or implied, including the implied warranties of merchantability or fitness for a particular purpose.

Recommended Accessories



ThinkCentre Tiny VESA Mount II

4XFON03161

The ThinkCentre Tiny VESA Mount II is a unique design specific to house the Tiny PC while featuring the universal VESA mount configuration. The Mount supports both 75x75mm and 100x100mm VESA. The VESA standard enabl...

Recommended Services

BEST	4Y Premier Support Plus upgrade from 3Y Onsite (5WSIL39206)
BETTER	3Y Premier Support Plus upgrade from 3Y Onsite (5WSIL39278)
GOOD	3Y Premier Support Upgrade from 3Y Onsite (5WSOV07841)

Please click [here](#) to view the full list of accessories.



PSREF
Product Specifications
Reference