

# ViewSonic® LCD DISPLAY VG2441V


## Key Features

- **Instant, secure access** to your digital workspace using **Windows Hello**
- **Crystal-clear video with 5MP webcam**, privacy cover, dual microphones, and stereo speakers
- **120Hz refresh rate** ensures ultra-smooth visuals during meetings and multitasking
- **USB-C port** simplifies connections for audio, video, and data transfer
- **USB 3.2 hub** with 1 USB-C upstream, 3 USB downstream ports, HDMI, and DisplayPort inputs for **seamless multi-device connectivity**



## Product Description

The VG2441V is a 24" Full HD (1920 x 1080) **USB-C video conferencing monitor with Windows Hello**, designed to deliver secure, high-quality virtual meetings straight out of the box. With **facial recognition login via Windows Hello**, users can sign in quickly and securely—reducing password fatigue and minimizing the risk of visual hacking. A built-in **5MP adjustable webcam**, **dual microphones**, and **dual 2W speakers** provide sharp video and clear audio for professional-grade conferencing. The webcam's **±5° vertical tilt** ensures perfect framing, while the **built-in privacy cover** safeguards user privacy when the camera is not in use. The monitor supports streamlined connectivity with a **USB-C upstream port** for video, audio, and data, plus **HDMI, DisplayPort, and three USB 3.2 downstream ports**—making it ideal for both home and office environments. With a **120Hz refresh rate** and integrated **Eye ProTech+** technology (low blue light and flicker-free viewing), the VG2441V ensures smooth visuals and greater eye comfort throughout the workday. For additional productivity, it supports **vDisplay Manager** for on-screen control and **vSplit** for efficient window layout management—both available via the **ViewSonic Display Portal**. With full **ergonomic adjustability** including height, tilt, swivel, and pivot, the VG2441V adapts to your setup for long-lasting comfort and flexible workflows.



- |  |                                 |                 |
|--|---------------------------------|-----------------|
| 1. Menu Control Panel                      | 7. USB 3.2 Up Stream (Type C)   | 14. Slide Cover |
| 2. Speakers                                | 8. USB 3.2 Down Stream (Type A) | 15. IR Camera   |
| 3. VESA Compatible(Wall Mount 100 x 100mm) | 9. Audio Out                    |                 |
| 4. Power In                                | 10. USB Type C (Quick Charging) |                 |
| 5. HDMI                                    | 11. Microphones                 |                 |
| 6. Display Port                            | 12. IR Sensors                  |                 |
|  | 13. 5MP Camera                  |                 |

Visit Us [www.viewsonic.com](http://www.viewsonic.com)



**DISPLAY**

Display Size (in.):	24
Viewable Area (in.):	23.8
Panel Type:	IPS Technology
Resolution:	1920 x 1080
Resolution Type:	FHD (Full HD)
Static Contrast Ratio:	1,500:1 (typ)
Dynamic Contrast Ratio:	50M:1
Light Source:	LED
Brightness:	250 cd/m <sup>2</sup> (typ)
Colors:	16.7M
Color Space Support:	8 bit (6 bit + FRC)
Aspect Ratio:	16:9
Response Time (Typical GTG):	4ms
Response Time (GTG w/OD):	4.39ms
Viewing Angles:	178° horizontal, 178° vertical
Backlight Life (Hours):	30000 Hrs (Min)
Curvature:	Flat
Refresh Rate (Hz):	120
Variable Refresh Rate Technology:	Yes
Low Blue Light:	Hardware solution
Flicker-Free:	Yes
Color Gamut:	NTSC: 72% size (Typ) sRGB: 104% size (Typ)
Pixel Size:	0.275 mm (H) x 0.275 mm (V)
Surface Treatment:	Anti-Glare, Hard Coating (3H)

**COMPATIBILITY**

PC Resolution (max):	1920x1080
Mac® Resolution (max):	1920x1080
PC Operating System:	Windows 10/11 certified; macOS tested
Mac® Resolution (min):	1920x1080

**CONNECTOR**

USB 3.2 Type A Down Stream:	2
USB 3.2 Type C Down stream:	1 (15W power charger)
USB 3.2 Type C Up Stream; DisplayPort Alt mode :	1
3.5mm Audio Out:	1
HDMI 1.4:	1
DisplayPort:	1
Power in:	3-pin Socket (IEC C14 / CEE22)

**AUDIO**

Internal Speakers:	2Watts x2
--------------------	-----------

**POWER**

Eco Mode (Conserve):	12W
Eco Mode (optimized):	16W
Consumption (typical):	19W
Consumption (max):	64W
Voltage:	AC 100-240V
Stand-by:	0.5W
Power Supply:	Internal Power Supply

**ADDITIONAL HARDWARE**

Kensington Lock Slot:	1
Webcam:	5.0M pixel
Cable Organization:	Yes
Microphone:	Yes

**CONTROLS**

Physical Controls:	Key 1 (volume down), Key 2, Key 3, Key 4, Key 5, Key 6 (power)
On Screen Display:	Input Select, Audio/MIC Adjust, ViewMode, Color Adjust, Manual Image Adjust, Setup Menu

**OPERATING CONDITIONS**

Temperature:	32°F to 104°F (0°C to 40°C)
Humidity (non-condensing):	20% to 90%

**WALL MOUNT**

VESA Compatible:	100 x 100 mm
------------------	--------------

**INPUT SIGNAL**

Frequency Horizontal:	30 ~ 135KHz
Frequency Vertical:	48 ~ 120Hz

**VIDEO INPUT**

Digital Sync:	TMDS - HDMI (v1.4), PCI-E - DisplayPort (v1.2), Micro-Packet - Type C
---------------	---

**ERGONOMICS**

Height Adjust (mm):	150
Swivel:	90°
Tilt (Forward/Back):	-5° / 20°
Pivot (Right/Left):	90° / 90°

**WEIGHT (IMPERIAL)**

Net (lbs):	9.9
Net Without Stand (lbs):	6.4
Gross (lbs):	15

**WEIGHT (METRIC)**

Net (kg):	4.5
Net Without Stand (kg):	2.9
Gross (kg):	6.8

**DIMENSIONS (IMPERIAL) (WXHxD)**

Packaging (in.):	24.8 x 20.2 x 4.9
Physical (in.):	21.25 x 15.2~20.84 x 8.11
Physical Without Stand (in.):	21.25 x 13.66 x 2.31

**DIMENSIONS (METRIC) (WXHxD)**

Packaging (mm):	630 x 513 x 125
Physical (mm):	539.8 x 386.1~529.4 x 206.1
Physical Without Stand (mm):	539.8 x 346.9 x 58.6

**GENERAL**

Regulations:	cTUVus, FCC-B, ICES003, Energy Star, EPEAT, CEC, NOM, Mexico Energy
PACKAGE CONTENTS:	VG2441V x1, 3-pin Plug (IEC C13 / CEE22) x1, HDMI Cable (v1.4; Male-Male) x1, USB Type-C Cable (Male-Male; with Type-A adapter) x1, Quick Start Guide x1
Recycle/Disposal:	Please dispose of in accordance with local, state or federal laws.
Warranty:	*Warranty offered may differ from market to market
Power Management:	Energy Star standards, EPEAT

