

ViewSonic® DIRECT VIEW LED LDP217-121C


Key Features

- **4K UHD resolution with Mini LED** delivers ultra-fine detail, vivid color, and deep contrast for premium visual impact
- **Advanced COB technology** ensures enhanced durability with water, dust, and impact resistance—ideal for high-traffic professional spaces
- **All-in-One integration** simplifies installation by combining power, control, image stitching, and display
- Energy-efficient design with **common cathode LEDs** and **smart ICs** reduces power consumption and supports sustainable operation
- Smart collaboration tools include **PIP/PBP screen-split modes**, **LAN control**, and **wireless content sharing** via ViewShare and AirSync



Product Description

The ViewSonic LDP217-121C is a 217" enterprise-class **All-in-One LED Display** designed to elevate visual performance in premium corporate environments. Featuring **4K UHD resolution**, **Mini LED architecture**, **600 nits of brightness** and a **10,000:1 contrast ratio**, it delivers sharp visuals and vibrant color with ultra-fine detail. Built with **Chip-on-Board (COB) technology**, the display ensures enhanced durability against impact, dust, and moisture, achieving **IP54** and **IK08 protection ratings**. **All-in-One integration** simplifies installation by combining power, control, image stitching, and display, allowing two people to complete setup in under two hours. A **31mm ultra-slim profile** and near bezel-free design create a premium aesthetic that complements any professional space. Powered by a **common cathode LED design** and **smart driving ICs**, the display reduces power consumption while supporting long-term energy efficiency. Designed for seamless collaboration, it features **PIP/PBP screen-split modes**, **LAN control**, and **optional wireless content sharing** via ViewShare (sold separately) and AirSync—making it a smart, future-ready LED video wall solution for high-end meeting spaces, training rooms, and executive boardrooms.



- | | | |
|--------------------------------|---------------------------------|-----------------|
| 1. Speakers | 8. RS232 x1 | 15. IR Receiver |
| 2. HDMI 2.0 x3 | 9. Audio Out x1 | |
| 3. RJ45 (Internet, Control) x2 | 10. Wireless/ Bluetooth Antenna | |
| 4. Audio Out x1 | 11. USB-C (Data only) x1 | |
| 5. IR Out x1 | 12. USB-A (2.0, 3.0) x2 | |

6. USB-A (Power) x1
7. HDMI 2.0 x1

13. Keypad
14. Power Button

Visit Us

www.viewsonic.com

SPECIFICATION

Screen Size:	217"
Display Area (mm):	4800 (H) x 2700(V)
Native Resolution:	3840x2160
Panel Technology:	Direct view LED
LED Package Type:	Flip Chip COB
Pixel Pitch (mm):	1.25
Brightness (max.):	600 nits (100 levels adjustable)
Contrast Ratio (typ.):	10000:1
Orientation:	Landscape
Viewing Angles (typ.):	H = 170, V = 170
LED Lifetime (typ.):	100,000 Hours
Local Storage:	Total 32GB (26GB available storage)
Embedded OS:	Android 9.0
Resolution Support:	VGA(640 x 480) to 4K(3840 x 2160@60hz)
HDTV Compatibility:	480p, 576p, 720p, 1080p, 2160p
Horizontal Frequency:	31K-94kHz
Vertical Scan Rate:	56-85Hz

INPUT

HDMI:	4 (HDMI 2.0/HDCP 2.2) (internal x3, external x1)
USB Type A:	3 (USB3.0 x1, USB2.0 x2)
RJ45 Input:	3 (internet x2, control x1)
IR in (3.5mm):	1
Wi-Fi Input:	2.4G/5G Hz
USB Type C:	1 (data only)

OUTPUT

HDMI out:	1 (HDMI 1.4/HDCP 1.4) (internal x1)
Speaker:	30Wx2
Audio out (3.5mm):	2
S/PDIF:	1
USB Type A (Power):	Shared with USB A input (USB 3.0 5V/0.9A x1, USB 2.0 5V/0.5A x1, USB 2.0 5V/2A x1)
USB Type C (Power):	Shared with USB Type C input (5V/1A x1)

CONTROL

RJ45 (LAN control):	1(shared with internet)
USB Type A (Services):	1(shared with USB A input)
RS232 (DB 9-pin female):	1
IR Receiver:	1

OTHERS

Power Supply Voltage:	100-120V/40A ~ 50/60Hz or 220-240V/25A ~ 50Hz (vary by country)
Power Consumption:	1150W (typ), 3449W (max) < 0.5W (Hibernate)
Operating Temperature:	0~40°C
Total LED Module Quantity:	512
Ingress Protection Rating:	IP54(Front)
Impact Protection Rating:	IK08(Front)
Net Weight:	864.21 lbs (392kg)
Gross Weight:	1384.50 lbs (628kg)
Product Dimensions (WxHxD):	189.45 x 112.09 x 1.61 inches (4812 x 2847 x 41mm)
Product Dimensions (WxHxD) with wall mount:	189.45 x 112.09 x 2.35 inches (4812 x 2847 x 59.8mm)
Packing Dimensions (WxHxD):	61.42 x 35.43 x 39.37 inches x3 (1560 x 900 x 1000 mm x3) 77.95 x 18.50 x 18.50 inch (1980 x 470 x 470 mm)

STANDARD ACCESSORIES

Power Cord:	2
LAN Cable (Cat 5E):	1
IR Extender Cable:	1
Remote Control:	1
Installation Guide:	1
Wall Mount:	1
Spare Parts:	LED module x 36
Maintenance Tool:	LD-MK-004 x1 LD-MK-006 x1

OPTIONAL ACCESSORIES

Maintenance Tool:	LD-MK-004 LD-MK-006
-------------------	------------------------