



EL2P MSPO PDU, 60 AMP, 3 PH , 36 OUTLETS

E36G31L

EL2P MSPO PDU, 60 AMP, (18)C13/C15, (18)C13/C15/C19/C21, IEC 60309 3P+E 9h 60A (IP44), BLACK

Specifications

Note	USA, Canada
Includes	Mounting Hardware
Product Type	PDU
Mount Orientation	Vertical
PDU Form Factor	0U FULL
Rack PDU Type	Monitored & Switched per Outlet
Plug Type	IEC 60309 3P+E 9h 60A (IP44)
Number of Circuit Breakers	6
Input Amperage (A)	60
Phase	3-Phase
Frequency Compatibility (Hz)	50/60
Current Measurement Accuracy (%)	±1%
Voltage Measurement Accuracy (%)	±1%
Power Measurement Accuracy (%)	±1%
Input Cord Length (ft.)	10
Input Cord Length (m)	3
Output Receptacles	(18)C13/C15, (18)C13/C15/C19/C21
Output Voltage (V)	208
Front Panel Display	Use display to set IP address, update firmware, quick configure, rotate display, balance loads across phases, view alarms, read current, voltage, power and energy on the device
Apparent Power (kVA)	17.3
Network Monitoring Port	Gigabit network port reduces labor by auto negotiating with data center level network switches
SNMP Compatibility	Yes
Network Card	Panduit EL2P Dual Gigabit Network Module
LED Indicators	Green LED indicates outlet is on
Material	Metal
Finish/Coating	Powder-Coated
Color	Black

Specifications (continued)

Overall Width (In.)	2
Overall Width (mm)	58
Overall Height (In.)	70
Overall Height (mm)	1780
Overall Depth (In.)	3
Overall Depth (mm)	75
Number of Rack Units	40
Maximum Operating Temperature (°C)	60
Maximum Operating Temperature (°F)	140
Minimum Operating Temperature (°C)	10
Minimum Operating Temperature (°F)	50
Maximum Storage Temperature (°C)	60
Maximum Storage Temperature (°F)	140
Minimum Storage Temperature (°C)	-20
Minimum Storage Temperature (°F)	-4
Compliance Certifications	CB & NRTL Certificate/Report, ROHS, REACH
Product Warranty Period (Worldwide)	5 Years
Part Features	• Touch Screen • Auto Rotating Screen • Secure Zero Touch Provisioning • Full Redfish API • Cybersecurity per IEC 62443 • USGv6 Certified IPV6 • 64 PDU Daisy Chain • Secure Supply Chain via Code Signing • 3 Year Warranty • Extended Warranty Available • Dual Ethernet Ports • High Visibility Combination Outlets

Packaging Detail

UPC	61305690243
Std. Pkg. Qty.	1
Std. Pkg. Volume (cf)	0.3650
Std. Ctn. Qty.	0
Std. Ctn. Volume (cf)	0.0000