

PERFORMANCE

Display Size
21.5"

View Area
476.1x267.8 mm

Panel
In-Plane Switching

Backlight
WLED

Aspect Ratio
16:9

Resolution
1920x1080

Pixel Pitch
0.2479x0.2479 mm

Dot / Pixel Per Inch
102 DPI

View Angle (H / V)
178° / 178°

Response Time
4ms GtG (Extreme mode) / 6ms GtG (Typical mode)

Color Support
16.7 Million

Refresh Rate
100Hz

Brightness
250 cd/m²

Contrast Ratio
1300:1

Color Gamut
99% sRGB

Screen Surface Treatment
Anti-glare

Curvature
Flat Panel

Camera
None

Microphone
None

Speakers
2Wx2

Power Consumption (Typical / Maximum)
10.5W / 25W

Power Adapter
Integrated

Touchscreen
None

Smart System
None

DESIGN

Stand
Tilt, Swivel, Pivot, Height Adjust Stand

Case Color
Raven Black

Side Bezel Width
2.0 mm

Mounting
Supports VESA mount 100 x 100 mm

ThinkCentre® M Series Support
Tiny Support

Pen
None

Dimensions (WxDxH)^[1]

- Lowest Position | 489.3 x 178.8 x 317.3 mm (19.26 x 7.04 x 12.49 inches)
- Highest Position | 489.3 x 178.8 x 472.3 mm (19.26 x 7.04 x 18.59 inches)
- Head Only | 489.3 x 52.7 x 296.8 mm (19.26 x 2.07 x 11.69 inches)

Packaging Dimensions (WxDxH)
555.0 x 130.0 x 420.0 mm (21.85 x 5.12 x 16.54 inches)

Weight^[2]

- Monitor With Stand | 4.1 kg (9.0 lbs)
- Monitor Head Only | 2.5 kg (5.5 lbs)

Packaging Weight
5.7 kg (12.6 lbs)

CONNECTIVITY

USB Port
None

Video Connector
1x HDMI® 1.4, 1x DP 1.2, 1x VGA

Network Connectivity
None

SERVICE

Base Warranty
3-year

CERTIFICATIONS

Environmental Certification
ENERGY STAR® Certified, TCO 10, TCO Edge 2.1, EPEAT™ Gold, EU Energy Efficiency Level (Level-C)

Ergonomic Certification
TÜV Low Blue Light (Hardware solution), TÜV Rheinland® Flicker Free

Sync Technology
None

Special Features
Natural Low Blue Light

SOFTWARE

Operating System
Support Windows® 10, Windows® 11


ACCESSORIES

Video Cables
HDMI® cable

MODEL

Announce Date : 2025-07-30 **Region** : NA

EAN / UPC / JAN : 0198158436120 / 198158436120 / None



Product image is a sample, it may not match the real color of this model

Note:

[1] The system dimensions may vary depending on configurations.
[2] The system weight is approximate and based on results in Lenovo lab, which varies depending on the source of component, variance of the distribution of each component, and manufacturing process. It may not be the exact weight for each specific model.

· Lenovo reserves the right to change specifications without notice.
· California Electronic Waste Recycling Fee In California, per state law, Lenovo charges an electronic waste recycling fee on this covered device at the time of sale of the product. For more information, go to: <https://www.calrecycle.ca.gov/Electronics/Consumer>

To see more note information, please access the [web page](#).

Premium Care - Advanced Support from Real People. Real Fast.



REAL PERSON

Choose how you want to reach us - through the phone, chat or email - our expert technicians will take care of you.



REAL FAST

Highly trained technicians will provide you real-time solutions, whatever the issue, on your first contact. If needed, our team will schedule an onsite visit for the next business day.



HASSLE FREE

'Getting started' and 'how-to' assistance for hardware and software. Easy solutions that are simple to reach - that's how Premium Care delivers you the ideal support experience.



PC HEALTH CHECK

Free annual PC Health Check that allows our experts to spot issues before you do so they can resolve them quickly and help you avoid PC problems.

Accidental Damage Protection - Protection of your PC from the unexpected.



Experience shows that a significant portion of devices may be damaged (and not covered under warranty) in the first three years. Lenovo's Accidental Damage Protection service covers accidents beyond the system warranty such as drops, spills, bumps and even electrical surges. Make sure your new device has maximum protection, avoid unplanned costs and get peace of mind.

Base Warranty – Included with the systems you purchase, default 1- or 3-year coverage window.

Warranty Extensions & Upgrades – Service and protection that's right for your circumstances.

- Pick Up & Return Courier
- Technician Installed Customer
- Onsite Support
- Replaceable Unit Service
- International Warranty Upgrade

Lenovo may not offer the products, services or features discussed in this document in all regions. Lenovo may withdraw an offering at any time. Consult your local representative for information on offerings available in your area. Lenovo reserves the right to change specifications or other product information without notice. Lenovo is not responsible for photographic or typographical errors. Lenovo provides this publication "as is" without warranty of any kind, either express or implied, including the implied warranties of merchantability or fitness for a particular purpose.



Lenovo

PSREF
Product Specifications
Reference