

PERFORMANCE

Display Size	27"
View Area	597.9x336.3 mm
Panel	In-Plane Switching
Backlight	WLED
Aspect Ratio	16:9
Resolution	1920x1080
Pixel Pitch	0.3114x0.3114 mm
Dot / Pixel Per Inch	82 dpi
View Angle (H / V)	178° / 178°
Response Time	4ms GtG (Extreme mode) / 6ms GtG (Typical mode)
Color Support	16.7 Million
Refresh Rate	48Hz - 120Hz
Brightness	300 cd/m ²
Contrast Ratio	1500:1
Color Gamut	99% sRGB, 99% BT.709
Screen Surface Treatment	Anti-glare
Curvature	Flat Panel
Camera	ThinkVision® VoIP Stack MC60 Monitor Webcam
Microphone	None
Speakers	Modular Speaker Support
Power Consumption (Typical / Maximum)	15W / 75W
Power Adapter	Integrated
Touchscreen	None

Smart System	None
DESIGN	
Stand	Tilt, Swivel, Pivot, Height Adjust Stand
Case Color	Eclipse Black
Side Bezel Width	2 mm
Mounting	Supports VESA mount 100 x 100 mm
ThinkCentre® M Series Support	Tiny Support

Pen	None
Dimensions (WxDxH)^[1]	- Lowest Position 611.9 x 195.0 x 382.8 mm (24.09 x 7.68 x 15.07 inches) - Highest Position 611.9 x 195.0 x 537.8 mm (24.09 x 7.68 x 21.17 inches) - Head Only 611.9 x 46.0 x 355.2 mm (24.09 x 1.81 x 13.98 inches)
Packaging Dimensions (WxDxH)	693.0 x 150.0 x 420.0 mm (27.28 x 5.91 x 16.54 inches)
Weight^[2]	- Monitor With Stand 6.5 kg (14.3 lbs) - Monitor Head Only 4.4 kg (9.7 lbs)

Packaging Weight	Models with ThinkVision® VoIP Stack MC60 Monitor Webcam: 9.3 kg (20.53lbs)
-------------------------	--

CONNECTIVITY

USB Port	3x USB-A (USB 5Gbps), 1x USB-C® (USB 5Gbps, PD 15W), 1x USB-B (USB 5Gbps, USB upstream)
Video Connector	1x HDMI® 1.4, 1x DP 1.2, 1x VGA
Network Connectivity	None

SERVICE

Base Warranty	3-year
----------------------	--------

CERTIFICATIONS

Environmental Certification	ENERGY STAR® Certified, TCO 10, TCO Edge 2.1, EPEAT™ Gold, EU Energy Efficiency Level (Level-D)
------------------------------------	---

Ergonomic Certification

Eyesafe® Display 2.0, TÜV Low Blue Light (Hardware solution), TÜV Rheinland® Eye Comfort (5 Stars)

Sync Technology

None

Special Features

- Lenovo® ThinkColour (Lenovo® Accessories and Display Manager) Support
Lenovo® ThinkColour supports Windows® 10 & 11, Mac OS (functions vary across systems).
Lenovo® Accessories and Display Manager is formerly Lenovo® Display Control Center.
- LDFM (Lenovo® Display Fleet Manager)
- Natural Low Blue Light

SOFTWARE

Operating System

Support Windows® 10, Windows® 11

ACCESSORIES

Video Cables

DP cable, USB-B to USB-A cable

MODEL

Announce Date	: 2025-03-27	Region	: NA
EAN / UPC / JAN	: 0198155817090 / 198155817090 / None		



Product image is a sample, it may not match the real color of this model

Note:

^[1] The system dimensions may vary depending on.....

- Lenovo reserves the right to change specifications without notice.
- California Electronic Waste Recycling Fee In California, per state law, Lenovo charges an electronic waste recycling fee on this covered device at the time of sale of the product. For more information, go to: <https://www.calrecycle.ca.gov/Electronics/Consumer>

To see more note information, please access the [web page](#).

Premium Care - Advanced Support from Real People. Real Fast.



REAL PERSON

Choose how you want to reach us - through the phone, chat or email - our expert technicians will take care of you.



REAL FAST

Highly trained technicians will provide you real-time solutions, whatever the issue, on your first contact. If needed, our team will schedule an onsite visit for the next business day.



HASSLE FREE

'Getting started' and 'how-to' assistance for hardware and software. Easy solutions that are simple to reach - that's how Premium Care delivers you the ideal support experience.



PC HEALTH CHECK

Free annual PC Health Check that allows our experts to spot issues before you do so they can resolve them quickly and help you avoid PC problems.

Accidental Damage Protection - Protection of your PC from the unexpected.

Experience shows that a significant portion of devices may be damaged (and not covered under warranty) in the first three years. Lenovo's Accidental Damage Protection service covers accidents beyond the system warranty such as drops, spills, bumps and even electrical surges. Make sure your new device has maximum protection, avoid unplanned costs and get peace of mind.

Base Warranty – Included with the systems you purchase, default 1- or 3-year coverage window.

Warranty Extensions & Upgrades – Service and protection that's right for your circumstances.

- Pick Up & Return Courier
- Onsite Support
- Technician Installed Customer
- Replaceable Unit Service
- International Warranty Upgrade

Lenovo may not offer the products, services or features discussed in this document in all regions. Lenovo may withdraw an offering at any time. Consult your local representative for information on offerings available in your area. Lenovo reserves the right to change specifications or other product information without notice. Lenovo is not responsible for photographic or typographical errors. Lenovo provides this publication "as is" without warranty of any kind, either express or implied, including the implied warranties of merchantability or fitness for a particular purpose.

Recommended Accessories



Lenovo Essential FHD Webcam

4XC1B34802

The Lenovo FHD Webcam is powered by a Full HD 1080P 2 Megapixel CMOS camera that allows your friends, family, and colleagues to see you as clear as day, even when they are worlds away. With full stereo dual-mics that ...



Lenovo Performance FHD Webcam

4XC1D66055

A USB Video Class (UVC) compliant video camera designed for teleconferencing applications on desktop or laptop. It's a reliable digital video device to transfer video data with HD quality through a high-speed USB inte...

Please click [here](#) to view the full list of accessories.

Lenovo

PSREF
Product Specifications
Reference