

PERFORMANCE

Processor
Intel® Core™ Ultra 7 255HX, 20C (8P + 12E) / 20T, Max Turbo up to 5.2GHz, 30MB

AI PC Category
AI-Ready Workstations

NPU
Integrated Intel® AI Boost, up to 13 TOPS

Graphics
NVIDIA® RTX PRO 2000 Blackwell Generation 8GB GDDR7 Laptop GPU

Chipset
Intel® WM880 Chipset

Memory
2x 16GB SODIMM DDR5-5600 Non-ECC

Memory Slots
Four DDR5 SO-DIMM slots, dual-channel capable

Max Memory

- Models with ECC memory: Up to 128GB (4x 32GB SO-DIMM DDR5-5600 ECC)
- Models with Non-ECC memory: Up to 192GB (4x 48GB SO-DIMM DDR5-5600 Non-ECC)

Storage
1TB SSD M.2 2280 PCIe® 5.0x4 Performance NVMe® Opal 2.0

Storage Slot
Three M.2 slots

- One M.2 2280 PCIe® 5.0 x4 slot
- Two M.2 2280 PCIe® 4.0 x4 slots

Max Storage Support
Up to three M.2 2280 Gen 5 Performance SSD; up to 12TB, 4TB each

Card Reader
SD Express 8.0 Card Reader

Audio Chip
SoundWire®, Cirrus Logic® CS42L43 codec

Speakers
Stereo speakers, 2W x2, Dolby Atmos®

Microphone
2x, Array

Camera
5.0MP + IR with Privacy Shutter and Computer Vision Human Presence Detection on ISP

Battery
99.9Wh

Power Adapter
180W USB-C® GaN (3-pin)

DESIGN

Display
16" WQUXGA (3840x2400) IPS 800nits Anti-glare, 100% DCI-P3, 60Hz, DisplayHDR™ 400, Dolby Vision®, Eyesafe®, TÜV Low Blue Light

Screen-to-Body Ratio
82%

Color Calibration
X-Rite® Factory Color Calibration

Pen
Pen Not Supported

Keyboard
Backlit, English

Dimensions (WxDxH)
362 x 252 x 15.8 / 20.9 (front / rear), 29.8 (maximum) mm
14.25 x 9.92 x 0.62 / 0.82 (front / rear), 1.17 (maximum) inches

Weight
Starting at 2.54 kg (5.6 lbs)

Case Color
Black

Case Material
Aluminium (Top), Aluminium (Bottom)

SOFTWARE

Operating System
Windows® 11 Pro, English (US) / English (UK)

Bundled Software
Lenovo® AI Now

CONNECTIVITY

WLAN + Bluetooth®
Intel® Wi-Fi® 7 BE200, 802.11be 2x2 + BT5.4

WWAN
Non-WWAN

Ethernet
1x 2.5GbE RJ-45

Standard Ports

- 1x USB-A (USB 10Gbps / USB 3.2 Gen 2), Always On
- 1x USB-A (USB 10Gbps / USB 3.2 Gen 2)
- 2x Thunderbolt™ 5, with USB PD 3.1, 180W input / 15W output
- 1x Thunderbolt™ 4, with USB PD 3.1, 180W input / 15W output
- 1x HDMI® 2.1, up to 8K/60Hz
- 1x Headphone / microphone combo jack (3.5mm)
- 1x Ethernet (2.5GbE RJ-45)
- 1x SD Express 8.0 card reader

SECURITY & PRIVACY

Security Chip
Discrete TPM 2.0 Enabled

Physical Locks
Kensington® Nano Security Slot™, 2.5 x 6 mm

Fingerprint Reader
Touch Style, Match-on-Chip, Integrated in Power Button

Other Security

- Camera privacy shutter (camera models)
- Computer Vision-based User Presence Sensing on Image Signal Processor (ISP)

MANAGEABILITY

System Management
Non-vPro®

SERVICE

Base Warranty
1-year, Courier or Carry-in

Included Upgrade
1Y Premier Support Upgrade from 1Y Courier/Carry-in

CERTIFICATIONS

ISV Certifications
Please visit [ISV certifications for Lenovo® Workstations](#)

Green Certifications

- ENERGY STAR® 9.0
- EPEAT™ Gold Registered
- RoHS compliant
- TCO Certified, generation 10

Mil-Spec Test
MIL-STD-810H military test passed

Other Certifications

- Eyesafe® Certified 2.0
- TÜV Rheinland® Low Blue Light

MODEL

TopSeller	: Yes	Announce Date	: 2025-09-22
EAN / UPC / JAN	: 199272179320	End of Support	: 2032-04-09

Premier Support - A direct 24x7x365 line to our most elite technicians.



Advanced technical support, 24x7x365, in more than 100 markets



Technical Account Managers for proactive relationship and escalation management



Comprehensive hardware & OEM software support



Priority on service delivery and repair parts



Single point of contact for simplified end-to-end case management



Lenovo Service Connect Portal for customized reporting and product support

Accidental Damage Protection - Protection of your PC from the unexpected.

Experience shows that a significant portion of devices may be damaged (and not covered under warranty) in the first three years. Lenovo's Accidental Damage Protection service covers accidents beyond the system warranty such as drops, spills, bumps and even electrical surges. Make sure your new device has maximum protection, avoid unplanned costs and get peace of mind.

Base Warranty - Included with the systems you purchase, default 1- or 3-year coverage window.

Warranty Extensions & Upgrades - Service and protection that's right for your circumstances.

- Pick Up & Return Courier
- Onsite Support
- Technician Installed Customer
- Replaceable Unit Service
- International Warranty Upgrade

Lenovo may not offer the products, services or features discussed in this document in all regions. Lenovo may withdraw an offering at any time. Information is subject to change without notice. Consult your local representative for information on offerings available in your area. Lenovo reserves the right to change specifications or other product information without notice. Lenovo is not responsible for photographic or typographical errors. Lenovo provides this publication "as is" without warranty of any kind, either express or implied, including the implied warranties of merchantability or fitness for a particular purpose.

Recommended Accessories



Lenovo Professional Wireless Combo Keyboard & Mouse (US English)

4X30H56796

This sleek and stylish full-size keyboard and mouse combo offers exceptional quality in a modern wireless solution. The slim 3-zone keyboard with number pad has responsive quiet keys and a premium typing experience. O...



Lenovo Essential USB Mouse

4Y50R20863

The Lenovo Essential USB Mouse is more than your basic mouse. It features an easy plug-and-play connection to PCs with USB cord. The ergonomic full-size design provides comfortable grip for all day comfort. A high-re...

Please click [here](#) to view the full list of accessories.



PSREF
Product Specifications
Reference